



SIMATIC ET 200SP HA, configurable I/O module, AI-DI16/DQ16x24VDC HART, suitable for terminal block H1, M1, color code CC00, channel diagnostics, 16-bit, +/-0.1%,

General information	
Product type designation	AI-DI 16/DQ 16x24VDC HART HA
Firmware version	V1.1
• FW update possible	Yes
Usable terminal block	TB type H1, M1 and N0
Color code for module-specific color identification plate	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V16
• STEP 7 configurable/integrated from version	V5.6
• PCS 7 configurable/integrated from version	V9.0
• PCS neo can be configured/integrated from version	V3.0
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• DI	Yes
• Counter	Yes
• DQ	Yes
• DQ with energy-saving function	No
• PWM	No
• Oversampling	No
• MSI	No
• MSO	No
Redundancy	
• Redundancy capability	Yes; With TB type M1
CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	80 mA; without sensor supply
Current consumption, max.	90 mA; without sensor supply
Encoder supply	
Number of outputs	16
Output voltage, min.	18.2 V
Short-circuit protection	Yes; per channel, electronic
24 V encoder supply	

<ul style="list-style-type: none"> • 24 V • Short-circuit protection • Output current per channel, max. • Output current per module, max. 	Yes Yes; Electronic (response threshold 0.7 A to 1.5 A) 0.5 A 2 A
Power loss	
Power loss, typ.	4.5 W; without sensor supply
Address area	
Address space per module	
<ul style="list-style-type: none"> • Address space per module in mixed operation, max. • Address space per module in mixed operation with HART, max. • Address space per module in mixed operation with multiHART, max. • Address space per module in purely digital operation, max. • Address space per module in purely digital operation with counter/frequency measurement, max. 	42 byte; 34 bytes for inputs, 2 bytes for outputs and 6 bytes for QI information 82 byte; 34-byte inputs, 2-byte outputs, 40 bytes for HART secondary variables, and 6 bytes for QI information 70 byte; 34-byte inputs, 2-byte outputs, 24-byte HART inputs, 4-byte HART outputs, and 6 bytes for QI information 26 byte; 2 bytes for inputs, 2 bytes for outputs, 18 bytes for high-precision time stamping and 4 bytes for QI information. 88 byte; 2 bytes for inputs, 2 bytes for outputs, 40 bytes for counter input data, 40 bytes for counter output data and 4 bytes for QI information.
Digital inputs	
Number of digital inputs	16
Digital inputs, parameterizable	Yes
Source/sink input	Yes; P-reading
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Input characteristic curve in accordance with IEC 61131, type 2	No
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Pulse extension	Yes; off, 50 ms, 100 ms, 200 ms, 500 ms, 1 s, 2 s
Time stamping	Yes; Resolution 10 ms
Time stamp (with precision of 1 ms)	Yes; Resolution 1ms
Digital input functions, parameterizable	
<ul style="list-style-type: none"> • Gate start/stop • Freely usable digital input • Counter <ul style="list-style-type: none"> — Number, max. — Counting frequency, max. — Counting width — Counting direction up/down 	Yes; Partner channel of n+8 counter Yes; Parameterizable input filter Yes; Incl. frequency measurement 8; Counter channel n=0 ... 7 5 kHz 32 bit; Without sign Yes; Up
Input voltage	
<ul style="list-style-type: none"> • Rated value (DC) • for signal "0" • for signal "1" 	24 V -30 to +5 V +11 to +30V
Input current	
<ul style="list-style-type: none"> • for signal "1", typ. 	2.5 mA
Input delay (for rated value of input voltage)	
for standard inputs <ul style="list-style-type: none"> — parameterizable 	Yes; 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms (in each case + delay of 30 to 500 µs, depending on line length)
Cable length	
<ul style="list-style-type: none"> • shielded, max. • unshielded, max. 	1 000 m 600 m
Digital outputs	
Number of digital outputs	16
Current-sinking	No
Current-sourcing	Yes
Short-circuit protection	Yes; Response threshold 0.7 A to 1.3 A
Open-circuit detection	Yes
Overload protection	Yes
Limitation of inductive shutdown voltage to	L+ -(37 to 41V)
Controlling a digital input	Yes
Switching capacity of the outputs	
<ul style="list-style-type: none"> • with resistive load, max. • on lamp load, max. 	0.5 A 5 W
Load resistance range	
<ul style="list-style-type: none"> • lower limit 	48 Ω

• upper limit	12 kΩ
Output current	
• for signal "1" rated value	0.5 A
• for signal "0" residual current, max.	0.7 mA
Output delay with resistive load	
• "0" to "1", typ.	50 μs
• "1" to "0", typ.	100 μs
Parallel switching of two outputs	
• for uprating	No
• for redundant control of a load	Yes
Switching frequency	
• with resistive load, max.	100 Hz
• on lamp load, max.	10 Hz
Total current of the outputs	
• Current per channel, max.	0.5 A
• Current per module, max.	2 A
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Analog inputs	
Number of analog inputs	16
permissible input current for current input (destruction limit), max.	30 mA
Input ranges	
• Current	Yes; 0 ... 10 mA, 0 ... 20 mA, 4 ... 20 mA, 4 ... 20 mA HART
Input ranges (rated values), currents	
• 0 to 10 mA — Input resistance (0 to 10 mA)	Yes 250 Ω
• 0 to 20 mA — Input resistance (0 to 20 mA)	Yes; 16 bit incl. sign 250 Ω
• 4 mA to 20 mA — Input resistance (4 mA to 20 mA)	Yes; 16 bit incl. sign 250 Ω
Analog value generation for the inputs	
Measurement principle	integrating (Sigma-Delta)
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit; Resolution with overrange (bit including sign), max. 16 bits, exception: 15 bits at 60 Hz interference suppression and 0 to 10 mA
• Integration time, parameterizable	Yes; channel by channel
Smoothing of measured values	
• parameterizable	Yes; none, weak, medium, strong, channel-by-channel
Encoder	
Connection of signal encoders	
• for current measurement as 2-wire transducer	Yes
Connectable encoders	
• 2-wire sensor — permissible quiescent current (2-wire sensor), max.	Yes 1.5 mA
Errors/accuracies	
Linearity error (relative to input range), (+/-)	0.01 %
Temperature error (relative to input range), (+/-)	0.005 %/K
Crosstalk between the inputs, min.	60 dB
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.05 %
Operational error limit in overall temperature range	
• Current, relative to input range, (+/-)	0.5 %
Basic error limit (operational limit at 25 °C)	
• Current, relative to input range, (+/-)	0.1 %
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes

• Maintenance interrupt	Yes
• Limit value alarm	Yes; two upper and two lower limit values in each case
• Hardware interrupt	Yes; Parameterizable, channels 0 to 15, rising/falling edge
Diagnoses	
• Monitoring the supply voltage	Yes
• Wire-break	Yes; channel by channel
• Short-circuit to M	Yes; Encoder supply to M, channel by channel
• Group error	Yes
• Overflow/underflow	Yes; channel by channel
Diagnostics indication LED	
• MAINT LED	Yes; Yellow LED
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	No
• for channel diagnostics	No
• for module diagnostics	Yes; green/red DIAG LED
Integrated Functions	
Frequency measurement	Yes
• Number of frequency meters	8
Counting functions	
• Continuous counting	Yes
• Counter response parameterizable	Yes
• Hardware gate via digital input	Yes; Via partner channel (digital input n+8)
• Software gate	Yes
Measuring functions	
• Dynamic measurement period adjustment	Yes
Measuring range	
— Frequency measurement, min.	0.1 Hz
— Frequency measurement, max.	5 kHz
Accuracy	
— Frequency measurement	100 ppm; depending on measuring interval and signal evaluation
Potential separation	
Potential separation channels	
• between the channels	No
• between the channels and backplane bus	Yes
• Between the channels and load voltage L+	No
Isolation	
Isolation tested with	1 500 V DC/1 min, type test
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-40 °C
• horizontal installation, max.	70 °C; Observe derating
• vertical installation, min.	-40 °C
• vertical installation, max.	60 °C; Observe derating
Dimensions	
Width	22.5 mm
Height	115 mm
Depth	138 mm
Weights	
Weight, approx.	150 g

last modified:

11/2/2021 