



SIMATIC Cloud Connect 7, CC716 IoT Gateway for connection of automation devices to cloud services and OPC 2x Ethernet RJ45, 1xMPI/PB Field protocols: S7, OPC UA, Modbus MES/Cloud protocols: MQTT, HTTP, OPC UA

transfer rate	
transfer rate	
• at the 1st interface	10 ... 1000 Mbit/s
• at the 2nd interface	10 ... 1000 Mbit/s
• at the 1st interface / according to PROFIBUS	9.6 kbit/s ... 12 Mbit/s
interfaces	
number of electrical connections	
• at the 1st interface / according to Industrial Ethernet	1
• at the 2nd interface / according to Industrial Ethernet	1
• at the 1st interface / according to PROFIBUS	1
• for power supply	2
type of electrical connection	
• at the 1st interface / according to Industrial Ethernet	RJ45 port
• at the 2nd interface / according to Industrial Ethernet	RJ45 port
type of electrical connection	
• at the 1st interface / according to PROFIBUS	9-pin Sub-D socket (RS485)
• for power supply	5-pin terminal strip
design of the removable storage	
• CLP	Yes
signal inputs/outputs	
number of electrical connections / for digital input signals	1
number of electrical connections / for digital output signals	1
supply voltage, current consumption, power loss	
type of voltage / of the supply voltage	DC
supply voltage	24 V
supply voltage / external	10.8 ... 28.8 V
supply voltage / external / at DC / rated value	24 V
consumed current	
• from external supply voltage / at 24 V DC	
— in communication mode / typical	180 mA
power loss [W]	4.3 W
ambient conditions	
ambient temperature	
• for vertical installation / during operation	0 ... 40 °C
• for horizontally arranged busbars / during operation	0 ... 60 °C
• during storage	-40 ... +40 °C
• during transport	-40 ... +70 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %

protection class IP	IP20
design, dimensions and weights	
module format	Compact
width	35 mm
height	147 mm
depth	127 mm
net weight	0.4 kg
fastening method	
• 35 mm top hat DIN rail mounting	Yes
• S7-300 rail mounting	Yes
• S7-1500 rail mounting	Yes
• wall mounting	Yes
product functions / cloud connectivity	
protocol / is supported	
• Message Queuing Telemetry Transport (MQTT)	Yes
• Advanced Message Queuing Protocol (AMQP)	No
• HTTP	Yes
• REST-API	Yes
product function / for cloud connectivity	
• trigger management	Yes
• time stamping	Yes
product feature / for cloud connectivity / buffered message frame memory	Yes
number of active connections / for cloud connectivity	3
number of lower-level devices / maximum	7
number of data points per device / maximum	3500
performance data / PROFIBUS DP	
service / as DP master	
• DPV0	No
• DPV1	No
service / as DP slave	
• DPV0	No
• DPV1	No
performance data / S7 communication	
number of possible connections / for S7 communication	
• maximum	7
performance data / as OPC UA server	
protocol / is supported / OPC UA Server	Yes
number of possible connections / to OPC UA clients / maximum	10
number of variables (items) / maximum	3500
performance data / as OPC UA client	
protocol / is supported / OPC UA Client	Yes
number of possible connections / for OPC UA server / maximum	7
product functions / diagnostics	
product function / web-based diagnostics	Yes
product functions / security	
operating mode / Virtual Private Network (VPN)	No
product function	
• password protection for Web applications	Yes
• SysLog	Yes
product functions / time	
protocol / is supported	
• NTP	Yes
• NTP (secure)	Yes
time synchronization	
• from NTP-server	Yes
• manual setting	Yes
standards, specifications, approvals / hazardous environments	
certificate of suitability / CCC / for hazardous zone according to GB standard	Yes
• as marking	Ex nA IIC T4 Gc

further information / internet links

internet link

- to web page: selection aid TIA Selection Tool
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAX-Download-Manager
- to website: Industry Online Support

<http://www.siemens.com/tia-selection-tool>
<http://www.siemens.com/simatic-net>
<https://mall.industry.siemens.com>
<http://www.siemens.com/industry/infocenter>
<http://automation.siemens.com/bilddb>
<http://www.siemens.com/cax>
<https://support.industry.siemens.com>

security information

security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

6/7/2023 