



SIPLUS ET 200SP AI 4xU/I 2-wire T1 rail based on 6ES7134-6HD01-0BA1 with conformal coating, -40...+60 °C, OT1 with ST1/2 (+70 °C für 10 minutes), analog input module, suitable for BU type A0, A1, color code CC03, module diagnostics, 16 bit, +/-0.3%

General information	
Product type designation	AI 4x U/I 2-wire
Firmware version	
• FW update possible	Yes
usable BaseUnits	BU type A0, A1
Color code for module-specific color identification plate	CC03
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
• Measuring range scalable	No
Operating mode	
• Oversampling	No
• MSI	No
CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Calibration possible in RUN	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	37 mA; without sensor supply
Encoder supply	
24 V encoder supply	
• 24 V	Yes
• Short-circuit protection	Yes
• Output current, max.	20 mA; max. 50 mA per channel for a duration < 10 s
Power loss	
Power loss, typ.	0.85 W; Without encoder supply voltage
Address area	
Address space per module	
• Address space per module, max.	8 byte; + 1 byte for QI information
Hardware configuration	
Automatic encoding	
• Mechanical coding element	Yes
Selection of BaseUnit for connection variants	
• 2-wire connection	BU type A0, A1
Analog inputs	
Number of analog inputs	4; Differential inputs

permissible input voltage for voltage input (destruction limit), max.	30 V
permissible input current for current input (destruction limit), max.	50 mA
Cycle time (all channels), min.	Sum of the basic conversion times and additional processing times (depending on the parameterization of the active channels)
<b>Input ranges (rated values), voltages</b>	
<ul style="list-style-type: none"> <li>0 to +10 V <ul style="list-style-type: none"> <li>Input resistance (0 to 10 V)</li> </ul> </li> <li>1 V to 5 V <ul style="list-style-type: none"> <li>Input resistance (1 V to 5 V)</li> </ul> </li> <li>-10 V to +10 V <ul style="list-style-type: none"> <li>Input resistance (-10 V to +10 V)</li> </ul> </li> <li>-5 V to +5 V <ul style="list-style-type: none"> <li>Input resistance (-5 V to +5 V)</li> </ul> </li> </ul>	Yes; 15 bit 120 kΩ Yes; 15 bit 120 kΩ Yes; 16 bit incl. sign 120 kΩ Yes; 16 bit incl. sign 120 kΩ
<b>Input ranges (rated values), currents</b>	
<ul style="list-style-type: none"> <li>0 to 20 mA <ul style="list-style-type: none"> <li>Input resistance (0 to 20 mA)</li> </ul> </li> <li>4 mA to 20 mA <ul style="list-style-type: none"> <li>Input resistance (4 mA to 20 mA)</li> </ul> </li> </ul>	Yes; 15 bit 100 Ω; + approx. 0.7 V diode forward voltage Yes; 15 bit 100 Ω; + approx. 0.7 V diode forward voltage
<b>Cable length</b>	
<ul style="list-style-type: none"> <li>shielded, max.</li> </ul>	1 000 m; 200 m for voltage measurement
<b>Analog value generation for the inputs</b>	
Measurement principle	integrating (Sigma-Delta)
<b>Integration and conversion time/resolution per channel</b>	
<ul style="list-style-type: none"> <li>Resolution with overrange (bit including sign), max.</li> <li>Integration time, parameterizable</li> <li>Interference voltage suppression for interference frequency f1 in Hz</li> <li>Conversion time (per channel)</li> </ul>	16 bit Yes 16.6 / 50 / 60 Hz 180 / 60 / 50 ms
<b>Smoothering of measured values</b>	
<ul style="list-style-type: none"> <li>Number of smoothering levels</li> <li>parameterizable</li> </ul>	4; None; 4/8/16 times Yes
<b>Encoder</b>	
<b>Connection of signal encoders</b>	
<ul style="list-style-type: none"> <li>for voltage measurement</li> <li>for current measurement as 2-wire transducer <ul style="list-style-type: none"> <li>Burden of 2-wire transmitter, max.</li> </ul> </li> <li>for current measurement as 4-wire transducer</li> </ul>	Yes Yes 650 Ω No
<b>Errors/accuracies</b>	
Linearity error (relative to input range), (+/-)	0.01 %
Temperature error (relative to input range), (+/-)	0.005 %/K
Crosstalk between the inputs, min.	50 dB
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.05 %
<b>Operational error limit in overall temperature range</b>	
<ul style="list-style-type: none"> <li>Voltage, relative to input range, (+/-)</li> <li>Current, relative to input range, (+/-)</li> </ul>	0.7 % 0.7 %
<b>Basic error limit (operational limit at 25 °C)</b>	
<ul style="list-style-type: none"> <li>Voltage, relative to input range, (+/-)</li> <li>Current, relative to input range, (+/-)</li> </ul>	0.3 % 0.3 %
<b>Interference voltage suppression for <math>f = n \times (f1 \pm 1 \%)</math>, f1 = interference frequency</b>	
<ul style="list-style-type: none"> <li>Series mode interference (peak value of interference &lt; rated value of input range), min.</li> <li>Common mode voltage, max.</li> <li>Common mode interference, min.</li> </ul>	70 dB 10 V 90 dB
<b>Interrupts/diagnostics/status information</b>	
Diagnostics function	Yes
<b>Alarms</b>	
<ul style="list-style-type: none"> <li>Diagnostic alarm</li> <li>Limit value alarm</li> </ul>	Yes No
<b>Diagnoses</b>	

<ul style="list-style-type: none"> <li>• Monitoring the supply voltage</li> <li>• Wire-break</li> <li>• Short-circuit</li> <li>• Group error</li> <li>• Overflow/underflow</li> </ul>	<p>Yes</p> <p>Yes; at 4 to 20 mA</p> <p>Yes; with 1 to 5 V or 2-wire mode: Short-circuit of the encoder supply to ground or of an input to the encoder supply</p> <p>Yes</p> <p>Yes</p>
<b>Diagnostics indication LED</b>	
<ul style="list-style-type: none"> <li>• Monitoring of the supply voltage (PWR-LED)</li> <li>• Channel status display</li> <li>• for channel diagnostics</li> <li>• for module diagnostics</li> </ul>	<p>Yes; green LED</p> <p>Yes; green LED</p> <p>No</p> <p>Yes; green/red LED</p>
<b>Potential separation</b>	
<b>Potential separation channels</b>	
<ul style="list-style-type: none"> <li>• between the channels</li> <li>• between the channels and backplane bus</li> <li>• between the channels and the power supply of the electronics</li> </ul>	<p>Yes; channel group-specific between 2-wire current input group and voltage input group</p> <p>Yes</p> <p>Yes; only for voltage inputs</p>
<b>Permissible potential difference</b>	
between the inputs (UCM)	10 V DC
<b>Isolation</b>	
Isolation tested with	750 V DC (type test) and according to EN 50155 (routine test)
<b>Standards, approvals, certificates</b>	
<b>Railway application</b>	
<ul style="list-style-type: none"> <li>• EN 50121-3-2</li> <li>• EN 50121-4</li> <li>• EN 50124-1</li> <li>• EN 50125-1</li> <li>• EN 50125-2</li> <li>• EN 50125-3</li> <li>• EN 50155</li> <li>• EN 61373</li> <li>• Fire protection acc. to EN 45545-2</li> </ul>	<p>Yes; EMC for rail vehicles</p> <p>Yes; EMC for signal and telecommunications systems</p> <p>Yes; Railway applications - overvoltage category OV2; pollution degree PD2; rated surge voltage UNi = 0.5 kV; UNm = 24 V DC</p> <p>Yes; Rail vehicles - see ambient conditions</p> <p>Yes; Stationary electrical equipment - see ambient conditions</p> <p>Yes; Signal and telecommunications systems - see ambient conditions; vibrations and shocks: Application point outside of tracks (1 m to 3 m away from track)</p> <p>Yes; Rail vehicles - temperature class OT1, ST1/ST2, horizontal mounting position</p> <p>Yes; Rail vehicles - vibrations and shocks: Category 1 Class A/B</p> <p>Yes; For proof of conformity, see Service &amp; Support</p>
<b>Ambient conditions</b>	
<b>Ambient temperature during operation</b>	
<ul style="list-style-type: none"> <li>• horizontal installation, min.</li> <li>• horizontal installation, max.</li> <li>• vertical installation, min.</li> <li>• vertical installation, max.</li> </ul>	<p>-40 °C; = Tmin (incl. condensation/frost); start-up @ -30 °C</p> <p>60 °C; = Tmax; +70 °C for 10 min (OT1, ST1/ST2 acc. to EN 50155)</p> <p>-40 °C; = Tmin; startup @ -30 °C</p> <p>50 °C; = Tmax</p>
<b>Altitude during operation relating to sea level</b>	
<ul style="list-style-type: none"> <li>• Installation altitude above sea level, max.</li> <li>• Ambient air temperature-barometric pressure-altitude</li> </ul>	<p>2 000 m</p> <p>Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m)</p>
<b>Relative humidity</b>	
<ul style="list-style-type: none"> <li>• With condensation, tested in accordance with IEC 60068-2-38, max.</li> </ul>	100 %; RH incl. condensation / frost (no commissioning in bedewed state), horizontal installation
<b>Resistance</b>	
<b>Coolants and lubricants</b>	
— Resistant to commercially available coolants and lubricants	Yes; Incl. diesel and oil droplets in the air
<b>Use in stationary industrial systems</b>	
— to biologically active substances according to EN 60721-3-3	Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request
— to chemically active substances according to EN 60721-3-3	Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-3	Yes; Class 3S4 incl. sand, dust, *
— Against mechanical environmental conditions acc. to EN 60721-3-3	Yes; Class 3M8 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0)
<b>Use on land craft, rail vehicles and special-purpose vehicles</b>	
— to biologically active substances according to EN 60721-3-5	Yes; Class 5B2 mold, fungus and dry rot spores (with the exception of fauna); Class 5B3 on request

— to chemically active substances according to EN 60721-3-5	Yes; Class 5C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-5	Yes; Class 5S3 incl. sand, dust; *
— Against mechanical environmental conditions acc. to EN 60721-3-5	Yes; Class 5M2 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0)
— against mechanical environmental conditions in agriculture acc. to ISO 15003	Yes; level 1 (Location LE) using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0)
<b>Usage in industrial process technology</b>	
— Against chemically active substances acc. to EN 60654-4	Yes; Class 3 (excluding trichlorethylene)
— Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04	Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)
<b>Remark</b>	
— Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04	* The supplied plug covers must remain in place over the unused interfaces during operation!
<b>Conformal coating</b>	
<ul style="list-style-type: none"> <li>Coatings for printed circuit board assemblies acc. to EN 61086</li> <li>Protection against fouling acc. to EN 60664-3</li> <li>Electronic equipment on rolling stock acc. to EN 50155</li> <li>Military testing according to MIL-I-46058C, Amendment 7</li> <li>Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A</li> </ul>	<p>Yes; Class 2 for high reliability</p> <p>Yes; Type 1 protection</p> <p>Yes; Class PC2 protective coating acc. to EN 50155:2017</p> <p>Yes; Discoloration of coating possible during service life</p> <p>Yes; Conformal coating, Class A</p>
<b>Dimensions</b>	
Width	15 mm
Height	73 mm
Depth	58 mm
<b>Weights</b>	
Weight, approx.	31 g
<b>Other</b>	
Note:	for use in railway applications, also observe the product information "SIPLUS extreme RAIL" A5E37661960A, Online Support article 109736776

last modified:

4/11/2022 