



SIMATIC ET 200SP, Potential distributor module, PotDis-BaseUnit, PotDis-BU Typ P1, dark-colored, 17 x P1-potential, 1 x P2-potential, Push-In terminals. P1-, P2- and AUX-rail bridged to left BU, Packaging Unit: 1 Piece, WxH: 15mm x 117mm

General information	
Product type designation	PotDis BU type P1, dark version, PU 1
HW functional status	FS10 and higher
Color code for module-specific color identification plate	CC62
Supply voltage	
Rated value (DC)	
<ul style="list-style-type: none"> For P1 and P2 bus for process terminals 	48 V; max.
external protection for power supply lines	Yes; 10 A miniature circuit breaker with type B or C tripping characteristic for the respective rated supply voltage
Current carrying capacity	
For P1 and P2 bus, max.	10 A
For process terminals, max.	10 A
Hardware configuration	
Formation of potential groups	
<ul style="list-style-type: none"> New potential group Potential group continued from the left 	No Yes
Slots	
<ul style="list-style-type: none"> Number of slots 	1
Potential separation	
between backplane bus and supply voltage	Yes
Isolation	
Isolation tested with	3 250 V DC
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> horizontal installation, min. horizontal installation, max. vertical installation, min. vertical installation, max. 	-30 °C 60 °C -30 °C 50 °C
Altitude during operation relating to sea level	
<ul style="list-style-type: none"> Installation altitude above sea level, max. 	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Accessories	
Color coding labels	
<ul style="list-style-type: none"> for process terminals 	CC62
connection method	
Terminals	
<ul style="list-style-type: none"> Terminal type Conductor cross-section, min. Conductor cross-section, max. Number of terminals with connection to P1 and P2 bus 	Push-in terminal 0.14 mm ² 2.5 mm ² 17 terminals to P1, 1 terminal to P2

Dimensions	
Width	15 mm
Height	117 mm
Depth	35 mm
Weights	
Weight, approx.	40 g

last modified: 12/19/2020 