



SIMATIC DP, IM154-8F PN/DP CPU f. ET200 PRO, 512 KB work memory, Int. PROFINET interface, Int. PROFIBUS DP master/slave interface Degree of protection IP65/67, Micro Memory Card and Connection module required

General information	
HW functional status	01
Firmware version	V3.2
Product function	
<ul style="list-style-type: none"> • Isochronous mode 	Yes; Via PROFIBUS DP or PROFINET interface
Engineering with	
<ul style="list-style-type: none"> • Programming package 	STEP 7 V5.5 or higher, Distributed Safety V5.4 SP4
Supply voltage	
Rated value (DC)	24 V
external protection for power supply lines (recommendation)	MCB 24 V DC / 16 A with tripping characteristic Type B and C (see ET 200pro manual)
Load voltage L+	
<ul style="list-style-type: none"> • Rated value (DC) • permissible range, lower limit (DC) • permissible range, upper limit (DC) • Reverse polarity protection 	24 V 20.4 V 28.8 V Yes
Input current	
Current consumption, typ.	350 mA
Current consumption (in no-load operation), typ.	250 mA; Typical, current consumption for CPU in STOP state
Inrush current, typ.	2 A
I ² t	0.25 A ² ·s; Typical
Power loss	
Power loss, typ.	8.5 W
Memory	
Work memory	
<ul style="list-style-type: none"> • integrated • expandable 	512 kbyte No
Load memory	
<ul style="list-style-type: none"> • Plug-in (MMC) • Plug-in (MMC), max. • Data management on MMC (after last programming), min. 	Yes 8 Mbyte 10 a
Backup	
<ul style="list-style-type: none"> • present • without battery 	Yes; Guaranteed by MMC (maintenance-free) Yes; Program and data
CPU processing times	
for bit operations, typ.	0.05 μs
for word operations, typ.	0.09 μs
for fixed point arithmetic, typ.	0.12 μs
for floating point arithmetic, typ.	0.45 μs

CPU-blocks

Number of blocks (total)	1 024; (DBs, FCs, FBs); the maximum number of loadable blocks can be reduced by the MMC used.
DB	
• Number, max.	1 024; Number range: 1 to 16000
• Size, max.	64 kbyte
FB	
• Number, max.	1 024; Number range: 0 to 7999
• Size, max.	64 kbyte
FC	
• Number, max.	1 024; Number range: 0 to 7999
• Size, max.	64 kbyte
OB	
• Size, max.	64 kbyte
• Number of free cycle OBs	1; OB 1
• Number of time alarm OBs	1; OB 10
• Number of delay alarm OBs	2; OB 20, 21
• Number of cyclic interrupt OBs	4; OB 32, 33, 34, 35
• Number of process alarm OBs	1; OB 40
• Number of DPV1 alarm OBs	3; OB 55, 56, 57
• Number of isochronous mode OBs	1; OB 61
• Number of startup OBs	1; OB 100
• Number of asynchronous error OBs	6; OB 80, 82, 83, 85, 86, 87 (OB83 only for centralized I/O and PROFINET IO)
• Number of synchronous error OBs	2; OB 121, 122
Nesting depth	
• per priority class	16
• additional within an error OB	4
Counters, timers and their retentivity	
S7 counter	
• Number	256
Retentivity	
— adjustable	Yes
— lower limit	0
— upper limit	255
— preset	Z 0 to Z 7
Counting range	
— adjustable	Yes
— lower limit	0
— upper limit	999
IEC counter	
• present	Yes
• Type	SFB
• Number	Unlimited (limited only by RAM capacity)
S7 times	
• Number	256
Retentivity	
— adjustable	Yes
— lower limit	0
— upper limit	255
— preset	No retentivity
Time range	
— lower limit	10 ms
— upper limit	9 990 s
IEC timer	
• present	Yes
• Type	SFB
• Number	Unlimited (limited only by RAM capacity)
Data areas and their retentivity	
Retentive data area (incl. timers, counters, flags), max.	128 kbyte
Flag	
• Size, max.	2 048 byte

<ul style="list-style-type: none"> • Retentivity available • Retentivity preset • Number of clock memories 	Yes; MB 0 to MB 2 047 MB 0 to MB 15 8
Data blocks	
<ul style="list-style-type: none"> • Retentivity adjustable • Retentivity preset 	Yes; via non-retain property on DB Yes
Local data	
<ul style="list-style-type: none"> • per priority class, max. 	32 768 byte; Max. 2048 bytes per block
Address area	
I/O address area	
<ul style="list-style-type: none"> • Inputs • Outputs 	2 048 byte 2 048 byte
of which distributed	
<ul style="list-style-type: none"> — Inputs — Outputs 	2 048 byte 2 048 byte
Process image	
<ul style="list-style-type: none"> • Inputs, adjustable • Outputs, adjustable • Inputs, default • Outputs, default 	2 048 byte 2 048 byte 128 byte 128 byte
Subprocess images	
<ul style="list-style-type: none"> • Number of subprocess images, max. 	1; With PROFINET IO, the length of the user data is limited to 1600 bytes
Digital channels	
<ul style="list-style-type: none"> • Inputs <ul style="list-style-type: none"> — of which central • Outputs <ul style="list-style-type: none"> — of which central 	16 384 128 16 384 64
Analog channels	
<ul style="list-style-type: none"> • Inputs <ul style="list-style-type: none"> — of which central • Outputs <ul style="list-style-type: none"> — of which central 	1 024 64 1 024 64
Hardware configuration	
Integrated power supply	No
Number of DP masters	
<ul style="list-style-type: none"> • integrated 	1
Rack	
<ul style="list-style-type: none"> • Racks, max. • Modules per rack, max. 	1 16; Expansion width max. 1 m
Time of day	
Clock	
<ul style="list-style-type: none"> • Hardware clock (real-time) • retentive and synchronizable • Backup time • Deviation per day, max. 	Yes Yes 6 wk; At 40 °C ambient temperature 10 s; Typ.: 2 s
Operating hours counter	
<ul style="list-style-type: none"> • Number • Number/Number range • Range of values • Granularity • retentive 	1 0 0 to 2 ³¹ hours (when using SFC 101) 1 h Yes; Must be restarted at each restart
Clock synchronization	
<ul style="list-style-type: none"> • supported • to MPI, master • to MPI, slave • to DP, master • to DP, slave • on Ethernet via NTP 	Yes Yes Yes Yes; With DP slave only slave clock Yes Yes; As client
1. Interface	
Interface type	Integrated RS 485 interface

Isolated	Yes
Interface types	
• RS 485	Yes
• Output current of the interface, max.	May only be used for external terminating resistor
• Design of the connection	2x M12 B-coded
Protocols	
• MPI	Yes
• PROFIBUS DP master	Yes
• PROFIBUS DP slave	Yes
• Point-to-point connection	No
MPI	
• Transmission rate, max.	12 Mbit/s
Services	
— PG/OP communication	Yes
— Routing	Yes
— Global data communication	Yes
— S7 basic communication	Yes
— S7 communication	Yes
— S7 communication, as client	No
— S7 communication, as server	Yes
PROFIBUS DP master	
• Transmission rate, max.	12 Mbit/s
• Number of DP slaves, max.	124
Services	
— PG/OP communication	Yes
— Routing	Yes
— Global data communication	No
— S7 basic communication	Yes; I blocks only
— S7 communication	Yes
— S7 communication, as client	No
— S7 communication, as server	Yes; Connection configured on one side only
— Equidistance	Yes
— Isochronous mode	Yes; OB 61 - isochronous mode is possible either on DP or PROFINET IO (not simultaneously)
— SYNC/FREEZE	Yes
— Activation/deactivation of DP slaves	Yes
— Direct data exchange (slave-to-slave communication)	Yes; as subscriber
— DPV1	Yes
Address area	
— Inputs, max.	2 048 byte
— Outputs, max.	2 048 byte
User data per DP slave	
— Inputs, max.	244 byte
— Outputs, max.	244 byte
PROFIBUS DP slave	
• Transmission rate, max.	12 Mbit/s
• automatic baud rate search	Yes; only with passive interface
• Address area, max.	32
• User data per address area, max.	32 byte
Services	
— Routing	Yes; with interface active
— Global data communication	No
— S7 basic communication	No
— S7 communication	Yes
— S7 communication, as client	No
— S7 communication, as server	Yes; Connection configured on one side only
— Direct data exchange (slave-to-slave communication)	Yes
— DPV1	No
Transfer memory	
— Inputs	244 byte

— Outputs	244 byte
2. Interface	
Interface type	PROFINET
Isolated	Yes; Galvanic isolation for P3 is implemented in IM154-8, for P1 and P2 in CM
automatic detection of transmission rate	Yes; 10/100 Mbit/s
Autonegotiation	Yes
Autocrossing	Yes
Change of IP address at runtime, supported	Yes
Interface types	
• Number of ports	3
• integrated switch	Yes
• Design of the connection	Ethernet (2x M12 D-coded; 1x RJ45)
Protocols	
• MPI	No
• PROFINET IO Controller	Yes; Also simultaneously with IO-Device functionality
• PROFINET IO Device	Yes; Also simultaneously with IO Controller functionality
• PROFINET CBA	Yes
• PROFIBUS DP master	No
• PROFIBUS DP slave	No
• Open IE communication	Yes; Via TCP/IP, ISO on TCP, and UDP
• Web server	Yes
• Media redundancy	Yes
PROFINET IO Controller	
• Transmission rate, max.	100 Mbit/s
Services	
— PG/OP communication	Yes
— Routing	Yes
— S7 communication	Yes; With loadable FBs, max. configurable connections: 14, max. number of instances: 32
— Isochronous mode	Yes; OB 61 - isochronous mode is possible either on DP or PROFINET IO (not simultaneously)
— IRT	Yes
— Prioritized startup	Yes
— Number of IO devices with prioritized startup, max.	32
— Number of connectable IO Devices, max.	128
— Of which IO devices with IRT, max.	64
— of which in line, max.	64
— Number of IO Devices with IRT and the option "high flexibility"	128
— of which in line, max.	61
— Number of connectable IO Devices for RT, max.	128
— of which in line, max.	128
— Activation/deactivation of IO Devices	Yes
— Number of IO Devices that can be simultaneously activated/deactivated, max.	8
— IO Devices changing during operation (partner ports), supported	Yes
— Number of IO Devices per tool, max.	8
— Device replacement without swap medium	Yes
— Send cycles	250 µs, 500 µs, 1 ms; 2 ms, 4 ms (not in the case of IRT with "high flexibility" option)
— Updating time	250 µs to 512 ms (depending on the operating mode, see "IM 154-8 CPU Interface Module" operating instructions for more details)
Address area	
— Inputs, max.	2 048 byte
— Outputs, max.	2 048 byte
— User data consistency, max.	1 024 byte
PROFINET IO Device	
Services	
— PG/OP communication	Yes
— Routing	Yes
— S7 communication	Yes; With loadable FBs, max. configurable connections: 14, max. number of instances: 32

— Isochronous mode	No
— IRT	Yes
— PROFINergy	Yes; With SFB 73 / 74 prepared for loadable PROFINergy standard FB for I-Device
— Shared device	Yes
— Number of IO Controllers with shared device, max.	2
Transfer memory	
— Inputs, max.	1 440 byte; Per IO Controller with shared device
— Outputs, max.	1 440 byte; Per IO Controller with shared device
Submodules	
— Number, max.	64
— User data per submodule, max.	1 024 byte
PROFINET CBA	
• acyclic transmission	Yes
• cyclic transmission	Yes
Open IE communication	
• Number of connections, max.	8
• Local port numbers used at the system end	0, 20, 21, 23, 25, 80, 102, 135, 161, 443, 8080, 34962, 34963, 34964, 65532, 65533, 65534, 65535
• Keep-alive function, supported	Yes
Protocols	
Redundancy mode	
Media redundancy	
— Switchover time on line break, typ.	200 ms; PROFINET MRP
— Number of stations in the ring, max.	50
SIMATIC communication	
• S7 routing	Yes
Open IE communication	
• TCP/IP	Yes; via integrated PROFINET interface and loadable FBs
— Number of connections, max.	8
— Data length, max.	32 768 byte; 1 460 bytes with connection type 01H; 32 768 bytes with connection type 11H
— several passive connections per port, supported	Yes
• ISO-on-TCP (RFC1006)	Yes
— Number of connections, max.	8
— Data length, max.	32 768 byte
• UDP	Yes
— Number of connections, max.	8
— Data length, max.	1 472 byte
Web server	
• supported	Yes
• User-defined websites	Yes
• Number of HTTP clients	5
communication functions / header	
PG/OP communication	Yes
Global data communication	
• supported	Yes
• Number of GD loops, max.	8
• Number of GD packets, max.	8
• Number of GD packets, transmitter, max.	8
• Number of GD packets, receiver, max.	8
• Size of GD packets, max.	22 byte
• Size of GD packet (of which consistent), max.	22 byte
S7 basic communication	
• supported	Yes
• User data per job, max.	76 byte
• User data per job (of which consistent), max.	76 byte; 76 bytes (with X_SEND or X_RCV); 64 bytes (with X_PUT or X_GET as server)
S7 communication	
• supported	Yes
• as server	Yes
• as client	Yes; via integrated PROFINET interface and loadable FBs

- User data per job, max.

See online help of STEP 7 (shared parameters of the SFBs/FBs and of the SFCs/FCs of S7 Communication)

communication functions / PROFINET CBA (with set target communication load) / header	
• Setpoint for the CPU communication load	50 %
• number of remote connection partners / with PROFINET CBA	32
• number of technological functions / with PROFINET CBA / for master or slave	30
• number of connections / with PROFINET CBA / for master or slave / total	1 000
• data volume / of the input variables / with PROFINET CBA / for master or slave	4 000 byte
• data volume / of the output variables / with PROFINET CBA / for master or slave	4 000 byte
• number of internal and PROFIBUS interconnections / with PROFINET CBA / maximum	500
• data volume / of internal and PROFIBUS interconnections / with PROFINET CBA / for master or slave	4 000 byte
• data volume / with PROFINET CBA / per connection / maximum	1 400 byte
performance data / PROFINET CBA / remote interconnection / with acyclic transfer / header	
— update time / of the remote interconnections / in the case of acyclic transmission / with PROFINET CBA	500 ms
— number of remote connections to input variables / in the case of acyclic transmission / with PROFINET CBA / maximum	100
— number of remote connections to output variables / in the case of acyclic transmission / with PROFINET CBA / maximum	100
— data volume / as user data for remote interconnections with input variables / in the case of acyclic transmission / with PROFINET CBA	2 000 byte
— data volume / as user data for remote interconnections with output variables / in the case of acyclic transmission / with PROFINET CBA	2 000 byte
— data volume / as user data for remote interconnections / in the case of acyclic transmission / with PROFINET CBA / per connection / maximum	1 400 byte
performance data / PROFINET CBA / remote interconnection / with cyclic transfer / header	
— update time / of the remote interconnections / with cyclical transfer / with PROFINET CBA	1 ms
— number of remote connections to input variables / with PROFINET CBA / with cyclic transfer / maximum	200
— number of remote connections to output variables / with cyclical transfer / with PROFINET CBA / maximum	200
— data volume / as user data for remote interconnections with input variables / with cyclical transfer / with PROFINET CBA / maximum	2 000 byte
— data volume / as user data for remote interconnections with output variables / with cyclical transfer / with PROFINET CBA / maximum	2 000 byte
— data volume / as user data for remote interconnections / with cyclical transfer / with PROFINET CBA / per connection / maximum	450 byte
performance data / PROFINET CBA / HMI variables via PROFINET / acyclic / header	
— number of connectable HMI stations / for HMI variables / in the case of acyclic transmission / with PROFINET CBA	3; 2x PN OPC/1x iMap
— update time / of the HMI variables / in the case of acyclic transmission / with PROFINET CBA	500 ms
— number of HMI variables / in the case of acyclic transmission / with PROFINET CBA / maximum	200
— data volume / as user data for HMI variables / in the case of acyclic transmission / with PROFINET CBA / maximum	2 000 byte
performance data / PROFINET CBA / PROFIBUS proxy functionality / header	
— product function / with PROFINET CBA / PROFIBUS proxy functionality	Yes
— number of coupled PROFIBUS devices / with PROFIBUS functionality	16
— data volume / with PROFIBUS proxy functionality / with PROFINET CBA / per connection / maximum	240 byte; Slave-dependent

Number of connections	
<ul style="list-style-type: none"> ● overall ● usable for PG communication <ul style="list-style-type: none"> — reserved for PG communication — adjustable for PG communication, min. — adjustable for PG communication, max. ● usable for OP communication <ul style="list-style-type: none"> — reserved for OP communication — adjustable for OP communication, min. — adjustable for OP communication, max. ● usable for S7 basic communication <ul style="list-style-type: none"> — reserved for S7 basic communication — adjustable for S7 basic communication, min. — adjustable for S7 basic communication, max. ● usable for routing 	<p>16</p> <p>15</p> <p>1</p> <p>1</p> <p>15</p> <p>15</p> <p>1</p> <p>1</p> <p>15</p> <p>14</p> <p>0</p> <p>0</p> <p>14</p> <p>X1 as MPI: max. 10; X1 as DP master: max. 24; X1 as DP slave (active): max. 14; X2 as PROFINET: 24 max.</p>
S7 message functions	
Number of login stations for message functions, max.	16; Depending on the configured connections for PG/OP and S7 basic communication
Process diagnostic messages	Yes
simultaneously active Alarm-S blocks, max.	300
Test commissioning functions	
Status block	Yes; Up to 2 simultaneously
Single step	Yes
Number of breakpoints	4
Status/control	
<ul style="list-style-type: none"> ● Status/control variable ● Variables ● Number of variables, max. <ul style="list-style-type: none"> — of which status variables, max. — of which control variables, max. 	<p>Yes</p> <p>Inputs, outputs, memory bits, DB, times, counters</p> <p>30</p> <p>30</p> <p>14</p>
Forcing	
<ul style="list-style-type: none"> ● Forcing ● Forcing, variables ● Number of variables, max. 	<p>Yes</p> <p>I/O</p> <p>10</p>
Diagnostic buffer	
<ul style="list-style-type: none"> ● present ● Number of entries, max. <ul style="list-style-type: none"> — adjustable — preset 	<p>Yes</p> <p>500; Only the last 100 entries are retentive at power on/off</p> <p>No</p> <p>10</p>
Potential separation	
between backplane bus and electronics	No
between backplane bus and all other circuit components	Yes
between supply and all other circuits	Yes
Isolation	
Isolation tested with	In general, 707 V DC (type test), Ethernet interface 1 500 V AC (for P1 and P2 on CM, for P3 on IM)
Degree and class of protection	
IP degree of protection	IP65/67
Standards, approvals, certificates	
CE mark	Yes
CSA approval	No
cULus	Yes
FM approval	No
RCM (formerly C-TICK)	Yes
Highest safety class achievable in safety mode	
<ul style="list-style-type: none"> ● Performance level according to ISO 13849-1 ● SIL acc. to IEC 61508 	<p>PLe</p> <p>SIL 3</p>
configuration / header	
Configuration software	
<ul style="list-style-type: none"> ● STEP 7 	Yes; V5.5 or higher

configuration / programming / header	
• Command set	see instruction list
• Nesting levels	8
• System functions (SFC)	see instruction list
• System function blocks (SFB)	see instruction list
Programming language	
— LAD	Yes
— FBD	Yes
— STL	Yes
— SCL	Yes
— CFC	Yes
— GRAPH	Yes
— HiGraph®	Yes
Know-how protection	
• User program protection/password protection	Yes
• Block encryption	Yes; With S7 block Privacy
Dimensions	
Width	135 mm
Height	130 mm
Depth	65 mm; 60 mm without cover for RJ45 socket; 65 mm with cover for RJ45 socket
Weights	
Weight, approx.	720 g

last modified: 4/1/2022 