



Figure similar

SIPLUS ET 200SP CPU 1515SP PC2 L rail based on 6ES7677-2DB40-0GB0 with conformal coating, -40...+60 °C, OT2 with ST1/2 (+70 °C für 10 minutes), 8 GB RAM, 128 GB CFast, Ready4Linux, S7-1500 software controller CPU 1505SP preinstalled, interfaces: 1x slot CFast, 1x slot SD/MMC, 1x connection for ET 200SP BusAdapter PROFINET, 1x 10/100/1000 Mbps Ethernet 2x USB 3.0; 2x USB 2.0, 1x DisplayPort,

General information	
Product type designation	CPU 1515SP PC2 L
Engineering with	
<ul style="list-style-type: none"> <li>STEP 7 TIA Portal configurable/integrated from version</li> </ul>	see entry ID: 109746275
Installed software	
<ul style="list-style-type: none"> <li>Visualization</li> <li>Control</li> </ul>	No S7-1500 Software Controller CPU 1505SP
Configuration control	
via dataset	Yes
Control elements	
Mode selector switch	1
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Mains buffering	
<ul style="list-style-type: none"> <li>Mains/voltage failure stored energy time</li> </ul>	5 ms
Input current	
Current consumption (rated value)	1.8 A; Full processor load, incl. ET 200SP modules and using USB
Current consumption (in no-load operation), typ.	0.5 A
Current consumption, max.	2.9 A
I <sup>2</sup> t	0.426 A <sup>2</sup> ·s; with starting current inrush
Power	
Active power input, max.	55 W; incl. ET 200SP modules and using USB
Infeed power to the backplane bus	8.75 W
Power loss	
Power loss, typ.	4 W
Processor	
Processor type	Intel Atom E3940, 1.6 GHz, 4 cores
Memory	
Type of memory	DDR3L
Main memory	8 GB RAM
CFast memory card	Yes; 128 GB flash memory
SIMATIC memory card required	No
Work memory	
<ul style="list-style-type: none"> <li>integrated (for program)</li> <li>integrated (for data)</li> <li>integrated (for CPU function library of CPU Runtime)</li> </ul>	1 Mbyte 5 Mbyte 20 Mbyte

<b>Load memory</b>	
• integrated (on PC mass storage)	320 Mbyte
<b>Backup</b>	
• with UPS	Yes; all memory areas declared retentive
• with non-volatile memory	Yes
<b>CPU processing times</b>	
for bit operations, typ.	10 ns
for word operations, typ.	12 ns
for fixed point arithmetic, typ.	16 ns
for floating point arithmetic, typ.	64 ns
<b>CPU-blocks</b>	
Number of elements (total)	6 000; In addition to blocks such as DBs, FBs and FCs, UDTs, global constants, etc. are also regarded as elements
<b>DB</b>	
• Number, max.	5 999; Number range: 1 to 65535
• Size, max.	5 Mbyte
<b>FB</b>	
• Number, max.	5 998; Number range: 1 to 65535
• Size, max.	1 024 kbyte
<b>FC</b>	
• Number, max.	5 999; Number range: 1 to 65535
• Size, max.	1 024 kbyte
<b>OB</b>	
• Size, max.	1 024 kbyte
• Number of free cycle OBs	100
• Number of time alarm OBs	20
• Number of delay alarm OBs	20
• Number of cyclic interrupt OBs	20
• Number of process alarm OBs	50
• Number of DPV1 alarm OBs	3
• Number of isochronous mode OBs	1
• Number of technology synchronous alarm OBs	2
• Number of startup OBs	100
• Number of asynchronous error OBs	4
• Number of synchronous error OBs	2
• Number of diagnostic alarm OBs	1
<b>Nesting depth</b>	
• per priority class	24
<b>Counters, timers and their retentivity</b>	
<b>S7 counter</b>	
• Number	2 048
Retentivity	
— adjustable	Yes
<b>IEC counter</b>	
• Number	Any (only limited by the main memory)
Retentivity	
— adjustable	Yes
<b>S7 times</b>	
• Number	2 048
Retentivity	
— adjustable	Yes
<b>IEC timer</b>	
• Number	Any (only limited by the main memory)
Retentivity	
— adjustable	Yes
<b>Data areas and their retentivity</b>	
Retentive data area (incl. timers, counters, flags), max.	410 kbyte; For storage in NVRAM; for storage in mass storage 5 242 020 bytes
<b>Flag</b>	
• Size, max.	16 kbyte
• Number of clock memories	8; 8 clock memory bit, grouped into one clock memory byte
<b>Data blocks</b>	

<ul style="list-style-type: none"> <li>• Retentivity adjustable</li> <li>• Retentivity preset</li> </ul>	<p>Yes</p> <p>No</p>
<b>Local data</b>	
<ul style="list-style-type: none"> <li>• per priority class, max.</li> </ul>	64 kbyte; max. 16 KB per block
<b>Address area</b>	
Number of IO modules	7 473
<b>I/O address area</b>	
<ul style="list-style-type: none"> <li>• Inputs</li> <li>• Outputs</li> </ul>	<p>16 kbyte; All inputs are in the process image</p> <p>16 kbyte; All outputs are in the process image</p>
<b>Subprocess images</b>	
<ul style="list-style-type: none"> <li>• Number of subprocess images, max.</li> </ul>	32
<b>Hardware configuration</b>	
Integrated power supply	Yes
Number of distributed IO systems	20
<b>Number of IO Controllers</b>	
<ul style="list-style-type: none"> <li>• via PC interfaces</li> </ul>	1
<b>Rack</b>	
<ul style="list-style-type: none"> <li>• Modules per rack, max.</li> <li>• Quantity of operable ET 200SP modules, max.</li> <li>• Quantity of operable ET 200AL modules, max.</li> <li>• Number of lines, max.</li> </ul>	<p>64; CPU 1515SP PC + 64 modules + server module</p> <p>64</p> <p>16</p> <p>1</p>
<b>PtP CM</b>	
<ul style="list-style-type: none"> <li>• Number of PtP CMs</li> </ul>	the number of connectable PtP CMs is only limited by the number of available slots
<b>Time of day</b>	
<b>Clock</b>	
<ul style="list-style-type: none"> <li>• Type</li> <li>• Hardware clock (real-time)</li> <li>• Backup time</li> <li>• Deviation per day, max.</li> </ul>	<p>Hardware clock</p> <p>Yes; Resolution: 1 s</p> <p>6 wk; At 40 °C ambient temperature, typically</p> <p>10 s; Typ.: 2 s</p>
<b>Clock synchronization</b>	
<ul style="list-style-type: none"> <li>• supported</li> <li>• to DP, master</li> <li>• on Ethernet via NTP</li> <li>• on Windows clock, slave</li> </ul>	<p>Yes</p> <p>No</p> <p>Yes</p> <p>No</p>
<b>Interfaces</b>	
Number of industrial Ethernet interfaces	2
Number of PROFINET interfaces	1
Number of USB interfaces	4; 2x USB 2.0, 2x USB 3.0 on front side
Number of SD card slots	1
<b>Video interfaces</b>	
<ul style="list-style-type: none"> <li>• Graphics interface</li> </ul>	1x DisplayPort
<b>1. Interface</b>	
Interface type	PROFINET
automatic detection of transmission rate	Yes
Autonegotiation	Yes
Autocrossing	Yes
Number of connections	88
<b>Interface types</b>	
<ul style="list-style-type: none"> <li>• RJ 45 (Ethernet) <ul style="list-style-type: none"> <li>— Transmission rate, max.</li> <li>— Industrial Ethernet status LED</li> </ul> </li> <li>• Number of ports</li> <li>• integrated switch</li> <li>• BusAdapter (PROFINET)</li> </ul>	<p>Yes; Via BusAdapter BA 2x RJ45</p> <p>100 Mbit/s</p> <p>Yes</p> <p>2</p> <p>Yes</p> <p>Yes; Compatible BusAdapter: BA 2x RJ45, BA 2x FC, BA 2x SCRJ (from FS03, V2.2), BA SCRJ / RJ45 (from FS03, V3.1), BA SCRJ / FC (from FS03, V3.1), BA 2x LC (from FS03, V3.3), BA LC / RJ45 (from FS03, V3.3), BA LC / FC (from FS03, V3.3)</p>
<b>Protocols</b>	
<ul style="list-style-type: none"> <li>• PROFINET IO Controller</li> <li>• PROFINET IO Device</li> <li>• SIMATIC communication</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p>

• Open IE communication	Yes
• Web server	Yes
<b>PROFINET IO Controller</b>	
<b>Services</b>	
— Isochronous mode	Yes
— shortest clock pulse	500 µs
— IRT	Yes
— PROFINergy	Yes
— Prioritized startup	Yes; max. 32 PROFINET devices; if you want to use the "Prioritized startup" functionality in STEP 7 for the PROFINET interface of the CPU, the CPU and the device must be separated by means of a switch (e.g. SCALANCE X205)
— Number of connectable IO Devices, max.	128
— Of which IO devices with IRT, max.	64
— of which in line, max.	64
— Number of connectable IO Devices for RT, max.	128
— of which in line, max.	128
— Number of IO Devices that can be simultaneously activated/deactivated, max.	8
— IO Devices changing during operation (partner ports), supported	Yes
— Number of IO Devices per tool, max.	8
— Updating times	The minimum value of the update time also depends on communication share set for PROFINET IO, on the number of IO devices, and on the quantity of configured user data
<b>Update time for IRT</b>	
— for send cycle of 500 µs	500 µs to 8 ms
— for send cycle of 1 ms	1 ms to 16 ms
— for send cycle of 2 ms	2 ms to 32 ms
— for send cycle of 4 ms	4 ms to 64 ms
— With IRT and parameterization of "odd" send cycles	Update time = set "odd" send clock (any multiple of 125 µs: 625 µs ... 3 875 µs) minimum cycle time start from 500 µs
<b>Update time for RT</b>	
— for send cycle of 500 µs	500 µs to 256 ms
— for send cycle of 1 ms	1 ms to 512 ms
— for send cycle of 2 ms	2 ms to 512 ms
— for send cycle of 4 ms	4 ms to 512 ms
<b>Address area</b>	
— Inputs, max.	8 kbyte
— Outputs, max.	8 kbyte
<b>PROFINET IO Device</b>	
<b>Services</b>	
— Isochronous mode	No
— shortest clock pulse	500 µs
— IRT	Yes
— PROFINergy	Yes
— Prioritized startup	Yes
— Shared device	Yes
— Number of IO Controllers with shared device, max.	4
— Asset management record	Yes
<b>2. Interface</b>	
Interface type	Integrated Ethernet interface
automatic detection of transmission rate	Yes
Autonegotiation	Yes
Autocrossing	Yes
<b>Interface types</b>	
• RJ 45 (Ethernet)	Yes; Integrated
— Transmission rate, max.	1 000 Mbit/s
— Industrial Ethernet status LED	No
• Number of ports	1
<b>Protocols</b>	
PROFIsafe	No
<b>Number of connections</b>	
• Number of connections, max.	88

• Number of connections reserved for ES/HMI/web	10
• Number of S7 routing paths	No
<b>Redundancy mode</b>	
<b>Media redundancy</b>	
— Switchover time on line break, typ.	200 ms
— Number of stations in the ring, max.	50
<b>SIMATIC communication</b>	
• PG/OP communication	Yes
• S7 routing	No
• S7 communication, as server	Yes
• S7 communication, as client	Yes
• User data per job, max.	64 kbyte; BSEND/BRCV: 64 KB; PUT/GET: 960 bytes
<b>Open IE communication</b>	
• TCP/IP	Yes
— Data length, max.	64 kbyte
• ISO-on-TCP (RFC1006)	Yes
— Data length, max.	64 kbyte
• UDP	Yes
— Data length, max.	2 048 byte
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
<b>Web server</b>	
• HTTP	Yes; Only via PROFINET interface
• HTTPS	Yes; Only via PROFINET interface
<b>OPC UA</b>	
• Runtime license required	Yes; "Small" license required
• OPC UA Client	Yes; Data access (read, write), method call
— Application authentication	Yes
— Security policies	Yes; Available security policies: None, Basic128Rsa15, Basic256Rsa15, Basic256Sha256
— User authentication	Yes; "anonymous" or by user name & password
— Number of connections, max.	10
— Number of nodes of the client interfaces, recommended max.	2 000
— Number of elements for one call of OPC-UA_NodeGetHandleList/OPC-UA_ReadList/OPC-UA_WriteList, max.	300
— Number of elements for one call of OPC-UA_NameSpaceGetIndexList, max.	20
— Number of elements for one call of OPC-UA_MethodGetHandleList, max.	100
— Number of simultaneous calls of the client instructions for session management, per connection, max.	1
— Number of simultaneous calls of the client instructions for data access, per connection, max.	5
— Number of registerable nodes, max.	2 000
— Number of registerable method calls of OPC-UA_MethodCall, max.	100
— Number of inputs/outputs when calling OPC-UA_MethodCall, max.	20
• OPC UA Server	Yes; Data access (read, write, subscribe), runtime license required
— Application authentication	Yes; Available security policies: None, Basic128Rsa15, Basic256Rsa15, Basic256Sha256
— Security policies	Yes; Available security policies: None, Basic128Rsa15, Basic256Rsa15, Basic256Sha256
— User authentication	Yes; "anonymous" or by user name & password
— Number of sessions, max.	48
— Number of accessible variables, max.	100 000
— Number of registerable nodes, max.	20 000
— Number of subscriptions per session, max.	20
— Sampling interval, min.	100 ms
— Publishing interval, min.	200 ms
— Number of server methods, max.	50

— Number of inputs/outputs per server method, max.	20
— Number of monitored items, recommended max.	2 000; for 1 s sampling interval and 1 s send interval
— Number of server interfaces, max.	10
— Number of nodes for user-defined server interfaces, max.	5 000

#### Further protocols

- MODBUS Yes; MODBUS TCP

#### S7 message functions

Number of login stations for message functions, max.	32
Program alarms	Yes
Number of configurable program messages, max.	10 000
Number of simultaneously active program alarms	1 000
• Number of program alarms	1 000
• Number of alarms for system diagnostics	200
• Number of alarms for motion technology objects	160

#### Test commissioning functions

Joint commission (Team Engineering)	Yes; Parallel online access possible for up to 10 engineering systems
Status block	Yes; up to 8 simultaneously
Single step	Yes
Number of breakpoints	8

#### Status/control

- Status/control variable Yes
- Variables Inputs, outputs, memory bits, DB, times, counters
- Number of variables, max.
  - of which status variables, max. 200
  - of which control variables, max. 200

#### Forcing

- Forcing Yes
- Forcing, variables Inputs, outputs
- Number of variables, max. 200

#### Diagnostic buffer

- present Yes
- Number of entries, max. 1 000
  - of which powerfail-proof 300

#### Traces

- Number of configurable Traces 4
- Memory size per trace, max. 512 kbyte

#### Interrupts/diagnostics/status information

##### Diagnostics indication LED

- RUN/STOP LED Yes
- ERROR LED Yes
- MAINT LED Yes

#### Supported technology objects

Motion Control	Yes
• Number of available Motion Control resources for technology objects	2 400
• Required Motion Control resources	
— per speed-controlled axis	40; per axis
— per positioning axis	80; per axis
— per synchronous axis	160; per axis
— per external encoder	80; per external encoder
— per output cam	20; per cam
— per cam track	160; per cam track
— per probe	40; per probe
• Positioning axis	
— Number of positioning axes at motion control cycle of 4 ms (typical value)	15
— Number of positioning axes at motion control cycle of 8 ms (typical value)	30

#### Controller

- PID\_Compact Yes; Universal PID controller with integrated optimization
- PID\_3Step Yes; PID controller with integrated optimization for valves

<ul style="list-style-type: none"> <li>• PID-Temp</li> </ul>	Yes; PID controller with integrated optimization for temperature
Counting and measuring	
<ul style="list-style-type: none"> <li>• High-speed counter</li> </ul>	Yes
<b>Isolation</b>	
Isolation tested with	750 V DC (type test) and according to EN 50155 (routine test)
<b>Standards, approvals, certificates</b>	
<b>Railway application</b>	
<ul style="list-style-type: none"> <li>• EN 50121-3-2</li> </ul>	Yes; EMC for rail vehicles
<ul style="list-style-type: none"> <li>• EN 50121-4</li> </ul>	Yes; EMC for signal and telecommunications systems
<ul style="list-style-type: none"> <li>• EN 50124-1</li> </ul>	Yes; Railway applications - overvoltage category OV2; pollution degree PD2; rated surge voltage UNi = 0.5 kV; UNm = 24 V DC
<ul style="list-style-type: none"> <li>• EN 50125-1</li> </ul>	Yes; Rail vehicles - see ambient conditions
<ul style="list-style-type: none"> <li>• EN 50125-2</li> </ul>	Yes; Stationary electrical equipment - see ambient conditions
<ul style="list-style-type: none"> <li>• EN 50125-3</li> </ul>	Yes; Signal and telecommunications systems - see ambient conditions; vibrations and shocks: Application point outside of tracks (1 m to 3 m away from track)
<ul style="list-style-type: none"> <li>• EN 50155</li> </ul>	Yes; Rail vehicles - temperature class OT2, ST1/ST2, horizontal mounting position
<ul style="list-style-type: none"> <li>• EN 61373</li> </ul>	Yes; Rail vehicles - vibrations and shocks: Category 1 Class A/B
<ul style="list-style-type: none"> <li>• Fire protection acc. to EN 45545-2</li> </ul>	Yes; For proof of conformity, see Service & Support
<b>Ambient conditions</b>	
<b>Ambient temperature during operation</b>	
<ul style="list-style-type: none"> <li>• min.</li> </ul>	-40 °C; = Tmin
<ul style="list-style-type: none"> <li>• max.</li> </ul>	up to 55 °C with max. 64 ET 200SP modules, max. 2x 900 mA USB load and max. 2x 500 mA USB load; up to 60 °C with max. 32 ET 200SP modules and 4x 500 mA USB load; FS06 or higher: up to 70 °C with max. 16 ET 200SP modules, 4x 100 mA USB load and no visualization
<ul style="list-style-type: none"> <li>• horizontal installation, min.</li> </ul>	-40 °C; = Tmin (incl. condensation/frost)
<ul style="list-style-type: none"> <li>• horizontal installation, max.</li> </ul>	70 °C; = Tmax; +85 °C for 10 min (OT4, ST1/ST2 acc. to EN 50155)
<ul style="list-style-type: none"> <li>• vertical installation, min.</li> </ul>	-40 °C; = Tmin
<ul style="list-style-type: none"> <li>• vertical installation, max.</li> </ul>	50 °C; = Tmax; with max. 32 ET 200SP modules and max. 4x 500 mA USB load
<b>Ambient temperature during storage/transportation</b>	
<ul style="list-style-type: none"> <li>• min.</li> </ul>	-40 °C
<ul style="list-style-type: none"> <li>• max.</li> </ul>	70 °C
<b>Altitude during operation relating to sea level</b>	
<ul style="list-style-type: none"> <li>• Installation altitude above sea level, max.</li> </ul>	2 000 m
<ul style="list-style-type: none"> <li>• Ambient air temperature-barometric pressure-altitude</li> </ul>	Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m)
<b>Relative humidity</b>	
<ul style="list-style-type: none"> <li>• With condensation, tested in accordance with IEC 60068-2-38, max.</li> </ul>	100 %; RH incl. condensation / frost (no commissioning in bedewed state), horizontal installation
<b>Vibrations</b>	
<ul style="list-style-type: none"> <li>• Operation, tested according to IEC 60068-2-6</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Transport, tested acc. to IEC 60068-2-6</li> </ul>	Yes
<b>Shock testing</b>	
<ul style="list-style-type: none"> <li>• tested according to IEC 60068-2-6</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• tested according to IEC 60068-2-27</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• tested according to IEC 60068-2-29</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• Storage/transport, tested acc. to IEC 60068-2-27</li> </ul>	Yes
<b>Resistance</b>	
<b>Coolants and lubricants</b>	
<ul style="list-style-type: none"> <li>— Resistant to commercially available coolants and lubricants</li> </ul>	Yes; Incl. diesel and oil droplets in the air
<b>Use in stationary industrial systems</b>	
<ul style="list-style-type: none"> <li>— to biologically active substances according to EN 60721-3-3</li> </ul>	Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request
<ul style="list-style-type: none"> <li>— to chemically active substances according to EN 60721-3-3</li> </ul>	Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
<ul style="list-style-type: none"> <li>— to mechanically active substances according to EN 60721-3-3</li> </ul>	Yes; Class 3S4 incl. sand, dust, *
<ul style="list-style-type: none"> <li>— Against mechanical environmental conditions acc. to EN 60721-3-3</li> </ul>	Yes; Class 3M8 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0//6AG1193-6AB00-0AA0)
<b>Use on land craft, rail vehicles and special-purpose vehicles</b>	
<ul style="list-style-type: none"> <li>— to biologically active substances according to EN 60721-3-5</li> </ul>	Yes; Class 5B2 mold, fungus and dry rot spores (with the exception of fauna); Class 5B3 on request

— to chemically active substances according to EN 60721-3-5	Yes; Class 5C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-5	Yes; Class 5S3 incl. sand, dust; *
— Against mechanical environmental conditions acc. to EN 60721-3-5	Yes; Class 5M2 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0/6AG1193-6AB00-0AA0)
— against mechanical environmental conditions in agriculture acc. to ISO 15003	Yes; Level 1 (Location LE) using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0/6AG1193-6AB00-0AA0)
<b>Usage in industrial process technology</b>	
— Against chemically active substances acc. to EN 60654-4	Yes; Class 3 (excluding trichlorethylene)
— Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04	Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)
<b>Remark</b>	
— Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04	* The supplied plug covers must remain in place over the unused interfaces during operation!
<b>Conformal coating</b>	
<ul style="list-style-type: none"> <li>• Coatings for printed circuit board assemblies acc. to EN 61086</li> <li>• Protection against fouling acc. to EN 60664-3</li> <li>• Electronic equipment on rolling stock acc. to EN 50155</li> <li>• Military testing according to MIL-I-46058C, Amendment 7</li> <li>• Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A</li> </ul>	<p>Yes; Class 2 for high reliability</p> <p>Yes; Type 1 protection</p> <p>Yes; Class PC2 protective coating acc. to EN 50155:2017</p> <p>Yes; Discoloration of coating possible during service life</p> <p>Yes; Conformal coating, Class A</p>
<b>Operating systems</b>	
pre-installed operating system	No
<b>configuration / header</b>	
configuration / programming / header	
Programming language	
— LAD	Yes
— FBD	Yes
— STL	Yes
— SCL	Yes
— CFC	No
— GRAPH	Yes
<b>Know-how protection</b>	
<ul style="list-style-type: none"> <li>• User program protection/password protection</li> <li>• Copy protection</li> <li>• Block protection</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p>
<b>Access protection</b>	
<ul style="list-style-type: none"> <li>• Protection level: Write protection</li> <li>• Protection level: Read/write protection</li> <li>• Protection level: Complete protection</li> </ul>	<p>Yes</p> <p>Yes</p> <p>Yes</p>
<b>programming / cycle time monitoring / header</b>	
<ul style="list-style-type: none"> <li>• lower limit</li> <li>• upper limit</li> </ul>	<p>adjustable minimum cycle time</p> <p>adjustable maximum cycle time</p>
<b>Open Development interfaces</b>	
<ul style="list-style-type: none"> <li>• Size of ODK SO file, max.</li> </ul>	5.8 Mbyte
<b>Peripherals/Options</b>	
SD card	Optionally for additional mass storage
<b>Dimensions</b>	
Width	160 mm
Height	117 mm
Depth	75 mm
<b>Weights</b>	
Weight, approx.	0.83 kg
<b>Other</b>	
Note:	for use in railway applications, also observe the product information "SIPLUS extreme RAIL" A5E37661960A, Online Support article 109736776

last modified:

3/6/2023 