SIEMENS

Data sheet



SIMATIC IPC127E; Atom E3930 (2C/2T), 2 GB RAM; Base version; 2x Ethernet RJ45, 2x USB3.0; without operating system; 32 GB SSD; without mounting accessories

General information	
Product type designation	IPC127E
Installation type/mounting	
Design	Box PC, built-in unit
Supply voltage	
Type of supply voltage	24 V DC
Mains buffering	
Mains/voltage failure stored energy time	5 ms
Processor	
Processor type	Intel Atom E3930, 1.3 GHz, 2 cores
Drives	
SSD	Yes; 32 GB
Memory	
Type of memory	DDR4
Main memory	2 GB RAM
Capacity of main memory, max.	2 Gbyte
Hardware configuration	
Slots	
Number of PCI slots	0
Interfaces	
Number of industrial Ethernet interfaces	2; 2x RJ45 (independent)
Number of PROFINET interfaces	2
USB port	2x USB 3.0
Connection for keyboard/mouse	USB / USB
Video interfaces	
Graphics interface	1x DisplayPort
Industrial Ethernet	
 Industrial Ethernet interface 	2x Ethernet (RJ45)
— 100 Mbps	Yes
— 1000 Mbps	Yes
Protocols	
Protocols (Ethernet)	
• TCP/IP	Yes
Integrated Functions	
Monitoring functions	
 Temperature monitoring 	Yes
 Watchdog 	Yes
Status LEDs	1x power, 3x user
• Fan	No
EMC	

Interference immunity against discharge of static electricity	
Interference immunity against discharge of static	±6 kV contact discharge acc. to IEC 61000-4-2; ±8 kV air discharge acc. to IEC
electricity	61000-4-2
Interference immunity against high-frequency electromagnetic field	Is
Interference immunity against high frequency radiation	10 V/m, 80 MHz to 2 GHz, 80 % AM acc. to IEC 61000-4-3; 3 V/m, 2 GHz to 2.7 GHz, 80 % AM acc. to IEC 61000-4-3; 10 V, 10 kHz to 80 MHz, 80 % AM acc. to IEC 61000-4-6
Interference immunity to cable-borne interference	
Interference immunity on supply cables	± 2 kV (according to IEC 61000-4-4; burst); ± 0.5 kV (according to IEC 61000-4-5; surge pulse/line to line); ± 1 kV (according to IEC 61000-4-5; surge pulse/line to ground)
 Interference immunity on signal cables >30m 	±2 kV acc. to IEC 61000-4-5, surge, length > 30 m
Interference immunity on signal cables < 30m	± 1 kV acc. to IEC 61000-4-4; burst; length < 3 m; ± 2 kV acc. to IEC 61000-4-4; burst; length > 3 m
Interference immunity to magnetic fields	
 Interference immunity to magnetic fields at 50 Hz 	100 A/m; to IEC 61000-4-8
Emission of conducted and non-conducted interference	
• Interference emission via line/AC current cables	EN 61000-6-4:2007 +A1:2011 (industrial environments), EN 61000-6-3:2007 +A1:2011 (residential environments), CISPR 22 Class B, FCC Class A
Degree and class of protection	
IP degree of protection	IP40
Standards, approvals, certificates	
CE mark	Yes
UL approval	Yes
Dust protection	Protection against foreign bodies > 1 mm
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	55 °C
Ambient temperature during storage/transportation	
• min.	-20 °C
• max.	70 °C
Relative humidity	
Relative humidity	5 85 % at 30 °C, no condensation
Vibrations	
 Vibration resistance during operation acc. to IEC 60068- 2-6 	Tested according to IEC 6068-2-6; 5 Hz to 9 Hz: 3.5 mm, 9 Hz to 500 Hz: 9.8 m/s²
Shock testing	
 Shock load during operation 	Tested according to IEC 60068-2-27: 150 m/s², 11 ms
Operating systems	
pre-installed operating system	No
pre-installed operating system	
 Windows 10 Enterprise 	No
Dimensions	
Width	85 mm
Height	85 mm

last modified: 6/2/2022 🖸