

SIMATIC IFP2200 V2 PRO, 22 multi-touch display (16:9) with 1920x1080 pixel resolution, PRO variant support arm, for 24 V DC, DisplayPort, can be placed up to 100 m away HDBaseT, USB on the rear side, neutral design



Figure similar

General information	
Product type designation	IFP2200 V2 PRO
Short designation	Flat Panel 22" PRO multi-touch ext.
Display	
Design of display	TFT widescreen display, LED backlighting
Screen diagonal	21.5 in; 22"
Screen diagonal [cm]	54.6 cm
Display width	476.1 mm
Display height	267.8 mm
On Screen Display (OSD) configuration	No; Adjustable by means of software
Number of colors	16 777 216; 24 bit
Viewing angle	178° x 178°
Resolution (pixels)	
• Image resolution	1 920 x 1 080
• Horizontal image resolution	1 920 pixel
• Vertical image resolution	1 080 pixel
• Pixel size, horizontal	0.248 mm
• Pixel size, vertical	0.248 mm
General features	
• Brightness/contrast	250 cd/m ² / 1 000:1
• non-reflective and tempered mineral glass screen	Yes
• Detachable from computer unit	100 m; HDBaseT protocol
• Luminance	250 cd/m ²
Backlighting	
• Type of backlighting	LED
• MTBF backlighting (at 25 °C)	30 000 h; At 25°C
• Backlight dimmable	Yes; 0-100 %
Control elements	
Control elements	multi-touch screen
Input device	
• Integrated mouse cursor control	Yes; Also externally via USB
Touch operation	
• Design as touch screen	Yes
• Design as multi-touch screen	Yes; Projective-capacitive
• Monitor keyboard	Yes
Installation type/mounting	
Design	Support arm mounting
Front mounting	No
Support arm mounting	Yes

Stand mounting	No
VESA mounting	Yes; With VESA adapter set
maximum permitted forward tilt angle from vertical	45°
maximum permitted backward tilt angle from vertical	45°
Supply voltage	
Type of supply voltage	DC
Rated value (DC)	24 V; PELV / SELV floating
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Input current	
Current consumption (rated value)	1 A
Current consumption, max.	1.3 A
Starting current inrush I ² t	0.5 A ² ·s
Power loss	
Power loss, typ.	24 W
Power loss, max.	31 W
Interfaces	
Number of USB interfaces	2; USB 2.0 type A
USB on the rear	Yes; 2x onboard
Connection for keyboard/mouse	USB
Video interfaces	
• DisplayPort	Yes; Display port V1.2
Touch interfaces	
• USB	Yes
Degree and class of protection	
IP (at the front)	IP65
IP (rear)	IP65
NEMA (front)	
• Enclosure Type 4 at the front	Yes
• Enclosure Type 4x at the front	Yes
Standards, approvals, certificates	
Certificate of suitability	hazardous zone 2/22; shipbuilding
CE mark	Yes
UL approval	Yes
cULus	Yes; Corresponds to UL 508
FM approval	Available soon
RCM (formerly C-TICK)	Yes
EAC (formerly Gost-R)	Yes
EMC	CE, EN 55011, EN 61000-6-4, EN 61000-6-2
Use in hazardous areas	
• ATEX Zone 2	Yes
• ATEX Zone 22	Yes
• IECEx Zone 2	Yes
• IECEx Zone 22	Yes
• FM Class I Division 2	No
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	45 °C
Ambient temperature during storage/transportation	
• min.	-20 °C
• max.	60 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	3 500 m
Relative humidity	
• Operation, max.	95 %; no condensation
Vibrations	
• Vibration load in operation	1 gn
• Vibration load during transport/storage	1 gn
Shock testing	

- Shock load during operation 15 gn
- shock acceleration during storage/transport 15 gn

Mechanics/material

Enclosure material (front)	With neutral design
• Aluminum	Yes
• Aluminum casting	Yes
• Glass	Yes; at front
Enclosure material (rear)	aluminum

Dimensions

Width	527 mm
Height	329 mm; Without basic adapter
Depth	93.7 mm; Without basic adapter
Width of the housing front	527 mm
Height of housing front	329 mm

Weights

Weight (without packaging)	7.6 kg
Weight (with packaging)	8.4 kg

last modified: 5/31/2023 