

product type designation

product description

PROFIBUS M12-Cable

Flexible plug-in cable (2-core), preferred length, preassembled with two 5-pole M12 male/female connectors (B-coded)

PROFIBUS M12 plug-in cable (ET 200), Pre-assembled PB FC Trailing Cable with 2 M12 connectors, B-coded, 5-pole; 3 m.



suitability for use

Cable for connecting PROFIBUS stations (e.g. SIMATIC ET 200) to IP 65 degree of protection

cable designation

02YY (ST) C11Y 1x2x0,65/2,56-150 LI KF 40 FR petrol

wire length

3 m

electrical data

number of electrical connections

2

attenuation factor per length

• at 9.6 kHz / maximum	0.003 dB/m
• at 38.4 kHz / maximum	0.004 dB/m
• at 4 MHz / maximum	0.025 dB/m
• at 16 MHz / maximum	0.049 dB/m

impedance

• rated value	150 Ω
• at 9.6 kHz	270 Ω
• at 38.4 kHz	185 Ω
• at 3 MHz ... 20 MHz	150 Ω

relative symmetrical tolerance

• of the characteristic impedance at 9.6 kHz	10 %
• of the characteristic impedance at 38.4 kHz	10 %
• of the characteristic impedance at 3 MHz ... 20 MHz	10 %

loop resistance per length / maximum

133 mΩ/m

shield resistance per length / maximum

14 Ω/km

capacity per length / at 1 kHz

28 pF/m

operating voltage

• RMS value	80 V
-------------	------

mechanical data

number of electrical cores

2

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

type of electrical connection / FastConnect

Yes

outer diameter

• of inner conductor	0.67 mm
• of the wire insulation	2.56 mm
• of the inner sheath of the cable	5.4 mm
• of cable sheath	8 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.4 mm

material

• of the wire insulation	polyethylene (PE)
--------------------------	-------------------

• of the inner sheath of the cable • of cable sheath	PVC PUR (TPE-U)
color	
• of the insulation of data wires • of cable sheath	red/green petrol
bending radius	
• with single bend / minimum permissible • with continuous bending	40 mm 120 mm
number of bending cycles	3000000; Drag chain suitable for 3 million bending cycles at a bending radius of 120 mm (15x D) and an acceleration of 4 m/s ²
tensile load / maximum	100 N
weight per length	77 kg/km
ambient conditions	
ambient temperature	
• during operation • during storage • during transport • during installation • note	-40 ... +60 °C -40 ... +60 °C -40 ... +60 °C -40 ... +60 °C Electrical properties measured at 20 °C, tests according to DIN 47250 part 4 respectively DIN VDE 0472
ambient condition / for operation	Limited segment length (see manual for PROFIBUS networks)
fire behavior	flame resistant according to IEC 60332-1-2
chemical resistance	
• to mineral oil • to grease • to water	oil resistant according to IEC 60811-2-1 (7x24h/90°C) resistant conditional resistance
radiological resistance / to UV radiation	resistant
protection class IP	IP65, IP67
product features, product functions, product components / general	
product feature	
• halogen-free • silicon-free	No Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; CMX
UL/ETL style / 600 V Rating	No
certificate of suitability	
• EAC approval • CE marking • RoHS conformity	Yes Yes Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • Det Norske Veritas (DNV) • Germanische Lloyd (GL) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS)	No No No No No No No
reference code	
• according to IEC 81346-2 • according to IEC 81346-2:2019	WG WGB
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Selection guide for cables and connectors • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter https://sie.ag/2QdlxcP http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com
last modified:	12/31/2021 

