SIEMENS

Data sheet 6XV1830-3DN15

product type designation	**PROFIBUS M12-Cable**
product description	Flexible plug-in cable (2-core), preferred length, preassembled with two 5-pole M12 male/female connectors (B-coded)
	PROFIBUS M12 plug-in cable (ET 200) Pre-assembled PB FC Trailing Cable with 2 M12 connectors, B-coded, 5-pole; 15 m.



suitability for use	Cable for connecting PROFIBUS stations (e.g. SIMATIC ET 200) to IP 65 degree of protection
cable designation	02YY (ST) C11Y 1x2x0,65/2,56-150 LI KF 40 FR petrol
wire length	15 m
electrical data	
number of electrical connections	2
attenuation factor per length	
● at 9.6 kHz / maximum	0.003 dB/m
● at 38.4 kHz / maximum	0.004 dB/m
● at 4 MHz / maximum	0.025 dB/m
● at 16 MHz / maximum	0.049 dB/m
impedance	
● rated value	150 Ω
● at 9.6 kHz	270 Ω
● at 38.4 kHz	185 Ω
● at 3 MHz … 20 MHz	150 Ω
relative symmetrical tolerance	
● of the characteristic impedance at 9.6 kHz	10 %
● of the characteristic impedance at 38.4 kHz	10 %
● of the characteristic impedance at 3 MHz … 20 MHz	10 %
loop resistance per length / maximum	133 mΩ/m
shield resistance per length / maximum	14 Ω/km
capacity per length / at 1 kHz	28 pF/m
operating voltage	
● RMS value	80 V
mechanical data	
number of electrical cores	2
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires
type of electrical connection / FastConnect	Yes
outer diameter	
● of inner conductor	0.67 mm
● of the wire insulation	2.56 mm
● of the inner sheath of the cable	5.4 mm
● of cable sheath	8 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.4 mm
material	
● of the wire insulation	polyethylene (PE)

Subject to change without notice
© Copyright Siemens

● of the inner sheath of the cable	PVC
● of cable sheath	PUR (TPE-U)
color	
● of the insulation of data wires	red/green
● of cable sheath	petrol
bending radius	
● with single bend / minimum permissible	40 mm
● with continuous bending	120 mm
number of bending cycles	3000000; Drag chain suitable for 3 million bending cycles at a bending radius of 120 mm (15x D) and an acceleration of 4 m/s²
tensile load / maximum	100 N
weight per length	77 kg/km
ambient conditions	
ambient temperature	
● during operation	-40 ... +60 °C
● during storage	-40 ... +60 °C
● during transport	-40 ... +60 °C
● during installation	-40 ... +60 °C
● note	Electrical properties measured at 20 °C, tests according to DIN 47250 part 4 respectively DIN VDE 0472
ambient condition / for operation	Limited segment length (see manual for PROFIBUS networks)
fire behavior	flame resistant according to IEC 60332-1-2
chemical resistance	
● to mineral oil	oil resistant according to IEC 60811-2-1 (7x24h/90°C)
● to grease	resistant
● to water	conditional resistance
radiological resistance / to UV radiation	resistant
protection class IP	IP65, IP67
product features, product functions, product components / general	
product feature	
● halogen-free	No
● silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; CMX
UL/ETL style / 600 V Rating	No
certificate of suitability	
● EAC approval	Yes
● CE marking	Yes
● RoHS conformity	Yes
Marine classification association	
● American Bureau of Shipping Europe Ltd. (ABS)	No
● French marine classification society (BV)	No
● Det Norske Veritas (DNV)	No
● Germanische Lloyd (GL)	No
● Lloyds Register of Shipping (LRS)	No
● Nippon Kaiji Kyokai (NK)	No
● Polski Rejestr Statkow (PRS)	No
reference code	
● according to IEC 81346-2	WG
● according to IEC 81346-2:2019	WGB
further information / internet links	
internet link	
● to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
● to website: Industrial communication	http://www.siemens.com/simatic-net
● to website: Industry Mall	https://mall.industry.siemens.com
● to website: Information and Download Center	http://www.siemens.com/industry/infocenter
● to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
● to website: Image database	http://automation.siemens.com/bilddb
● to website: CAx-Download-Manager	http://www.siemens.com/cax
● to website: Industry Online Support	https://support.industry.siemens.com
last modified:	12/31/2021

Subject to change without notice
© Copyright Siemens

Subject to change without notice
© Copyright Siemens