

product type designation

product description

IE Connecting Cable M12-180/M12-180

Flexible plug-in cable (4-wire), preferred length, prefabricated with two 4-pole M12 connectors (D-coded, 180° cable outlet)

Industrial Ethernet connecting Cable M12-180/M12-180, pre-assembled IE FC Trailing cable GP, with 2 M12 plugs (D-coded) length 10.0 m.



suitability for use

For connecting Industrial Ethernet stations (e.g. SIMATIC ET200 and SCALANCE XP-200) in IP 65/67 degree of protection

cable designation

2YY (ST) CY 2x2x0,75/1,5-100 LI GN

wire length

10 m

electrical data

number of electrical connections

2

attenuation factor per length

- at 10 MHz / maximum
- at 100 MHz / maximum

0.063 dB/m
0.213 dB/m

impedance

- at 1 MHz ... 100 MHz

100 Ω

relative symmetrical tolerance

- of the characteristic impedance at 1 MHz ... 100 MHz

5 %

near-end crosstalk per length

- at 1 MHz ... 100 MHz

0.5 dB/m

transfer impedance per length / at 10 MHz

20 mΩ/m

loop resistance per length / maximum

120 mΩ/m

operating voltage

- RMS value

80 V

NVP value in percent

66 %

mechanical data

number of electrical cores

4

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

core diameter

- of AWG22 insulated conductor

0.75 mm

outer diameter

- of inner conductor
- of the wire insulation
- of the inner sheath of the cable
- of cable sheath

0.75 mm
1.5 mm
3.9 mm
6.5 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.2 mm

material

- of the wire insulation
- of the inner sheath of the cable
- of cable sheath

polyethylene (PE)
PVC
PVC

color

- of the insulation of data wires

white/yellow/blue/orange

• of cable sheath	green
bending radius	
• with single bend / minimum permissible	32.5 mm
• with multiple bends / minimum permissible	49 mm
• with continuous bending	100 mm
number of bending cycles	3000000; Drag chain suitable for 3 million bending cycles at a bending radius of 100 mm, a speed of 4 m/s and an acceleration of 4 m/s ²
tensile load / maximum	150 N
weight per length	68 kg/km
plug	
type of plug interlock	screwed
connector coding	
• of the M12 circular connector	D-coded
ambient conditions	
ambient temperature	
• during operation	-25 ... +75 °C
• during storage	-25 ... +75 °C
• during transport	-25 ... +75 °C
• during installation	-10 ... +60 °C
• note	Electrical properties measured at 20 °C, tests according to DIN VDE 0472
fire behavior	flame resistant according to UL 1685 (CSA FT 4)
chemical resistance	
• to mineral oil	conditional resistance
• to grease	Conditional resistance
radiological resistance / to UV radiation	resistant
protection class IP	IP65, IP67
product features, product functions, product components / general	
product feature	
• halogen-free	No
• silicon-free	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us, CMG FT4 / (ETL)us PLTC / Sun Res / OIL RES
UL/ETL style / 600 V Rating	Yes; cRUus AWM 21694 AWM I A/B 60°C 600V FT2
certificate of suitability	
• EAC approval	Yes
• CE marking	Yes
• RoHS conformity	Yes
standard for structured cabling	Cat5e
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• Det Norske Veritas (DNV)	No
• Germanische Lloyd (GL)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
• Polski Rejestr Statkow (PRS)	No
reference code	
• according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAX-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

2/3/2023 

