


product type designation

product description



PROFIBUS FC Standard Cable GP

Standard bus cable (2 wires), preferred length, not assembled

PROFIBUS FC Standard, bus cable 2-wire, shielded, special configuration for Quick assembly 50 m.

suitability for use

Standard cable specially designed for fast, permanent installation

cable designation

02YSY (ST) CY 1x2x0,64/2,55-150 VI KF 40 FR

wire length

50 m

electrical data

attenuation factor per length

• at 9.6 kHz / maximum	0.0025 dB/m
• at 38.4 kHz / maximum	0.004 dB/m
• at 4 MHz / maximum	0.022 dB/m
• at 16 MHz / maximum	0.042 dB/m

impedance

• rated value	150 Ω
• at 9.6 kHz	270 Ω
• at 38.4 kHz	185 Ω
• at 3 MHz ... 20 MHz	150 Ω

relative symmetrical tolerance

• of the characteristic impedance at 9.6 kHz	10 %
• of the characteristic impedance at 38.4 kHz	10 %
• of the characteristic impedance at 3 MHz ... 20 MHz	10 %

loop resistance per length / maximum

110 mΩ/m

shield resistance per length / maximum

9.5 Ω/km

capacity per length / at 1 kHz

28.5 pF/m

operating voltage

• RMS value	100 V
-------------	-------

mechanical data

number of electrical cores

2

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

type of electrical connection / FastConnect

Yes

outer diameter

• of inner conductor	0.65 mm
• of the wire insulation	2.55 mm
• of the inner sheath of the cable	5.4 mm
• of cable sheath	8 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.4 mm

material

• of the wire insulation	polyethylene (PE)
• of the inner sheath of the cable	PVC
• of cable sheath	PVC

color	
• of the insulation of data wires • of cable sheath	red/green Violet
bending radius	
• with single bend / minimum permissible • with multiple bends / minimum permissible	37.5 mm 75 mm
tensile load / maximum	100 N
weight per length	78 kg/km
ambient conditions	
ambient temperature	
• during operation • during storage • during transport • during installation • note	-40 ... +75 °C -40 ... +75 °C -40 ... +75 °C -40 ... +75 °C Electrical properties measured at 20 °C, tests according to DIN 47250 part 4 respectively DIN VDE 0472
fire behavior	flame resistant according to IEC 60332-3-24 (Category C) and UL 1685 (CSA FT 4)
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
• to mineral oil • to grease • to water	oil resistant according to IEC 60811-2-1 (4 h / 70°C) Conditional resistance conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
• halogen-free • silicon-free	No Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us, CMG / (ETL)us CL3 / Sun Res
UL/ETL style / 600 V Rating	Yes; cRUus AWM 21694 AWM I A/B 60°C 600V FT2
certificate of suitability	
• EAC approval • CE marking • UL approval • RoHS conformity	Yes Yes Yes Yes
Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • Det Norske Veritas (DNV) • Germanische Lloyd (GL) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS)	No No No No No No No
reference code	
• according to IEC 81346-2 • according to IEC 81346-2:2019	WG WGB
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Selection guide for cables and connectors • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter https://sie.ag/2QdlxcP http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified:

10/30/2021 