


product description



Flexible bus cable (4-core), sold by the meter, unassembled

Industrial Ethernet FC TP FOOD GP cable 2x2 (PROFINET Type C), TP installation cable for use in the food and beverages and tobacco industry, 4-core CAT5E, sold by the meter; delivery unit max. 1000 m, minimum order quantity: 20 m.

suitability for use	Food and beverages industry
cable designation	2YH (ST) C2Y 2X2X0,75/1,5-100 LI SF/UTP
electrical data	
attenuation factor per length	
• at 10 MHz / maximum	0.063 dB/m
• at 100 MHz / maximum	0.213 dB/m
impedance	
• at 1 MHz ... 100 MHz	100 Ω
relative symmetrical tolerance	
• of the characteristic impedance at 1 MHz ... 100 MHz	5 %
near-end crosstalk per length	
• at 1 MHz ... 100 MHz	0.5 dB/m
transfer impedance per length / at 10 MHz	10 mΩ/m
loop resistance per length / maximum	120 mΩ/m
operating voltage	
• RMS value	80 V
NVP value in percent	66 %
mechanical data	
number of electrical cores	4
design of the shield	Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires
type of electrical connection / FastConnect	Yes
core diameter	
• of AWG22 insulated conductor	0.75 mm
outer diameter	
• of inner conductor	0.75 mm
• of the wire insulation	1.5 mm
• of the inner sheath of the cable	3.9 mm
• of cable sheath	6.5 mm
symmetrical tolerance of the outer diameter / of cable sheath	0.2 mm
material	
• of the wire insulation	polyethylene (PE)
• of the inner sheath of the cable	FRNC
• of cable sheath	PE
color	
• of the insulation of data wires	white/yellow/blue/orange
• of cable sheath	Black
bending radius	
• with single bend / minimum permissible	20 mm

<ul style="list-style-type: none"> with multiple bends / minimum permissible 	49 mm
tensile load / maximum	150 N
weight per length	55 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport during installation note 	-40 ... +75 °C -50 ... +75 °C -50 ... +75 °C -20 ... +60 °C Electrical properties measured at 20 °C, tests according to DIN VDE 0472
fire behavior	inflammable
class of burning behaviour / according to EN 13501-6	Fca
chemical resistance	
<ul style="list-style-type: none"> to mineral oil to grease to water 	oil resistant according to IEC 60811-2-1 (4 h / 70°C) Conditional resistance conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free silicon-free 	Yes Yes
wire length / for Industrial Ethernet	
<ul style="list-style-type: none"> with 100BaseTX 	100 m
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	No
certificate of suitability	
<ul style="list-style-type: none"> EAC approval CE marking RoHS conformity 	Yes Yes Yes
standard for structured cabling	Cat5e
Marine classification association	
<ul style="list-style-type: none"> American Bureau of Shipping Europe Ltd. (ABS) French marine classification society (BV) Det Norske Veritas (DNV) Germanische Lloyd (GL) Lloyds Register of Shipping (LRS) Nippon Kaiji Kyokai (NK) Polski Rejestr Statkow (PRS) 	No No No No No No No
reference code	
<ul style="list-style-type: none"> according to IEC 81346-2 according to IEC 81346-2:2019 	WG WGB
further information / internet links	
internet link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool to website: Industrial communication to website: Industry Mall to website: Information and Download Center to website: Selection guide for cables and connectors to website: Image database to website: CAx-Download-Manager to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter https://sie.ag/2QdlxcP http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com
last modified:	2/9/2022 