



SIVACON S4 mounting plate 3VL6 up to 800A 4-pole withdraw. H: 600mm W: 600mm D: 600 800mm

Model	
product brand name	SIVACON S4
product designation	3VL assembly kit
design of the product	VL800
design of the surface	galvanized
Appearance	
RAL color number	other
color	miscellaneous
Product details	
product component top plate	No
Mechanical Design	
height	600 mm
width	600 mm
depth	600 mm
length	600 mm
material thickness of the plate	2 mm
net weight	8 kg
material	metal
General Product Approval	
Declaration of Conformity	

[Confirmation](#)



[Miscellaneous](#)



[Miscellaneous](#)

Declaration of Conformity



EG-Konf.



Marine / Shipping



DNV

other

[Miscellaneous](#)

[Confirmation](#)

Environment

[Environmental Confirmations](#)

### Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ6000-3BA88>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ6000-3BA88>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8PQ6000-3BA88](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ6000-3BA88)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

---

last modified:

1/21/2023 

