



Figure similar

SIMATIC DP, electronic module for ET200iSP, 4 DQ, 17.4 V DC/40 mA "H"-shutdown, Ex ib (ia Ga) IIC T4 Gb, Ex ib [ia IIIC Da] IIC T4 Gb, Ex ib [ia] I Mb

General information	
Product type designation	4DQ 17.4 V DC/40 mA
Input current	
Current consumption, typ.	380 mA
from load voltage L+ (without load), max.	400 mA
Power loss	
Power loss, typ.	2.8 W
Address area	
Address space per module	
• Address space per module, max.	2 byte
Digital outputs	
Type of digital output	Transistor
Number of digital outputs	4; additionally 1 intrinsically-safe input for H shutdown
Short-circuit protection	Yes
No-load voltage U _{ao} (DC)	17.4 V
Internal resistor R _i	167 Ω
Trend key points E	
• Voltage U _e (DC)	10.7 V
• Current I _e	40 mA; 80 mA when outputs connected in parallel
Output current	
• for signal "1" rated value	0.04 A
Output delay with resistive load	
• "0" to "1", max.	2 ms
• "1" to "0", max.	1.5 ms
Parallel switching of two outputs	
• for uprating	Yes
Switching frequency	
• with resistive load, max.	100 Hz
• with inductive load, max.	2 Hz
Cable length	
• shielded, max.	500 m
• unshielded, max.	500 m
Interrupts/diagnostics/status information	
Alarms	
• Diagnostic alarm	Yes; Parameterizable
Diagnoses	
• Diagnostic information readable	Yes
• Wire-break	Yes; R > 10 kohms, I < 100 μA
• Short-circuit	Yes; R < 80 Ohm (one output), R < 40 Ohm (outputs connected in parallel)

Diagnostics indication LED	
• Group error SF (red)	Yes
• Status indicator digital output (green)	Yes; Per channel
Ex(i) characteristics	
maximum values for connecting terminals for gas group IIC	
• U _o (no-load voltage), max.	19.4 V
• I _o (short-circuit current), max.	118 mA
• P _o (power output), max.	572 mW
• C _o (permissible external capacity), max.	241 nF; For IIC, 1507 nF for IIB
• L _o (permissible external inductivity), max.	1.7 mH; For IIC, 10.4 mH for IIB
Potential separation	
Potential separation digital outputs	
• between the channels	No
• between the channels and backplane bus	Yes
• Between the channels and load voltage L+	Yes
Permissible potential difference	
between different circuits	60 V DC/30 V AC
Standards, approvals, certificates	
CE mark	Yes
Highest safety class achievable in safety mode	
• SIL acc. to IEC 61508	No
Dimensions	
Width	30 mm
Height	129 mm
Depth	136.5 mm
Weights	
Weight, approx.	255 g
last modified:	3/16/2021 