



SIPLUS HCS4200 CIM4210C central interface module compact version with PROFINET communication und 2 slots for holding 2 POM4220

General information	
Product type designation	CIM4210C PROFINET
Installation type/mounting	
Mounting type	Backplane mounting
Mounting position	vertical
Type of ventilation	Self-ventilation
Supply voltage	
Type of supply voltage	DC
Rated value (DC)	24 V
relative symmetrical tolerance of the supply voltage	20 %
Connection method	
<ul style="list-style-type: none"> • Design of electrical connection for supply voltage <ul style="list-style-type: none"> — Connectable conductor cross-sections, solid — Connectable conductor cross-sections, finely stranded with wire end processing — Connectable conductor cross-sections for AWG cables 	plug, 2x 2-pole with spring-type terminal, push-in 1x (0.2 ... 2.5 mm ²) 1x (0.2 ... 2.5 mm ²) 1x (26 ... 12)
Power	
Active power input	8 W
Hardware configuration	
Type of power output connectable	POM4220
Slots	
<ul style="list-style-type: none"> • Number of slots 	2; POM4220
Interfaces	
Interfaces/bus type	PROFINET IO
Transmission rate, max.	100 Mbit/s
Supports protocol for PROFINET IO	
<ul style="list-style-type: none"> • Design of electrical connection of PROFINET interface 	2x RJ45
Protocols	
Supports protocol for PROFINET IO	Yes
PROFIBUS DP	No
EtherNet/IP	No
Interrupts/diagnostics/status information	
Number of status displays	3
LED status display	LED green = ready, LED yellow = heating on/off, LED red = error display
Isolation	
Overvoltage category	III
Degree of pollution	2
EMC	
EMC interference emission	Limit value in accordance with IEC 61000-6-4:2007 + A1:2011

Electrostatic discharge acc. to IEC 61000-4-2	4 kV contact discharging, 8 kV air discharging
Field-related interference acc. to IEC 61000-4-3	10 V/m (80 ... 1 000 MHz), 3 V/m (1.4 ... 2.0 GHz), 1 V/m (2.0 ... 2.7 GHz)
Conducted interference due to burst acc. to IEC 61000-4-4	2 kV power supply lines, 2 kV PROFINET cables
Conducted interference due to surge acc. to IEC 61000-4-5	DC supply lines: 0.5 kV symmetric and unsymmetric PROFINET cables: 1 kV unsymmetric
Conducted interference due to high-frequency radiation acc. to IEC 61000-4-6	10 V (0.15 ... 80 MHz)
Degree and class of protection	
IP degree of protection	IP20
Standards, approvals, certificates	
CE mark	Yes
UL approval	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
EAC (formerly Gost-R)	Yes
China RoHS compliance	Yes
reference designation according to IEC 81346-2 (2009)	K
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	55 °C
Ambient temperature during storage/transportation	
• Storage, min.	-25 °C
• Storage, max.	70 °C
• Transportation, min.	-25 °C
• Transportation, max.	70 °C
Air pressure acc. to IEC 60068-2-13	
• Operation, min.	860 hPa
• Operation, max.	1 080 hPa
• Storage, min.	660 hPa
• Storage, max.	1 080 hPa
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	2 000 m
Relative humidity	
• Operation at 25 °C, max.	95 %
• Operation at 50 °C, max.	50 %; 95 % at 25 °C, decreasing linearly to 50 % at 50 °C
Vibrations	
• Vibration resistance during operation acc. to IEC 60068-2-6	10 ... 58 Hz / 0.075 mm, 58 ... 150 Hz / 1 g
• Vibration resistance during storage acc. to IEC 60068-2-6	5 ... 8.5 Hz / 3.5 mm, 8.5 ... 500 Hz / 1 g
Shock testing	
• Shock resistance during operation acc. to IEC 60068-2-27	15 g / 11 ms / 3 shocks/axis
• Shock resistance during storage acc. to IEC 60068-2-29	25 g / 6 ms / 1 000 shocks/axis
Dimensions	
Width	104 mm
Height	339 mm
Depth	296 mm

last modified: 10/18/2021 