



SIPLUS ET 200SP DI 16x24VDC ST TX rail based on 6ES7131-6BH01-0BA0 with conformal coating, -40...+70 °C, OT4 with ST1/2 (+85 °C for 10 minutes), digital input module, suitable for BU type A0, color code CC00, input type 3 (IEC 61131), sink input, (PNP, sinking input), input delay 0.05..20 ms module diagnostics for: wire break, supply voltage

General information	
Product type designation	DI 16x24VDC ST
Firmware version	
• FW update possible	No
usable BaseUnits	BU type A0
Color code for module-specific color identification plate	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Operating mode	
• DI	Yes
• Counter	No
• Oversampling	No
• MSI	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	90 mA
Encoder supply	
24 V encoder supply	
• 24 V	No
Power loss	
Power loss, typ.	1.7 W
Address area	
Address space per module	
• Inputs	2 byte; + 2 bytes for QI information
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
Submodules	
• Number of configurable submodules, max.	4
Selection of BaseUnit for connection variants	
• 1-wire connection	BU type A0
• 2-wire connection	BU type A0 + Potential distributor module
• 3-wire connection	BU type A0 + Potential distributor module
• 4-wire connection	BU type A0 + Potential distributor module
Digital inputs	

Number of digital inputs	16
Digital inputs, parameterizable	Yes
Source/sink input	P-reading
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Input voltage	
<ul style="list-style-type: none"> • Rated value (DC) • for signal "0" • for signal "1" 	24 V -30 to +5 V +11 to +30V
Input current	
<ul style="list-style-type: none"> • for signal "1", typ. 	2.5 mA
Input delay (for rated value of input voltage)	
for standard inputs	
<ul style="list-style-type: none"> — parameterizable — at "0" to "1", min. — at "0" to "1", max. — at "1" to "0", min. — at "1" to "0", max. 	Yes; 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms (in each case + delay of 30 to 500 µs, depending on line length) 0.05 ms 20 ms 0.05 ms 20 ms
Cable length	
<ul style="list-style-type: none"> • shielded, max. • unshielded, max. 	1 000 m 600 m
Encoder	
Connectable encoders	
<ul style="list-style-type: none"> • 2-wire sensor — permissible quiescent current (2-wire sensor), max. 	Yes 1.5 mA
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
<ul style="list-style-type: none"> • Diagnostic alarm 	Yes
Diagnoses	
<ul style="list-style-type: none"> • Diagnostic information readable • Monitoring the supply voltage — parameterizable • Monitoring of encoder power supply • Wire-break • Short-circuit • Group error 	Yes Yes Yes No Yes; Module-by-module, optional protective circuit for preventing wire-break diagnostics in the case of simple encoder contacts: 25 kOhm to 45 kOhm No Yes
Diagnostics indication LED	
<ul style="list-style-type: none"> • Monitoring of the supply voltage (PWR-LED) • Channel status display • for channel diagnostics • for module diagnostics 	Yes; green PWR LED Yes; green LED No Yes; green/red DIAG LED
Potential separation	
Potential separation channels	
<ul style="list-style-type: none"> • between the channels • between the channels and backplane bus • between the channels and the power supply of the electronics 	No Yes No
Isolation	
Isolation tested with	750 V DC (type test) and according to EN 50155 (routine test)
Standards, approvals, certificates	
Suitable for safety functions	No
Railway application	
<ul style="list-style-type: none"> • EN 50121-3-2 • EN 50121-4 • EN 50124-1 • EN 50125-1 • EN 50125-2 • EN 50125-3 	Yes; EMC for rail vehicles Yes; EMC for signal and telecommunications systems Yes; Railway applications - overvoltage category OV2; pollution degree PD2; rated surge voltage UNi = 0.5 kV; UNm = 24 V DC Yes; Rail vehicles - see ambient conditions Yes; Stationary electrical equipment - see ambient conditions Yes; Signal and telecommunications systems - see ambient conditions; vibrations and shocks: Application point outside of tracks (1 m to 3 m away)

<ul style="list-style-type: none"> • EN 50155 • EN 61373 • Fire protection acc. to EN 45545-2 	<p>from track)</p> <p>Yes; Rail vehicles - temperature class OT4, ST1/ST2, horizontal mounting position</p> <p>Yes; Rail vehicles - vibrations and shocks: Category 1 Class A/B</p> <p>Yes; For proof of conformity, see Service & Support</p>
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> • horizontal installation, min. • horizontal installation, max. • vertical installation, min. • vertical installation, max. 	<p>-40 °C; = Tmin (incl. condensation/frost)</p> <p>70 °C; = Tmax; +85 °C for 10 min (OT4, ST1/ST2 acc. to EN 50155)</p> <p>-40 °C; = Tmin</p> <p>50 °C; = Tmax</p>
Altitude during operation relating to sea level	
<ul style="list-style-type: none"> • Installation altitude above sea level, max. • Ambient air temperature-barometric pressure-altitude 	<p>2 000 m</p> <p>Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m)</p>
Relative humidity	
<ul style="list-style-type: none"> • With condensation, tested in accordance with IEC 60068-2-38, max. 	100 %; RH incl. condensation / frost (no commissioning in bedewed state), horizontal installation
Resistance	
Coolants and lubricants	
<ul style="list-style-type: none"> — Resistant to commercially available coolants and lubricants 	Yes; Incl. diesel and oil droplets in the air
Use in stationary industrial systems	
<ul style="list-style-type: none"> — to biologically active substances according to EN 60721-3-3 — to chemically active substances according to EN 60721-3-3 — to mechanically active substances according to EN 60721-3-3 — Against mechanical environmental conditions acc. to EN 60721-3-3 	<p>Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request</p> <p>Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *</p> <p>Yes; Class 3S4 incl. sand, dust, *</p> <p>Yes; Class 3M8 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0)</p>
Use on land craft, rail vehicles and special-purpose vehicles	
<ul style="list-style-type: none"> — to biologically active substances according to EN 60721-3-5 — to chemically active substances according to EN 60721-3-5 — to mechanically active substances according to EN 60721-3-5 — Against mechanical environmental conditions acc. to EN 60721-3-5 — against mechanical environmental conditions in agriculture acc. to ISO 15003 	<p>Yes; Class 5B2 mold, fungus and dry rot spores (with the exception of fauna); Class 5B3 on request</p> <p>Yes; Class 5C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *</p> <p>Yes; Class 5S3 incl. sand, dust; *</p> <p>Yes; Class 5M2 using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0)</p> <p>Yes; level 1 (Location LE) using the SIPLUS Mounting Kit ET 200SP (6AG1193-6AA00-0AA0)</p>
Usage in industrial process technology	
<ul style="list-style-type: none"> — Against chemically active substances acc. to EN 60654-4 — Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04 	<p>Yes; Class 3 (excluding trichlorethylene)</p> <p>Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)</p>
Remark	
<ul style="list-style-type: none"> — Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04 	* The supplied plug covers must remain in place over the unused interfaces during operation!
Conformal coating	
<ul style="list-style-type: none"> • Coatings for printed circuit board assemblies acc. to EN 61086 • Protection against fouling acc. to EN 60664-3 • Electronic equipment on rolling stock acc. to EN 50155 • Military testing according to MIL-I-46058C, Amendment 7 • Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A 	<p>Yes; Class 2 for high reliability</p> <p>Yes; Type 1 protection</p> <p>Yes; Class PC2 protective coating acc. to EN 50155:2017</p> <p>Yes; Discoloration of coating possible during service life</p> <p>Yes; Conformal coating, Class A</p>
Dimensions	
Width	15 mm
Height	73 mm
Depth	58 mm
Weights	
Weight, approx.	28 g

Other

Note:

for use in railway applications, also observe the product information "SIPLUS extreme RAIL" A5E37661960A, Online Support article 109736776

last modified:

1/16/2021 