



SIMATIC ET 200SP, relay module, RQ COni 3x120VDC..230VAC/5A ST, 3 CO contacts non-isolated contacts, packing unit: 1 unit, suitable for BU type U0, color code CC20, substitute value output, module diagnostics for supply voltage

General information	
Product type designation	RQ 3x120VDC-230VAC/5A CO n.i. ST
Firmware version	V0.0
• FW update possible	No
usable BaseUnits	BU type U0
Color code for module-specific color identification plate	CC20
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
Redundancy	
• Redundancy capability	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption (rated value)	55 mA; without load
output voltage / header	
Rated value (AC)	230 V
Power loss	
Power loss, typ.	1.4 W
Address area	
Address space per module	
• Inputs	+ 1 byte for QI information
• Outputs	1 byte
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	type C
Selection of BaseUnit for connection variants	
• 2-wire connection	BU type U0
• 3-wire connection	BU type U0
Digital outputs	
Type of digital output	Relays
Number of digital outputs	3
Current-sinking	Yes
Current-sourcing	Yes
Digital outputs, parameterizable	Yes
Short-circuit protection	No

Switching capacity of the outputs	
• with resistive load, max.	5 A; see additional description in the manual
• with inductive load, max.	2 A; see additional description in the manual
Parallel switching of two outputs	
• for logic links	Yes
• for uprating	No
• for redundant control of a load	Yes
Switching frequency	
• with resistive load, max.	2 Hz
• with inductive load, max.	0.5 Hz
• on lamp load, max.	2 Hz
Total current of the outputs	
• Current per channel, max.	5 A
• Current per module, max.	5 A
Total current of the outputs (per module)	
horizontal installation	
— up to 50 °C, max.	5 A
— up to 60 °C, max.	5 A
vertical installation	
— up to 40 °C, max.	5 A
— up to 50 °C, max.	5 A
Relay outputs	
• Number of relay outputs	3; Changeover contact, non-floating
• Rated supply voltage of relay coil L+ (DC)	24 V
• Current consumption of relays (coil current of all relays), max.	40 mA
• external protection for relay outputs	yes, with miniature fuse max. 6.3 A tripping current, quick-response tripping characteristic and 1 500 A breaking capacity
• Number of operating cycles, max.	1 000 000; see additional description in the manual
Switching capacity of contacts	
— with inductive load, max.	2 A; see additional description in the manual
— with resistive load, max.	5 A; see additional description in the manual
— Thermal continuous current, max.	5 A; Max. 1 385 VA, 150 W
— Switching current, min.	10 mA; 5 V DC
— Rated switching voltage (DC)	24 V DC to 120 V DC
— Rated switching voltage (AC)	24V AC to 230V AC
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	200 m
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnoses	
• Monitoring the supply voltage	Yes
• Wire-break	No
• Short-circuit	No
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; green LED
• for channel diagnostics	No
• for module diagnostics	Yes; green/red DIAG LED
Potential separation	
Potential separation channels	
• between the channels	No
• between the channels and backplane bus	Yes
• between the channels and the power supply of the electronics	Yes
Isolation	
Isolation tested with	2 000 V DC (routine test)

tested with	
• between channels and backplane bus/supply voltage	2 000 V DC (routine test)
• between backplane bus and supply voltage	707 V DC (type test)
Standards, approvals, certificates	
Suitable for safety functions	No
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	2 000 m
Dimensions	
Width	20 mm
Height	73 mm
Depth	58 mm
Weights	
Weight, approx.	40 g

last modified:

12/28/2021 