

product type designation

SFP991-1LD A

SCALANCE X accessory; Active plug-in transceiver SFP991-1LD A; 1x 100 Mbit/s LC port, optical; single-mode optical up to max. 26 km.



interfaces	
number of electrical/optical connections / for network components or terminal equipment / maximum	1
number of optical interfaces / for network components or terminal equipment / maximum	1
number of 100 Mbit/s LC ports	1
design of the optical interface / for network components or terminal equipment	LC
wavelength / of the optical interface	1310 nm; Single-mode
connectable optical power relative to 1 mW <ul style="list-style-type: none"> of the transmitter output / minimum of the transmitter output / maximum of the receiver input / maximum 	-15 dB -8 dB -8 dB
optical sensitivity relating to 1 mW / of the receiver input / minimum	-31 dB
attenuation factor / of the FOC transmission link / minimum necessary	0 dB
range / at the optical interface / depending on the optical fiber used	0 ... 26 km
ambient conditions	
ambient temperature <ul style="list-style-type: none"> during operation during storage during transport note 	-40 ... +95 °C -40 ... +95 °C -40 ... +95 °C A maximum operating temperature of +95 °C is permissible for a duration of 16 hours.
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	SFP Module
width	14 mm
height	9 mm
depth	57 mm
net weight	0.01 kg
fastening method	latched
standards, specifications, approvals	
standard <ul style="list-style-type: none"> for hazardous zone for safety / from CSA and UL for emitted interference 	EN 60079-0: 2006, EN60079-15: 2005, II 3 G Ex nA II T4, KEMA 07 ATEX 0145 X UL 60950-1, CSA C22.2 No. 60950-1-03 EN 61000-6-4:2007 (Class A)

<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-2:2005
certificate of suitability	EN 61000-6-2:2005, EN 61000-6-4:2007
<ul style="list-style-type: none"> • CE marking 	Yes
<ul style="list-style-type: none"> • C-Tick 	Yes
<ul style="list-style-type: none"> • KC approval 	No
MTBF	370 a
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> • to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> • to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> • to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> • to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> • to website: CAx-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> • to website: Industry Online Support 	https://support.industry.siemens.com

last modified:

7/7/2022 