

product type designation

SFP992-1LD+

SCALANCE X accessory; plug-in transceiver SFP992-1LD+; 1x 1000 Mbit/s LC port, optical; single-mode optical up to max. 30 km.



interfaces	
number of electrical/optical connections / for network components or terminal equipment / maximum	1
number of optical interfaces / for network components or terminal equipment / maximum	1
number of 1000 Mbit/s LC ports / for single mode (LD) / integrated	1
design of the optical interface / for network components or terminal equipment	LC
wavelength / of the optical interface	1310 nm; Single-mode
connectable optical power relative to 1 mW	
• of the transmitter output / minimum	-5 dB
• of the transmitter output / maximum	0 dB
• of the receiver input / maximum	0 dB
optical sensitivity relating to 1 mW / of the receiver input / minimum	-24 dB
attenuation factor / of the FOC transmission link / minimum necessary	0 dB
range / at the optical interface / depending on the optical fiber used	0 ... 30 km
ambient conditions	
ambient temperature	
• during operation	-40 ... +85 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	SFP Module
width	14 mm
height	9 mm
depth	57 mm
net weight	0.01 kg
fastening method	latched
standards, specifications, approvals	
standard	
• for hazardous zone	EN 60079-0: 2006, EN60079-15: 2005, II 3 G Ex nA II T4, KEMA 07 ATEX 0145 X
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-1-03
• for emitted interference	EN 61000-6-4:2007 (Class A)
• for interference immunity	EN 61000-6-2:2005

certificate of suitability <ul style="list-style-type: none"> • CE marking • C-Tick • KC approval • CCC / for hazardous zone according to GB standard • CCC / for hazardous zone according to GB standard / as marking 	EN 61000-6-2:2005, EN 61000-6-4:2007 Yes Yes No Yes Ex nA IIC T4 Gc
Marine classification association <ul style="list-style-type: none"> • French marine classification society (BV) 	Yes
MTBF	320 a
further information / internet links	
internet link <ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAx-Download-Manager • to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified:

5/28/2023 