



SCALANCE X accessory; plug-in transceiver SFP992-1; 1x 1000 Mbit/s LC port, optical; multimode optical up to max. 750 m 1 pack = 10 units.

interfaces	
number of electrical/optical connections / for network components or terminal equipment / maximum	1
number of optical interfaces / for network components or terminal equipment / maximum	1
number of 1000 Mbit/s LC ports / for multimode / integrated	1
design of the optical interface / for network components or terminal equipment	LC
wavelength / of the optical interface	850 nm; Multi-mode
connectable optical power relative to 1 mW <ul style="list-style-type: none"> <li>• of the transmitter output / minimum</li> <li>• of the transmitter output / maximum</li> <li>• of the receiver input / maximum</li> </ul>	-9.5 dB -2.5 dB -3 dB
optical sensitivity relating to 1 mW / of the receiver input / minimum	-17 dB
attenuation factor / of the FOC transmission link / minimum necessary	0 dB
range / at the optical interface / depending on the optical fiber used	0.35 ... 0.75 km
ambient conditions	
ambient temperature <ul style="list-style-type: none"> <li>• during operation</li> <li>• during storage</li> <li>• during transport</li> <li>• note</li> </ul>	-40 ... +85 °C -40 ... +85 °C -40 ... +85 °C A maximum operating temperature of +85 °C is permissible for a duration of 16 hours
relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	SFP Module
width	14 mm
height	9 mm
depth	57 mm
net weight	0.01 kg
fastening method	latched
standards, specifications, approvals	
standard <ul style="list-style-type: none"> <li>• for FM</li> <li>• for hazardous zone</li> <li>• for safety / from CSA and UL</li> </ul>	FM3611: Class 1, Division 2, Group A, B, C, D / T4, Class 1, Zone 2, Group IIC, T4 EN 60079-0: 2006, EN60079-15: 2005, II 3 G Ex nA II T4, KEMA 07 ATEX 0145 X UL 60950-1, CSA C22.2 No. 60950-1-03

<ul style="list-style-type: none"> <li>• for emitted interference</li> <li>• for interference immunity</li> </ul>	EN 61000-6-4:2007 (Class A) EN 61000-6-2:2005
certificate of suitability <ul style="list-style-type: none"> <li>• CE marking</li> <li>• C-Tick</li> <li>• KC approval</li> </ul>	EN 61000-6-2:2005, EN 61000-6-4:2007 Yes Yes No
Marine classification association <ul style="list-style-type: none"> <li>• French marine classification society (BV)</li> </ul>	Yes
MTBF	670 a

**further information / internet links**

internet link <ul style="list-style-type: none"> <li>• to web page: selection aid TIA Selection Tool</li> <li>• to website: Industrial communication</li> <li>• to website: Industry Mall</li> <li>• to website: Information and Download Center</li> <li>• to website: Image database</li> <li>• to website: CAx-Download-Manager</li> <li>• to website: Industry Online Support</li> </ul>	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a> <a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a> <a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a> <a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a> <a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a> <a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a> <a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
--	---

**last modified:** 5/11/2022 