

product type designation

product description

antenna connection cable N-Connect/SMA plug/plug

Connecting cable for SIMATIC NET antennas, preassembled

N-Connect/ SMA male/male Flexible connection cable pre-assembled, for Suitable for railway applications; flexible connecting cable e.g. for SCALANCE M antenna length: 1 m.



suitability for use

Flexible connecting cable for connecting an antenna or Rcoax cable to a SCALANCE M/W, suitable for railway applications

wire length

1 m

electrical data

number of electrical connections

2

type of electrical connection

N-Connect/SMA male/male

transmission frequency

0 ... 6000 MHz

attenuation factor per length

- at 2.4 GHz / typical
- at 5.2 GHz / typical
- at 5.85 GHz / typical

0.47 dB/m
0.77 dB/m
0.83 dB/m

impedance

- rated value

50 Ω

capacity per length / at 1 kHz

80.2 pF/m

relative speed

83 %

mechanical data

outer diameter

- of inner conductor
- of dielectric
- of cable sheath

1.4 mm
3.8 mm
5.5 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.1 mm

material

- of inner conductor
- of dielectric
- of cable sheath

Cu, silver plated
SPEX
RADOX

color

- of cable sheath

Black

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible

25 mm
90 mm

number of bending cycles

50

weight per length

47.8 kg/km

ambient conditions

ambient temperature

- during operation
- during storage
- during transport

-30 ... +100 °C
-30 ... +100 °C
-30 ... +100 °C

protection class IP

IP67; when plugged in

product features, product functions, product components / general	
product feature	
• halogen-free	Yes
• silicon-free	Yes
standards, specifications, approvals	
certificate of suitability	fire protection according to NF F 16-101
• RoHS conformity	Yes
• fire protection in accordance with EN 45545-2	Yes
standard	
• for fire behavior / smoke emission	EN 61034-2
• for fire behavior / flame resistance	EN 60332-1-2, IEC 60332-3-22, EN 50305,9.1.2
• for fire behavior / toxic gas emission	NF-X 70-100
reference code	
• according to IEC 81346-2	WG
• according to IEC 81346-2:2019	WGB
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAX-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
last modified:	2/3/2023 