

PS2 membrane keyboard DE, with touch pad, desktop keyboard for devices with corresponding interface Further information, Quantity and content: see technical data



Figure similar

| General information | |
|--|---|
| Product type designation | PS/2 membrane keyboard DEU |
| Control elements | |
| Keyboard fonts | |
| <ul style="list-style-type: none"> • Design • Keyboard assignment • Key illumination • Function keys <ul style="list-style-type: none"> — Number of function keys — Programmable • Number pad • status LED displays <ul style="list-style-type: none"> — for number pad — for Shift keys | Membrane keyboard B3F, 101/102 or 104/105 OMRON No 12 Yes Yes Yes; Num, Caps and Scroll Yes Yes |
| Connection type | |
| <ul style="list-style-type: none"> • USB • PS/2 • Cable length | Yes; With PS/2 USB adapter (not included in the scope of supply) Yes 1.75 m |
| Frame size/design | |
| <ul style="list-style-type: none"> • Standard | Yes; For industrial applications |
| Installation type/mounting | |
| Rack mounting | No; Desktop housing |
| Input current | |
| Current consumption (rated value) | 25 mA; Typical |
| Battery | |
| Battery-operated | No; maintenance-free |
| EMC | |
| Emission of radio interference acc. to EN 55 011 | |
| <ul style="list-style-type: none"> • Limit class A, for use in industrial areas | Yes |
| Degree and class of protection | |
| IP (all-round) | IP65 |
| Splashproof | Yes |
| Standards, approvals, certificates | |
| CE mark | Yes |
| RoHS conformity | Yes |
| Ambient conditions | |
| Ambient temperature during operation | |
| <ul style="list-style-type: none"> • min. • max. | 0 °C 40 °C |

| | |
|--|---|
| Ambient temperature during storage/transportation | |
| • min. | -10 °C |
| • max. | 50 °C |
| Relative humidity | |
| • Operation, max. | 90 %; no condensation |
| • Condensation permissible | No |
| Operating systems | |
| Runs under operating system | |
| • Windows CE | Yes |
| • Windows Vista | Yes |
| • Windows XP | Yes |
| • Windows 7 | Yes |
| • Windows 10 | Yes |
| Mechanics/material | |
| Material | |
| • Plastic | Yes; AUTOTEX (R) V150 |
| • Sheet steel | No |
| Enclosure material (front) | |
| • Plastic | Yes; AUTOTEX (R) V150 |
| Service life | |
| • Number of operating cycles, keys | 1 000 000; Operations (minimum) |
| Dimensions | |
| Width | 478.5 mm |
| Height | 28 mm |
| Depth | 180 mm |
| Weights | |
| Weight (without packaging) | 2 260 g |
| Weight (with packaging) | 2 410 g |
| Scope of supply | |
| Delivery quantity in pieces | 1; Membrane keyboard with mouse pad |
| Other | |
| Merchandise | Yes; TIPRO no. K-547 |
| Manufacturer name | TIPRO Representative Office |
| Manufacturer's address | Vogelweg 20, 31785 Hameln, Germany |
| Target devices | Suitable for IPC and HMI devices with the corresponding interfaces (see manual) |
| Note: | Suitable PS/2 USB adapter (keyboard/mouse): 1x USB 1.1, plug A on 2x PS/2 sockets, 0.20 m, black; manufacturer: Renkforce; supply by Conrad Elektronik, order no.: 1360251 - 62 |
| Usable in the following products | |
| • Product 1 | 6AV2124-0GC13-0AX0 |
| • Product 2 | 6AV2124-0QC13-0AX0 |

last modified: 4/21/2021 