



SIPLUS NET SCALANCE XC216-4C based on 6GK5216-4BS00-2AC2 with conformal coating, -40...+70 °C, manageable layer 2 IE switch; 12x 10/100 Mbps RJ45 ports; 4x 1000 Mbps combo ports (either 1000 Mbps SFPs or 10/100/1000 Mbps RJ45 ports can be used); 1x console port; diagnostics LEDs; redundant power supply temperature range -40 °C to +70 °C; assembly: standard mounting rail/S7 mounting rail/ wall; redundancy functions; office features(RSTP,VLAN,etc.); PROFINET IO device; Ethernet/

product type designation	SIPLUS NET SCALANCE XC216-4C
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s, 1000 Mbit/s
interfaces / for communication / integrated	
number of electrical connections • for network components or terminal equipment	16; RJ45
number of 10/100 Mbit/s RJ45 ports / integrated • with securing collar	12
number of 10/100/1000 Mbit/s RJ45 ports / integrated	4
number of combo ports / with RJ45 interface for optical plug-in transceiver	4; 1000 Mbit/s SFPs
interfaces / for communication / plug-in	
number of electrical connections • for SFP	4; 1000 Mbit/s
interfaces / other	
number of electrical connections • for operator console • for signaling contact • for power supply	1 1 1
type of electrical connection • for operator console • for signaling contact • for power supply	RJ11 2-pole terminal block 3-pole terminal block, permanently installed
design of the removable storage • C-PLUG	Yes
signal inputs/outputs	
operating voltage / of the signaling contacts • at DC / rated value	24 V
supply voltage, current consumption, power loss	
type of voltage / 1 / of the supply voltage • supply voltage / 1 / rated value • power loss [W] / 1 / rated value • supply voltage / 1 / rated value	DC 24 V 13.2 W 9.6 ... 31.2 V
type of voltage / 4 / of the supply voltage • consumed current / 4 / at rated supply voltage / maximum	0.55 A
ambient conditions	
ambient temperature / in horizontal mounting position / during operation	-40 ... +70 °C
ambient temperature / during storage and transport	-40 ... +70 °C
installation altitude / at height above sea level / maximum	5000 m

relative humidity <ul style="list-style-type: none"> with condensation / according to IEC 60068-2-38 / maximum 	100 %; RH including condensation/frost (no commissioning when condensation is present), horizontal installation
chemical resistance / to commercially available cooling lubricants	Yes; incl. airborne diesel and oil droplets
ambient condition / relating to ambient temperature - air pressure - installation altitude	Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m) // Tmin ... (Tmax - 10 K) at 795 hPa ... 658 hPa (+2 000 m ... +3 500 m) // Tmin ... (Tmax - 20 K) at 658 hPa ... 540 hPa (+3 500 m ... +5 000 m)
resistance to biologically active substances <ul style="list-style-type: none"> conformity according to EN 60721-3-3 conformity according to EN 60721-3-6 	Yes; Class 3B2 mold and fungal spores (excluding fauna); class 3B3 on request Yes; Class 6B2 mold, fungal and dry rot spores (excluding fauna)
resistance to chemically active substances <ul style="list-style-type: none"> conformity according to EN 60721-3-3 conformity according to EN 60721-3-6 	Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); * Yes; Class 6C3 (RH < 75%) incl. salt spray acc. to EN 60068-2-52 (Severity degree 3); *
resistance to mechanically active substances <ul style="list-style-type: none"> conformity according to EN 60721-3-3 conformity according to EN 60721-3-6 	Yes; Class 3S4 incl. sand, dust; * Yes; Class 6S3 incl. sand, dust; *
environmental category / according to IEC 60721 / note	* The supplied plug covers must remain in place on the unused interfaces during operation!
coating / for equipped printed circuit board / according to EN 61086	Yes; Class 2 for high availability
type of coating <ul style="list-style-type: none"> protection against pollution according to EN 60664-3 	Yes; protection of the type 1
type of test / of the coating / according to MIL-I-46058C	Yes; coating discoloration during service life possible
product conformity / of the coating / Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A	Yes; conformal coating, class A
protection class IP	IP20
design, dimensions and weights	
design	compact
width	140 mm
height	150 mm
depth	125 mm
net weight	1.2 kg
material / of the enclosure	Polycarbonate (PC-GF10) / pressure die cast aluminum
fastening method <ul style="list-style-type: none"> 35 mm top hat DIN rail mounting wall mounting S7-300 rail mounting S7-1500 rail mounting 	Yes No Yes Yes
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of $\leq 0.3\text{ s}$	50
cascading in cases of star topology	any (depending only on signal propagation time)
product function / QoS according to DSCP	Yes
product feature <ul style="list-style-type: none"> Cut Through switching method Store & Forward switching method 	No Yes
product functions / management, configuration, engineering	
product function <ul style="list-style-type: none"> CLI web-based management MIB support TRAPs via email configuration with STEP 7 RMON SMTP server port mirroring multiport mirroring CoS PROFINET IO diagnosis 	Yes Yes Yes Yes Yes Yes No Yes Yes Yes Yes

PROFINET conformity class	B
product function / switch-managed	Yes
telegram length / for Ethernet / maximum	1632 byte
protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• BOOTP	No
• GMRP	Yes
• DCP	Yes
• LLDP	Yes
• EtherNet/IP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 - higher level designation/location designation	Yes
product functions / diagnostics	
product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes
product functions / VLAN	
product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
protocol / is supported / GVRP	Yes
product functions / DHCP	
product function	
• DHCP server	Yes
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes
product functions / redundancy	
product function	
• of the PROFINET IO device / is supported / PROFINET system redundancy	Yes
• ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• of the PROFINET IO device / is supported / H-Sync forwarding	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes

<ul style="list-style-type: none"> • redundancy procedure MSTP 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/operation in the PRP-network 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA) 	No
<ul style="list-style-type: none"> • passive listening 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • LACP 	Yes
product functions / security	
product function	
<ul style="list-style-type: none"> • IEEE 802.1x (radius) 	Yes
<ul style="list-style-type: none"> • broadcast/multicast/unicast limiter 	Yes
<ul style="list-style-type: none"> • broadcast blocking 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes
<ul style="list-style-type: none"> • SSL 	Yes
product functions / time	
product function	
<ul style="list-style-type: none"> • SICLOCK support 	Yes
<ul style="list-style-type: none"> • NTP-client 	Yes
<ul style="list-style-type: none"> • SNTP client 	Yes
protocol / is supported	
<ul style="list-style-type: none"> • NTP 	Yes
<ul style="list-style-type: none"> • SNTP 	Yes
system modification during operation	
product function / configuration in RUN via CiR/H-CiR	Yes
standards, specifications, approvals	
MTBF	46 a
reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2 	KF
<ul style="list-style-type: none"> • according to IEC 81346-2:2019 	KFE
standards, specifications, approvals / CE	
certificate of suitability / CE marking	Yes
product conformity / according to EMC-guideline	2014/30/EU
standard	
<ul style="list-style-type: none"> • for EMC interference emission 	EN 61000-6-4, EN 50121-12
<ul style="list-style-type: none"> • for immunity to EMC 	EN 61000-6-2, EN 50121-12
certificate of suitability / RoHS conformity	Yes; 2011/65/EU
last modified:	4/21/2023 