



Figure similar

SIPLUS HMI KP8F PN based on 6AV3688-3AF37-0AX0 with conformal coating, - 20...+55 °C, Key Panel, 8 short-stroke switches with multi-colored LEDs, PROFINET interfaces with PROFIsafe, 8 DI/DO and 2 safety DI pins, 24 V DC can be looped through parameterizable as of STEP 7 V5.5

General information	
Product type designation	KP8F PN
Control elements	
With parameterizable keys	Yes
Keyboard fonts	
<ul style="list-style-type: none"> <li>Membrane keyboard                             <ul style="list-style-type: none"> <li>— user-definable label membrane keys</li> </ul> </li> <li>Function keys                             <ul style="list-style-type: none"> <li>— Number of function keys</li> </ul> </li> <li>Short-stroke keys                             <ul style="list-style-type: none"> <li>— Number of short-stroke keys</li> </ul> </li> </ul>	Yes  8  8
Expansions for operator control of the process	
<ul style="list-style-type: none"> <li>DP direct LEDs (LEDs as S7 output I/O)</li> <li>Number of color modes for LED</li> <li>Direct keys (keys as S7 input I/O)</li> </ul>	8; Adjustable brightness 5; red, green, blue, yellow, white 8
Installation type/mounting	
Mounting type	Mounting clip
Mounting position	vertical
Rack mounting	No
Front mounting	Yes; Compatible with Extension Units dimensions
Rail mounting	No
Wall mounting/direct mounting	No
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
maximum permissible angle of inclination without external ventilation	30°; To the front/rear
Number of slots for command devices and signaling units	0
Supply voltage	
Type of supply voltage	DC
Rated value (DC)	24 V; 24 V can be looped through connector, interrupted when pulled
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Input current	
Current consumption (rated value)	0.3 A
Type of output	
LED colors	
<ul style="list-style-type: none"> <li>red</li> <li>yellow</li> <li>green</li> </ul>	Yes Yes Yes

• white	Yes
• blue	Yes
<b>Digital inputs</b>	
Number of digital inputs	8; Total inputs and outputs max. 8 and 1x SIL 2 or 2x SIL 3
Input voltage	
• Rated value (DC)	24 V
<b>Digital outputs</b>	
Number of digital outputs	8; Max. 8 inputs and outputs (total)
Short-circuit protection	Yes
Switching capacity of the outputs	
• with resistive load, max.	100 mA
Output voltage	
• Rated value (DC)	24 V; Non-isolated
Total current of the outputs	
• Current per channel, max.	100 mA
• Current per group, max.	800 mA
<b>Interfaces</b>	
Number of industrial Ethernet interfaces	2; For the construction of lines and rings without external switch
Number of PROFINET interfaces	2; Incl. switch
Industrial Ethernet	
• Industrial Ethernet status LED	2; Per port
• Number of ports of the integrated switch	2; Per port
<b>Protocols</b>	
PROFINET	Yes; also 3rd party PLC
Supports protocol for PROFINET IO	Yes
PROFINET CBA	No
IRT	Yes
PROFIsafe	Yes; 1x SIL 3 (two-channel) or 2x SIL 2 (single-channel) emergency stop sensors
PROFIBUS	No
EtherNet/IP	No
MPI	No
AS-Interface	No
EIB/KNX	No
Protocols (Ethernet)	
• TCP/IP	No
Redundancy mode	
Media redundancy	
— MRP	Yes
Further protocols	
• AS-Interface Safety at Work	No
• CAN	No
• Data-Highway	No
• DeviceNet	No
• DeviceNet Safety	No
• Foundation Fieldbus	No
• INTERBUS	No
• INTERBUS-Safety	No
• Local Operating Network	No
• MODBUS	No
• SafetyBUS p	No
• SERCOS	No
• SUCOnet	No
• other bus systems	No
<b>Test commissioning functions</b>	
Illuminant test	Yes; During switch on
Key and signal lamp test	Yes; automatically when switching on
<b>EMC</b>	
Emission of radio interference acc. to EN 55 011	
• Limit class A, for use in industrial areas	Yes; Group 1, measured at a distance of 10 m
• Limit class B, for use in residential areas	No

## Degree and class of protection

IP (at the front)	IP65
IP (rear)	IP20
NEMA (front)	
<ul style="list-style-type: none"> <li>Enclosure Type 4 at the front</li> </ul>	No
<ul style="list-style-type: none"> <li>Enclosure Type 4x at the front</li> </ul>	Yes; Incl. NEMA12

## Standards, approvals, certificates

CE mark	Yes
Suitable for safety functions	Yes

## Marine approval

<ul style="list-style-type: none"> <li>Germanischer Lloyd (GL)</li> </ul>	No
<ul style="list-style-type: none"> <li>American Bureau of Shipping (ABS)</li> </ul>	No
<ul style="list-style-type: none"> <li>Bureau Veritas (BV)</li> </ul>	No
<ul style="list-style-type: none"> <li>Det Norske Veritas (DNV)</li> </ul>	No
<ul style="list-style-type: none"> <li>Lloyds Register of Shipping (LRS)</li> </ul>	No
<ul style="list-style-type: none"> <li>Nippon Kaiji Kyokai (Class NK)</li> </ul>	No
<ul style="list-style-type: none"> <li>Polski Rejestr Statkow (PRS)</li> </ul>	No

## Ambient conditions

Ambient temperature during operation	
<ul style="list-style-type: none"> <li>min.</li> </ul>	-20 °C; = Tmin (incl. condensation/frost)
<ul style="list-style-type: none"> <li>max.</li> </ul>	55 °C; = Tmax
Operation (vertical installation)	
— For vertical installation, min.	-20 °C
— For vertical installation, max.	55 °C
Operation (max. tilt angle)	
— At maximum tilt angle, min.	-20 °C
— At maximum tilt angle, max.	45 °C
Operation (vertical installation, portrait format)	
— For vertical installation, min.	-20 °C
— For vertical installation, max.	55 °C
Operation (max. tilt angle, portrait format)	
— At maximum tilt angle, min.	-20 °C
— At maximum tilt angle, max.	45 °C
Ambient temperature during storage/transportation	
<ul style="list-style-type: none"> <li>min.</li> </ul>	-20 °C
<ul style="list-style-type: none"> <li>max.</li> </ul>	60 °C
Altitude during operation relating to sea level	
<ul style="list-style-type: none"> <li>Installation altitude above sea level, max.</li> </ul>	2 000 m
<ul style="list-style-type: none"> <li>Ambient air temperature-barometric pressure-altitude</li> </ul>	Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m)
Relative humidity	
<ul style="list-style-type: none"> <li>With condensation, tested in accordance with IEC 60068-2-38, max.</li> </ul>	100 %; RH incl. condensation / frost (no commissioning in bedewed state), horizontal installation
Resistance	
Coolants and lubricants	
— Resistant to commercially available coolants and lubricants	Yes; Incl. diesel and oil droplets in the air
Use in stationary industrial systems	
— to biologically active substances according to EN 60721-3-3	Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request
— to chemically active substances according to EN 60721-3-3	Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-3	Yes; Class 3S4 incl. sand, dust, *
Use on ships/at sea	
— to biologically active substances according to EN 60721-3-6	Yes; Class 6B2 mold, fungal and dry rot spores (excluding fauna)
— to chemically active substances according to EN 60721-3-6	Yes; Class 6C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-6	Yes; Class 6S3 incl. sand, dust; *
Remark	
— Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04	* The supplied plug covers must remain in place over the unused interfaces during operation!

<b>Conformal coating</b>	
<ul style="list-style-type: none"> <li>• Coatings for printed circuit board assemblies acc. to EN 61086</li> <li>• Protection against fouling acc. to EN 60664-3</li> <li>• Military testing according to MIL-I-46058C, Amendment 7</li> <li>• Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A</li> </ul>	<p>Yes; Class 2 for high reliability</p> <p>Yes; Type 1 protection</p> <p>Yes; Discoloration of coating possible during service life</p> <p>Yes; Conformal coating, Class A</p>
<b>configuration / header</b>	
<b>Configuration software</b>	
<ul style="list-style-type: none"> <li>• STEP 7 Basic (TIA Portal)</li> <li>• STEP 7 Professional (TIA Portal)</li> </ul>	<p>Yes</p> <p>Yes</p>
<b>Functionality under WinCC (TIA Portal)</b>	
<b>Process coupling</b>	
<ul style="list-style-type: none"> <li>• S7-1200</li> <li>• S7-1500</li> <li>• S7-200</li> <li>• S7-300/400</li> <li>• LOGO!</li> <li>• WinAC</li> <li>• SINUMERIK</li> <li>• SIMOTION</li> <li>• Allen Bradley (EtherNet/IP)</li> <li>• Allen Bradley (DF1)</li> <li>• Mitsubishi (MC TCP/IP)</li> <li>• Mitsubishi (FX)</li> <li>• OMRON (FINS TCP)</li> <li>• OMRON (LINK/Multilink)</li> <li>• Modicon (Modbus TCP/IP)</li> <li>• Modicon (Modbus)</li> </ul>	<p>Yes; with ET 200pro CPU and ET 200S CPU</p> <p>Yes</p> <p>No</p> <p>Yes; with F-CPU: STEP 7 V11 SP1 (or higher) and Safety V11 (or higher) or SIMATIC STEP 7 Basic V11 (or higher)</p> <p>No</p> <p>Yes</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p> <p>No</p>
<b>Mechanics/material</b>	
<b>Enclosure material (front)</b> <ul style="list-style-type: none"> <li>• Plastic</li> <li>• Aluminum</li> <li>• Stainless steel</li> </ul>	<p>Yes</p> <p>No</p> <p>No</p>
<b>Service life</b>	
<ul style="list-style-type: none"> <li>• Short-stroke keys (in switching cycles)</li> <li>• LEDs (ON period)</li> </ul>	<p>1 500 000</p> <p>100 %</p>
<b>Dimensions</b>	
Width of the housing front	98 mm
Height of housing front	155 mm
Mounting cutout, width	68 mm; Max. thickness of mounting plate 2 - 6 mm
Mounting cutout, height	129 mm
Overall depth	49 mm; Incl. angled SIMATIC Ethernet connector
<b>Weights</b>	
Weight (without packaging)	280 g

**last modified:** 3/2/2021 