

Data sheet

6GT2690-0AA00

product type designation

product description



Distance piece MDS D139

Support for mounting heat-resistant transponders with 30 mm distance to metal
MOBY D spacer for MDS D139.

suitability for use

The support and transponder are mounted using an M5 screw

suitability for operation

for holding the transponders MDS D139/D339

mechanical data

material

PPS

color

black

ambient conditions

ambient temperature

- during operation -40 ... +220 °C
- during storage -40 ... +220 °C
- during transport -40 ... +220 °C

design, dimensions and weights

height

30 mm

diameter

85 mm

net weight

80 g

further information / internet links

internet link

- to website: TIA Selection Tool <http://www.siemens.com/tia-selection-tool>
- to the website: IWLAN <http://www.siemens.com/iwlan>
- to website: Industrial communication <http://www.siemens.com/ident/rfid>
- to website: Industry Mall <https://mall.industry.siemens.com>
- to website: Information and Download Center <http://www.siemens.com/industry/infocenter>
- to website: Selection guide for cables and connectors <https://sie.ag/2QdlxcP>
- to website: Image database <http://automation.siemens.com/bilddb>
- to website: CAx-Download-Manager <http://www.siemens.com/cax>
- to website: Industry Online Support <https://support.industry.siemens.com>

last modified:

5/28/2023 