

product type designation

**MDS D560 transponder**

Transponder MDS D560 for RF200/RF300 Gen2 ISO pill Fujitsu MB89R112, 8192-byte FRAM user memory 16x 3 mm (DxH); Minimum order quantity 50 units.



suitability for operation

RF200, RF300

### radio frequencies

operating frequency / rated value	13.56 MHz
range / maximum	160 mm; range is reader dependent: observe <a href="http://support.automation.siemens.com/WW/view/en/67384964">http://support.automation.siemens.com/WW/view/en/67384964</a>
protocol / with radio transmission	ISO 15693
transfer rate / with radio transmission / maximum	26.5 kbit/s
product feature / multitag-capable	Yes

### electrical data

product component / backup battery	No
------------------------------------	----

### memory

type of memory	FRAM
storage capacity / of the user memory	8192 byte
type of memory organization	UID (fixed code) 8 bytes, user memory 8192 bytes, configuration memory 40 bytes
number of read cycles / at ambient temperature < 40 °C / maximum	1E+12
number of write cycles / at ambient temperature < 40 °C / maximum	1E+12
data retention time / at ambient temperature < 40 °C / not less than	10 a
property of memory	Block-by-block write protection of the user memory
type of transponder chip used	Fujitsu MB89R112

### mechanical data

material	PPS
color	beige
mounting distance / relating to metal surfaces / recommended / minimum	10 mm

### ambient conditions

ambient temperature	
<ul style="list-style-type: none"> <li>during read/write access</li> <li>outside the read/write area</li> <li>during storage</li> </ul>	-20 ... +85 °C -40 ... +90 °C -40 ... +90 °C
protection class IP	IP68
shock resistance	According to DIN EN 60721-3-7 Class 7 M3
shock acceleration	400 m/s <sup>2</sup>
vibrational acceleration	100 m/s <sup>2</sup>

### design, dimensions and weights

height	3 mm
diameter	16 mm
net weight	3 g

fastening method	patching, gluing
<b>product features, product functions, product components / general</b>	
product feature	
• printable	No
<b>standards, specifications, approvals</b>	
certificate of suitability	
• IECEX	No
MTBF	228 a
<b>accessories</b>	
accessories	Mounting support and spacer
<b>further information / internet links</b>	
internet link	
• to web page: selection aid TIA Selection Tool	<a href="https://support.industry.siemens.com/cs/ww/en/view/67384964">https://support.industry.siemens.com/cs/ww/en/view/67384964</a>
• to website: Industrial communication	<a href="http://www.siemens.com/ident/rfid">http://www.siemens.com/ident/rfid</a>
• to website: Industry Mall	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
• to website: Information and Download Center	<a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>
• to website: Image database	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
• to website: CAX-Download-Manager	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
• to website: Industry Online Support	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

**last modified:**

2/10/2022 