

product type designation



Reader RF615R CMIIT

SIMATIC RF600 Reader RF615R CMIIT; Interfaces: 1 Ethernet / PROFINET M12; 1 integrated antenna + 1 ext. antenna port; 1 dig. input, 1 dig. output; 24 V DC; IP67; -25 to +55 °C without accessories.

suitability for operation

RF600 Transponder, for direct connection to Ethernet, PROFINET, EtherNet/IP or PROFIBUS via communication module, OPC UA server integrated

radio frequencies

operating frequency	920 ... 925 MHz
transmit power	3 ... 400 mW
effective radiated power	
<ul style="list-style-type: none"> for each external antenna / maximum minimum maximum 	1100 mW 10 mW 200 mW
range / maximum	4 m; With the internal antenna 1.6 m, extended ranges possible, see RF600 System Manual, range table: http://support.automation.siemens.com/WW/view/en/67384964
protocol / with radio transmission	EPCglobal Class 1 Gen 2 V2 / ISO/IEC 18000-62/-63
transfer rate / with radio transmission / maximum	400 kbit/s
product feature / multitag-capable	Yes
polarization	circular

electrical data

transmission time / for user data	
<ul style="list-style-type: none"> for write access / per byte / typical for read access / per byte / typical 	2 ms 0.15 ms

interfaces

number of external antennas	1
standard for interfaces / for communication	Ethernet, PROFINET, OPC UA, EtherNet/IP, RS422
type of electrical connection	
<ul style="list-style-type: none"> for external antenna(s) for supply voltage for communications interface at the digital inputs/outputs 	RP-TNC M12, 8-pin, connector M12, 4-pin, d-coded M12, 5-pin, female connector
number of digital inputs	1
number of digital outputs	1

mechanical data

material	Pocan
color	silver, TI-Grey
mounting distance / relating to metal surfaces / recommended / minimum	0 mm

supply voltage, current consumption, power loss

supply voltage	
<ul style="list-style-type: none"> at DC / rated value at DC 	24 V 20 ... 30 V
consumed current / at DC	

<ul style="list-style-type: none"> • at 24 V / typical • at 24 V / maximum 	<p>0.2 A</p> <p>0.22 A</p>
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation • during storage • during transport 	<p>-25 ... +55 °C</p> <p>-40 ... +85 °C</p> <p>-40 ... +85 °C</p>
ambient condition / for operation	With operating temperature below -20 °C: Warming-up time at least 10 minutes
protection class IP	IP67
shock resistance	EN 60068-2-27, EN 60068-2-6
shock acceleration	250 m/s ²
vibrational acceleration	30 m/s ²
resistance to mechanical stress	the maximum values for shock and vibration acceleration must not occur as continuous stress and they apply exclusively to assembly using screws
design, dimensions and weights	
width	133 mm
height	133 mm
depth	45 mm
net weight	0.37 kg
fastening method	Vesa 100 with 4 x M4 screws
wire length	
<ul style="list-style-type: none"> • of antenna cable / minimum • of antenna cable / maximum 	<p>1 m</p> <p>40 m</p>
product features, product functions, product components / general	
display version	LED bars with 6 LED and 1 circulating LED
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function / of the PROFINET IO device / is supported / H-Sync forwarding	No
protocol / is supported	
<ul style="list-style-type: none"> • LLDP • PROFINET IO protocol • TCP/IP • SNMP v1 • SNMP v2 • SNMP v3 • DCP • EtherNet/IP protocol • OPC UA 	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>No</p> <p>No</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>
product feature / silicon-free	Yes
standards, specifications, approvals	
certificate of suitability	wireless acc. to CMIIT, OPC UA: embedded UA Server Profile
certificate of suitability	
<ul style="list-style-type: none"> • IECEx 	No
MTBF	29 a
accessories	
accessories	One external antenna
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support 	<p>https://support.industry.siemens.com/cs/ww/en/view/67384964</p> <p>http://www.siemens.com/ident/rfid</p> <p>https://mall.industry.siemens.com</p> <p>http://www.siemens.com/industry/infocenter</p> <p>http://automation.siemens.com/bilddb</p> <p>http://www.siemens.com/cax</p> <p>https://support.industry.siemens.com</p>

last modified:

2/3/2023 