

Data sheet

6GT2690-0AH00

product type designation

product description

quick-change chuck MDS D139, D339

Support for mounting heat-resistant transponders with 20 mm distance to metal

MOBY D/RF300 ISO Quick change holder Stainless steel for MDS D139 and MDS D339; Mounting with nut M8; Packing unit: 10 units.



suitability for use

The support is mounted via M8 nuts, whereas the transponder is held by a splint. The splint allows the transponder to be quickly removed from the support.

suitability for operation

for holding the transponders MDS D139/D339

mechanical data

material	Stainless steel
color	metallic

ambient conditions

ambient temperature	
• during operation	-40 ... +220 °C
• during storage	-40 ... +220 °C
• during transport	-40 ... +220 °C

design, dimensions and weights

height	60 mm
diameter	22 mm
net weight	80 g

further information / internet links

internet link

• to website: TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to the website: IWLAN	http://www.siemens.com/iwlan
• to website: Industrial communication	http://www.siemens.com/ident/rfid
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAX-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

5/28/2023