

product type designation

product description



Antenna duplexer UHF for RF600

The splitter splits an incoming VHF signal into two outputs

RF600 antenna splitter for operation of two RF600 antennas on RF600 readers with external antenna port; IP40 -25 to +85 °C; dimensions 50x 50x 20 mm without connector.

suitability for use

For the setup and extension of gate applications for up to 8 antennas

suitability for operation

operation on RF600 readers with external antennas

mechanical data

material

aluminum

color

silver

ambient conditions

ambient temperature

- during operation -40 ... +85 °C
- during storage -40 ... +100 °C
- during transport -40 ... +100 °C

design, dimensions and weights

width

51 mm

height

19 mm

depth

51 mm

net weight

170 g

further information / internet links

internet link

- to website: TIA Selection Tool <http://www.siemens.com/tia-selection-tool>
- to the website: IWLAN <http://www.siemens.com/iwlan>
- to website: Industrial communication <http://www.siemens.com/ident/rfid>
- to website: Industry Mall <https://mall.industry.siemens.com>
- to website: Information and Download Center <http://www.siemens.com/industry/infocenter>
- to website: Selection guide for cables and connectors <https://sie.ag/2QdlxcP>
- to website: Image database <http://automation.siemens.com/bilddb>
- to website: CAx-Download-Manager <http://www.siemens.com/cax>
- to website: Industry Online Support <https://support.industry.siemens.com>

last modified:

5/28/2023 