

product type designation

product description

PROFIBUS PCF Fiber Optic standard cable

PCF fiber-optic cable with plastic cladding, preferred length, preassembled

PROFIBUS PCF Fiber Optic, with 4 PCF BFOC connectors, Length 200 m .



suitability for use

Cable for indoor applications

version of the assembled FO cable

Assembled with four BFOC connectors

cable designation

I-V(ZN)Y 2K 200/230

wire length

200 m

optical data

attenuation factor per length

- at 650 nm / maximum
- at 660 nm / maximum

10 dB/km
10 dB/km

bandwidth length product

- at 650 nm

17 GHz·m

mechanical data

number of fibers / per FOC core

1

number of FO cores / per FOC cable

2

version of the FO conductor fiber

Step index fiber 200/230 µm

outer diameter

- of the optical fibers
- of the optical fiber sheath
- of the FOC core sheath

200 µm
230 µm
2.2 mm

symmetrical deviation / of the outer diameter of the FOC core sheath

0.1 mm

outer diameter / of the cable

4.7 mm

material

- of the fiber-optic cable core
- of the optical fiber sheath
- of the FOC core sheath
- of the fiber-optic cable sheath
- of the strain relief

Quartz glass
Fluoridated special polymer
PVC
PVC
Kevlar fibers

color

- of the FOC core sheath
- of cable sheath

orange/black
Violet

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible

47 mm
70 mm

tensile load

- during installation / short-term
- during operation / maximum

800 N
200 N

short-term shear force per length

100 N/cm

weight per length

22 kg/km

ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport during installation 	-30 ... +70 °C -30 ... +70 °C -30 ... +70 °C -5 ... +50 °C
fire behavior	flame-resistant acc. to IEC 60332-1-2
chemical resistance	
<ul style="list-style-type: none"> to mineral oil to grease 	conditional resistance conditional resistance
radiological resistance / to UV radiation	not resistant
protection class IP	IP20
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free silicon-free 	No Yes
product component / rodent protection	No
wire length	
<ul style="list-style-type: none"> for PCF FOC / with PROFIBUS / maximum 	400 m
standards, specifications, approvals	
certificate of suitability	
<ul style="list-style-type: none"> RoHS conformity 	Yes
reference code	
<ul style="list-style-type: none"> according to IEC 81346-2 according to IEC 81346-2:2019 	WH WHA
further information / internet links	
internet link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool to website: Industrial communication to website: Industry Mall to website: Information and Download Center to website: Selection guide for cables and connectors to website: Image database to website: CAx-Download-Manager to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter https://sie.ag/2QdlxcP http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified:

5/10/2022 