

product type designation

product description

PROFIBUS PCF Fiber Optic standard cable

PCF fiber-optic cable with plastic cladding, preferred length, preassembled

PROFIBUS PCF Fiber Optic, with 4 PCF Simplex connectors, length 300 m.



suitability for use

Cable for indoor applications

version of the assembled FO cable

Assembled with four Simplex connectors

cable designation

I-V(ZN)Y 2K 200/230

wire length

300 m

optical data

attenuation factor per length

- at 650 nm / maximum
- at 660 nm / maximum

10 dB/km

10 dB/km

bandwidth length product

- at 650 nm

17 GHz·m

mechanical data

number of fibers / per FOC core

1

number of FO cores / per FOC cable

2

version of the FO conductor fiber

Step index fiber 200/230 µm

outer diameter

- of the optical fibers
- of the optical fiber sheath
- of the FOC core sheath

200 µm

230 µm

2.2 mm

symmetrical deviation / of the outer diameter of the FOC core sheath

0.1 mm

outer diameter / of the cable

4.7 mm

material

- of the fiber-optic cable core
- of the optical fiber sheath
- of the FOC core sheath
- of the fiber-optic cable sheath
- of the strain relief

Quartz glass

Fluoridated special polymer

PVC

PVC

Kevlar fibers

color

- of the FOC core sheath
- of cable sheath

orange/black

Violet

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible

47 mm

70 mm

tensile load

- during installation / short-term
- during operation / maximum

800 N

200 N

short-term shear force per length

100 N/cm

weight per length

22 kg/km

ambient conditions	
ambient temperature	
• during operation	-30 ... +70 °C
• during storage	-30 ... +70 °C
• during transport	-30 ... +70 °C
• during installation	-5 ... +50 °C
fire behavior	flame-resistant acc. to IEC 60332-1-2
chemical resistance	
• to mineral oil	conditional resistance
• to grease	conditional resistance
radiological resistance / to UV radiation	not resistant
protection class IP	IP20
product features, product functions, product components / general	
product feature	
• halogen-free	No
• silicon-free	Yes
product component / rodent protection	No
wire length	
• for PCF FOC / with PROFIBUS / maximum	400 m
standards, specifications, approvals	
certificate of suitability	
• RoHS conformity	Yes
reference code	
• according to IEC 81346-2	WH
• according to IEC 81346-2:2019	WHA
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

5/10/2022 