

**product type designation**

product description

**MM FO CORD LC/LC, 50/125**

Multimode glass fiber-optic cable, preassembled

MM FO Cord LC/LC; 50/125; pre-assembled with 2x LC Duplex connectors; length 1.0 m.



suitability for use

Cable for applications in the control cabinet

version of the assembled FO cable

Pre-assembled with 2x LC DUPLEX connectors

cable designation

I-V(ZN)H 2x50/125 OM2

wire length

1 m

**optical data**

attenuation factor per length

- at 850 nm / maximum
- at 1300 nm / maximum

3.5 dB/km  
1.5 dB/km

bandwidth length product

- at 850 nm
- at 1300 nm

500 GHz·m  
1300 GHz·m

**mechanical data**

number of fibers / per FOC core

1

number of FO cores / per FOC cable

2

version of the FO conductor fiber

Multi-mode gradient fiber 50/125 µm, OM 2

design of the FOC core

Fixed core

outer diameter

- of the optical fibers
- of the optical fiber sheath
- of the FOC core sheath

50 µm  
125 µm  
2.8 mm

width / of cable sheath

5.9 mm

thickness / of cable sheath

2.8 mm

material

- of the fiber-optic cable core
- of the optical fiber sheath
- of the FOC core sheath
- of the fiber-optic cable sheath
- of the strain relief

Quartz glass  
Quartz glass  
FR-LSZH  
LSZH  
Aramid fibers

color

- of the FOC core sheath

green/green

bending radius

- with single bend / minimum permissible

42 mm

tensile load

- during installation / short-term
- during operation / maximum

500 N  
500 N

continuous shear force per length

100 N/cm

**ambient conditions**

ambient temperature

<ul style="list-style-type: none"> <li>• during operation</li> <li>• during storage</li> <li>• during transport</li> <li>• during installation</li> </ul>	<p>-30 ... +70 °C</p> <p>-30 ... +70 °C</p> <p>-30 ... +70 °C</p> <p>-5 ... +50 °C</p>
fire behavior	flame-resistant acc. to IEC 60332-3-22 (Cat. A)
protection class IP	IP20
<b>product features, product functions, product components / general</b>	
product feature	
<ul style="list-style-type: none"> <li>• halogen-free</li> <li>• silicon-free</li> </ul>	<p>Yes</p> <p>Yes</p>
product component / rodent protection	No
<b>standards, specifications, approvals</b>	
certificate of suitability	
<ul style="list-style-type: none"> <li>• RoHS conformity</li> </ul>	Yes
reference code	
<ul style="list-style-type: none"> <li>• according to IEC 81346-2</li> <li>• according to IEC 81346-2:2019</li> </ul>	<p>WH</p> <p>WHA</p>
<b>further information / internet links</b>	
internet link	
<ul style="list-style-type: none"> <li>• to web page: selection aid TIA Selection Tool</li> <li>• to website: Industrial communication</li> <li>• to website: Industry Mall</li> <li>• to website: Information and Download Center</li> <li>• to website: Selection guide for cables and connectors</li> <li>• to website: Image database</li> <li>• to website: CAx-Download-Manager</li> <li>• to website: Industry Online Support</li> </ul>	<p><a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a></p> <p><a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a></p> <p><a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a></p> <p><a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a></p> <p><a href="https://sie.ag/2QdlxcP">https://sie.ag/2QdlxcP</a></p> <p><a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a></p> <p><a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a></p> <p><a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a></p>

last modified:

5/10/2022 