

product type designation

product description

Fiber optic standard cable

Flexible glass fiber-optic cable, preferred length, preassembled

fiber optic cable (62.5/125), standard cable, splittable, pre-assembled with 4 BFOC connectors, length 10 m.



suitability for use

Cable for installation indoors and outdoors

version of the assembled FO cable

Assembled with four BFOC connectors

cable designation

AT-V(ZN)YY 2X1 G 62,5/125 OM1

wire length

10 m

optical data

attenuation factor per length

- at 850 nm / maximum
- at 1300 nm / maximum

3 dB/km

0.8 dB/km

bandwidth length product

- at 850 nm
- at 1300 nm

300 GHz·m

800 GHz·m

mechanical data

number of fibers / per FOC core

1

number of FO cores / per FOC cable

2

version of the FO conductor fiber

Multimode graded-index fiber 62.5/125 µm, OM 1

design of the FOC core

Compact core, diameter 900 µm

design of the fiber-optic cable

Segmentable outer conductor

outer diameter

- of the optical fibers
- of the optical fiber sheath
- of the FOC core sheath

62.5 µm

125 µm

3.5 mm

width / of cable sheath

9.8 mm

thickness / of cable sheath

6.3 mm

material

- of the fiber-optic cable core
- of the optical fiber sheath
- of the FOC core sheath
- of the fiber-optic cable sheath
- of the strain relief

Quartz glass

Quartz glass

PVC

PVC

Aramid fibers and glass roving

color

- of the FOC core sheath
- of cable sheath

gray

Black

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible

80 mm

80 mm

tensile load

- during installation / short-term
- during operation / maximum

1500 N

1500 N

continuous shear force per length	150 N/cm
weight per length	70 kg/km
ambient conditions	
ambient temperature	
• during operation	-40 ... +85 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
• during installation	-5 ... +50 °C
fire behavior	flame-resistant acc. to IEC 60332-1-2 and IEC 60332-3-22 (Cat. A)
chemical resistance	
• to mineral oil	not resistant
• to grease	not resistant
radiological resistance / to UV radiation	resistant
protection class IP	IP20
product features, product functions, product components / general	
product feature	
• halogen-free	No
• silicon-free	Yes
product component / rodent protection	No
wire length	
• for glass FOC / for 100BaseFX / for Industrial Ethernet / maximum	4000 m
• for glass FOC / for 1000BaseSX / for Industrial Ethernet / maximum	500 m
• for glass FOC / for 1000BaseLX / for Industrial Ethernet / maximum	1000 m
• for glass FOC / with PROFIBUS / maximum	3000 m
standards, specifications, approvals	
certificate of suitability	
• RoHS conformity	Yes
reference code	
• according to IEC 81346-2	WH
• according to IEC 81346-2:2019	WHA
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAx-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

2/14/2023 