


product type designation

product description

FO Standard Cable GP

Glass fiber-optic cable, preferred length, preassembled

FO Standard Cable 50/125, pre-assembled with 2x2 BFOC connectors, insertion aid, length 200 m.



suitability for use	Cable for installation indoors and outdoors, UL approval
version of the assembled FO cable	Assembled with four BFOC connectors
cable designation	AT-W(ZN)YY 2x1 G 50/125 OM2++
wire length	200 m
optical data	
attenuation factor per length	
• at 850 nm / maximum	2.7 dB/km
• at 1300 nm / maximum	0.7 dB/km
bandwidth length product	
• at 850 nm	600 GHz·m
• at 1300 nm	1200 GHz·m
mechanical data	
number of fibers / per FOC core	1
number of FO cores / per FOC cable	2
version of the FO conductor fiber	Multi-mode gradient fiber 50/125 µm, OM 2
design of the FOC core	Hollow core, filled, diameter 1400 µm
design of the fiber-optic cable	segmentable
outer diameter	
• of the optical fibers	50 µm
• of the optical fiber sheath	125 µm
• of the FOC core sheath	2.9 mm
symmetrical deviation / of the outer diameter of the FOC core sheath	0.1 mm
width / of cable sheath	7.4 mm
thickness / of cable sheath	4.5 mm
material	
• of the fiber-optic cable core	Quartz glass
• of the optical fiber sheath	Quartz glass
• of the FOC core sheath	PVC
• of the fiber-optic cable sheath	PVC
• of the strain relief	Aramid fibers
color	
• of the FOC core sheath	orange/black
• of cable sheath	green
bending radius	
• with single bend / minimum permissible	45 mm
• with multiple bends / minimum permissible	65 mm
tensile load	

<ul style="list-style-type: none"> during installation / short-term 	1200 N
<ul style="list-style-type: none"> during operation / maximum 	500 N
short-term shear force per length	600 N/cm
continuous shear force per length	400 N/cm
weight per length	40 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation 	-25 ... +80 °C
<ul style="list-style-type: none"> during storage 	-25 ... +80 °C
<ul style="list-style-type: none"> during transport 	-25 ... +80 °C
<ul style="list-style-type: none"> during installation 	-5 ... +50 °C
fire behavior	flame-resistant acc. to IEC 60332-1-2 and IEC 60332-3-22 (Cat. A)
chemical resistance	
<ul style="list-style-type: none"> to mineral oil 	conditional resistance
<ul style="list-style-type: none"> to grease 	conditional resistance
radiological resistance / to UV radiation	resistant
protection class IP	IP20
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free 	No
<ul style="list-style-type: none"> silicon-free 	Yes
product component / rodent protection	No
wire length	
<ul style="list-style-type: none"> for glass FOC / for 100BaseFX / for Industrial Ethernet / maximum 	5000 m
<ul style="list-style-type: none"> for glass FOC / for 1000BaseSX / for Industrial Ethernet / maximum 	750 m
<ul style="list-style-type: none"> for glass FOC / for 1000BaseLX / for Industrial Ethernet / maximum 	2000 m
<ul style="list-style-type: none"> for glass FOC / with PROFIBUS / maximum 	3000 m
standards, specifications, approvals	
certificate of suitability	
<ul style="list-style-type: none"> UL approval 	Yes; UL approval: cULus OFN (NEC Article 770, UL 1651) / CSA approval: OFN 90 FT4 (CSA Standard C22.2 No. 232)
<ul style="list-style-type: none"> RoHS conformity 	Yes
reference code	
<ul style="list-style-type: none"> according to IEC 81346-2 	WH
<ul style="list-style-type: none"> according to IEC 81346-2:2019 	WHA
further information / internet links	
internet link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
<ul style="list-style-type: none"> to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> to website: CAX-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> to website: Industry Online Support 	https://support.industry.siemens.com

last modified:

2/3/2023 