

product type designation

product description

FO Trailing Cable

Glass fiber-optic cable, preferred length, preassembled

FO Trailing Cable 50/125, pre-assembled with 2x2 BFOC connectors, insertion aid, length 50 m.



suitability for use

Flexible cable for use in cable carriers for high mechanical loading, no UL approval

version of the assembled FO cable

Assembled with four BFOC connectors

cable designation

AT-W(ZN)Y(ZN)11Y 2G 50/125 OM2++

wire length

50 m

optical data

attenuation factor per length

- at 850 nm / maximum
- at 1300 nm / maximum

2.7 dB/km
0.7 dB/km

bandwidth length product

- at 850 nm
- at 1300 nm

600 GHz·m
1200 GHz·m

mechanical data

number of fibers / per FOC core

1

number of FO cores / per FOC cable

2

version of the FO conductor fiber

Multi-mode gradient fiber 50/125 µm, OM 2

design of the FOC core

Hollow core, filled, diameter 1400 µm

design of the fiber-optic cable

segmentable

outer diameter

- of the optical fibers
- of the optical fiber sheath
- of the FOC core sheath

50 µm
125 µm
2.9 mm

symmetrical deviation / of the outer diameter of the FOC core sheath

0.1 mm

outer diameter / of the cable

10.5 mm

symmetrical deviation / of the outer diameter of the line

0.5 mm

material

- of the fiber-optic cable core
- of the optical fiber sheath
- of the FOC core sheath
- of the fiber-optic cable sheath
- of the strain relief

Quartz glass
Quartz glass
PVC
PUR
Aramid fibers

color

- of the FOC core sheath
- of cable sheath

orange/black
green

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible

150 mm
200 mm

number of bending cycles

5000000

tensile load	
• during installation / short-term	2000 N
• during operation / maximum	800 N
short-term shear force per length	700 N/cm
continuous shear force per length	400 N/cm
weight per length	90 kg/km
ambient conditions	
ambient temperature	
• during operation	-40 ... +80 °C
• during storage	-40 ... +80 °C
• during transport	-40 ... +80 °C
• during installation	-5 ... +50 °C
fire behavior	flammable
chemical resistance	
• to mineral oil	acc. to IEC 60811-404 with test oil IRM 902 (acc. to ISO 1817), +100 °C, 168 h, pull speed 250 mm/min.
• to grease	resistant
radiological resistance / to UV radiation	resistant
protection class IP	IP20
product features, product functions, product components / general	
product feature	
• halogen-free	No
• silicon-free	Yes
product component / rodent protection	No
wire length	
• for glass FOC / for 100BaseFX / for Industrial Ethernet / maximum	5000 m
• for glass FOC / for 1000BaseSX / for Industrial Ethernet / maximum	750 m
• for glass FOC / for 1000BaseLX / for Industrial Ethernet / maximum	2000 m
• for glass FOC / with PROFIBUS / maximum	3000 m
standards, specifications, approvals	
certificate of suitability	
• RoHS conformity	Yes
reference code	
• according to IEC 81346-2	WH
• according to IEC 81346-2:2019	WHA
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAX-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

5/10/2022 