

product type designation

product description

SM FO CORD SC/SC, 9/125

Singlemode glass fiber-optic cable, preassembled

SM FO Cord SC/SC; 9/125, pre-assembled with 2x2 SC duplex connectors, length 1.0 m.




Figure similar

suitability for use	Cable for applications in the control cabinet
version of the assembled FO cable	Pre-assembled with 2x SC DUPLEX connectors
cable designation	I-V(ZN)H 2E9/125 G.652D
wire length	1 m
optical data	
attenuation factor per length	
• at 1300 nm / maximum	0.4 dB/km
• at 1550 nm / maximum	0.3 dB/km
mechanical data	
number of fibers / per FOC core	1
number of FO cores / per FOC cable	2
version of the FO conductor fiber	Singlemode glass fiber 9/125 µm
design of the FOC core	Fixed core
outer diameter	
• of the optical fibers	9 µm
• of the optical fiber sheath	125 µm
• of the FOC core sheath	2.8 mm
width / of cable sheath	5.9 mm
thickness / of cable sheath	2.8 mm
material	
• of the fiber-optic cable core	Quartz glass
• of the optical fiber sheath	Quartz glass
• of the FOC core sheath	FR-LSZH
• of the fiber-optic cable sheath	LSZH
• of the strain relief	Aramid fibers
color	
• of the FOC core sheath	green/green
bending radius	
• with single bend / minimum permissible	42 mm
tensile load	
• during installation / short-term	500 N
• during operation / maximum	500 N
continuous shear force per length	100 N/cm
ambient conditions	
ambient temperature	
• during operation	-30 ... +70 °C
• during storage	-30 ... +70 °C

<ul style="list-style-type: none"> during transport during installation 	-30 ... +70 °C -5 ... +50 °C
fire behavior	flame-resistant acc. to IEC 60332-3-22 (Cat. A)
protection class IP	IP20
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free silicon-free 	Yes Yes
product component / rodent protection	No
standards, specifications, approvals	
certificate of suitability	
<ul style="list-style-type: none"> RoHS conformity 	Yes
reference code	
<ul style="list-style-type: none"> according to IEC 81346-2 according to IEC 81346-2:2019 	WH WHA
further information / internet links	
internet link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool to website: Industrial communication to website: Industry Mall to website: Information and Download Center to website: Selection guide for cables and connectors to website: Image database to website: CAx-Download-Manager to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter https://sie.ag/2QdlxcP http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified:

5/10/2022 