


product type designation

product description

FO Standard Cable GP

Glass fiber-optic cable, preferred length, preassembled

FO Standard Cable 50/125, pre-assembled with 2x2 BFOC connectors, length 0.5 m.



suitability for use

Cable for installation indoors and outdoors, UL approval

version of the assembled FO cable

Assembled with four BFOC connectors

cable designation

AT-W(ZN)YY 2x1 G 50/125 OM2++

wire length

0.5 m

optical data

attenuation factor per length

- at 850 nm / maximum
- at 1300 nm / maximum

2.7 dB/km

0.7 dB/km

bandwidth length product

- at 850 nm
- at 1300 nm

600 GHz·m

1200 GHz·m

mechanical data

number of fibers / per FOC core

1

number of FO cores / per FOC cable

2

version of the FO conductor fiber

Multi-mode gradient fiber 50/125 µm, OM 2

design of the FOC core

Hollow core, filled, diameter 1400 µm

design of the fiber-optic cable

segmentable

outer diameter

- of the optical fibers
- of the optical fiber sheath
- of the FOC core sheath

50 µm

125 µm

2.9 mm

symmetrical deviation / of the outer diameter of the FOC core sheath

0.1 mm

width / of cable sheath

7.4 mm

thickness / of cable sheath

4.5 mm

material

- of the fiber-optic cable core
- of the optical fiber sheath
- of the FOC core sheath
- of the fiber-optic cable sheath
- of the strain relief

Quartz glass

Quartz glass

PVC

PVC

Aramid fibers

color

- of the FOC core sheath
- of cable sheath

orange/black

green

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible

45 mm

65 mm

tensile load

• during installation / short-term	1200 N
• during operation / maximum	500 N
short-term shear force per length	600 N/cm
continuous shear force per length	400 N/cm
weight per length	40 kg/km
ambient conditions	
ambient temperature	
• during operation	-25 ... +80 °C
• during storage	-25 ... +80 °C
• during transport	-25 ... +80 °C
• during installation	-5 ... +50 °C
fire behavior	flame-resistant acc. to IEC 60332-1-2 and IEC 60332-3-22 (Cat. A)
chemical resistance	
• to mineral oil	conditional resistance
• to grease	conditional resistance
radiological resistance / to UV radiation	resistant
protection class IP	IP20
product features, product functions, product components / general	
product feature	
• halogen-free	No
• silicon-free	Yes
product component / rodent protection	No
wire length	
• for glass FOC / for 100BaseFX / for Industrial Ethernet / maximum	5000 m
• for glass FOC / for 1000BaseSX / for Industrial Ethernet / maximum	750 m
• for glass FOC / for 1000BaseLX / for Industrial Ethernet / maximum	2000 m
• for glass FOC / with PROFIBUS / maximum	3000 m
standards, specifications, approvals	
certificate of suitability	
• UL approval	Yes; UL approval: cULus OFN (NEC Article 770, UL 1651) / CSA approval: OFN 90 FT4 (CSA Standard C22.2 No. 232)
• RoHS conformity	Yes
reference code	
• according to IEC 81346-2	WH
• according to IEC 81346-2:2019	WHA
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	http://www.siemens.com/tia-selection-tool
• to website: Industrial communication	http://www.siemens.com/simatic-net
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Selection guide for cables and connectors	https://sie.ag/2QdlxcP
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAX-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com
last modified:	2/3/2023 