


product type designation

product description

FO Standard Cable GP

Glass fiber-optic cable, preferred length, preassembled

FO Standard Cable GP 50/125, pre-assembled with 2x LC duplex connectors, length 5.0m .



suitability for use	Cable for installation indoors and outdoors, UL approval
version of the assembled FO cable	Pre-assembled with 2x LC DUPLEX connectors
cable designation	AT-W(ZN)YY 2x1 G 50/125 OM2++
wire length	5 m
optical data	
attenuation factor per length	
• at 850 nm / maximum	2.7 dB/km
• at 1300 nm / maximum	0.7 dB/km
bandwidth length product	
• at 850 nm	600 GHz·m
• at 1300 nm	1200 GHz·m
mechanical data	
number of fibers / per FOC core	1
number of FO cores / per FOC cable	2
version of the FO conductor fiber	Multi-mode gradient fiber 50/125 µm, OM 2
design of the FOC core	Hollow core, filled, diameter 1400 µm
design of the fiber-optic cable	segmentable
outer diameter	
• of the optical fibers	50 µm
• of the optical fiber sheath	125 µm
• of the FOC core sheath	2.9 mm
symmetrical deviation / of the outer diameter of the FOC core sheath	0.1 mm
width / of cable sheath	7.4 mm
thickness / of cable sheath	4.5 mm
material	
• of the fiber-optic cable core	Quartz glass
• of the optical fiber sheath	Quartz glass
• of the FOC core sheath	PVC
• of the fiber-optic cable sheath	PVC
• of the strain relief	Aramid fibers
color	
• of the FOC core sheath	orange/black
• of cable sheath	green
bending radius	
• with single bend / minimum permissible	45 mm
• with multiple bends / minimum permissible	65 mm
tensile load	

<ul style="list-style-type: none"> during installation / short-term 	1200 N
<ul style="list-style-type: none"> during operation / maximum 	500 N
short-term shear force per length	600 N/cm
continuous shear force per length	400 N/cm
weight per length	40 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation 	-25 ... +80 °C
<ul style="list-style-type: none"> during storage 	-25 ... +80 °C
<ul style="list-style-type: none"> during transport 	-25 ... +80 °C
<ul style="list-style-type: none"> during installation 	-5 ... +50 °C
fire behavior	flame-resistant acc. to IEC 60332-1-2 and IEC 60332-3-22 (Cat. A)
chemical resistance	
<ul style="list-style-type: none"> to mineral oil 	conditional resistance
<ul style="list-style-type: none"> to grease 	conditional resistance
radiological resistance / to UV radiation	resistant
protection class IP	IP20
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free 	No
<ul style="list-style-type: none"> silicon-free 	Yes
product component / rodent protection	No
wire length	
<ul style="list-style-type: none"> for glass FOC / for 100BaseFX / for Industrial Ethernet / maximum 	5000 m
<ul style="list-style-type: none"> for glass FOC / for 1000BaseSX / for Industrial Ethernet / maximum 	750 m
<ul style="list-style-type: none"> for glass FOC / for 1000BaseLX / for Industrial Ethernet / maximum 	2000 m
<ul style="list-style-type: none"> for glass FOC / with PROFIBUS / maximum 	3000 m
standards, specifications, approvals	
certificate of suitability	
<ul style="list-style-type: none"> UL approval 	Yes; UL approval: cULus OFN (NEC Article 770, UL 1651) / CSA approval: OFN 90 FT4 (CSA Standard C22.2 No. 232)
<ul style="list-style-type: none"> RoHS conformity 	Yes
reference code	
<ul style="list-style-type: none"> according to IEC 81346-2 	WH
<ul style="list-style-type: none"> according to IEC 81346-2:2019 	WHA
further information / internet links	
internet link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
<ul style="list-style-type: none"> to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> to website: CAX-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> to website: Industry Online Support 	https://support.industry.siemens.com

last modified:

2/3/2023 