


**product type designation**

product description

**FO Standard Cable GP**

Glass fiber-optic cable, preferred length, preassembled

FO Standard Cable GP (50/125), pre-assembled with 2x2 SC connectors, length 15 m.



suitability for use	Cable for installation indoors and outdoors, UL approval
version of the assembled FO cable	Preassembled with four SC connectors
cable designation	AT-W(ZN)YY 2x1 G 50/125 OM2++
wire length	15 m
<b>optical data</b>	
attenuation factor per length	
• at 850 nm / maximum	2.7 dB/km
• at 1300 nm / maximum	0.7 dB/km
bandwidth length product	
• at 850 nm	600 GHz·m
• at 1300 nm	1200 GHz·m
<b>mechanical data</b>	
number of fibers / per FOC core	1
number of FO cores / per FOC cable	2
version of the FO conductor fiber	Multi-mode gradient fiber 50/125 µm, OM 2
design of the FOC core	Hollow core, filled, diameter 1400 µm
design of the fiber-optic cable	segmentable
outer diameter	
• of the optical fibers	50 µm
• of the optical fiber sheath	125 µm
• of the FOC core sheath	2.9 mm
symmetrical deviation / of the outer diameter of the FOC core sheath	0.1 mm
width / of cable sheath	7.4 mm
thickness / of cable sheath	4.5 mm
material	
• of the fiber-optic cable core	Quartz glass
• of the optical fiber sheath	Quartz glass
• of the FOC core sheath	PVC
• of the fiber-optic cable sheath	PVC
• of the strain relief	Aramid fibers
color	
• of the FOC core sheath	orange/black
• of cable sheath	green
bending radius	
• with single bend / minimum permissible	45 mm
• with multiple bends / minimum permissible	65 mm
tensile load	

<ul style="list-style-type: none"> <li>during installation / short-term</li> </ul>	1200 N
<ul style="list-style-type: none"> <li>during operation / maximum</li> </ul>	500 N
short-term shear force per length	600 N/cm
continuous shear force per length	400 N/cm
weight per length	40 kg/km
<b>ambient conditions</b>	
ambient temperature	
<ul style="list-style-type: none"> <li>during operation</li> </ul>	-25 ... +80 °C
<ul style="list-style-type: none"> <li>during storage</li> </ul>	-25 ... +80 °C
<ul style="list-style-type: none"> <li>during transport</li> </ul>	-25 ... +80 °C
<ul style="list-style-type: none"> <li>during installation</li> </ul>	-5 ... +50 °C
fire behavior	flame-resistant acc. to IEC 60332-1-2 and IEC 60332-3-22 (Cat. A)
chemical resistance	
<ul style="list-style-type: none"> <li>to mineral oil</li> </ul>	conditional resistance
<ul style="list-style-type: none"> <li>to grease</li> </ul>	conditional resistance
radiological resistance / to UV radiation	resistant
protection class IP	IP20
<b>product features, product functions, product components / general</b>	
product feature	
<ul style="list-style-type: none"> <li>halogen-free</li> </ul>	No
<ul style="list-style-type: none"> <li>silicon-free</li> </ul>	Yes
product component / rodent protection	No
wire length	
<ul style="list-style-type: none"> <li>for glass FOC / for 100BaseFX / for Industrial Ethernet / maximum</li> </ul>	5000 m
<ul style="list-style-type: none"> <li>for glass FOC / for 1000BaseSX / for Industrial Ethernet / maximum</li> </ul>	750 m
<ul style="list-style-type: none"> <li>for glass FOC / for 1000BaseLX / for Industrial Ethernet / maximum</li> </ul>	2000 m
<ul style="list-style-type: none"> <li>for glass FOC / with PROFIBUS / maximum</li> </ul>	3000 m
<b>standards, specifications, approvals</b>	
certificate of suitability	
<ul style="list-style-type: none"> <li>UL approval</li> </ul>	Yes; UL approval: cULus OFN (NEC Article 770, UL 1651) / CSA approval: OFN 90 FT4 (CSA Standard C22.2 No. 232)
<ul style="list-style-type: none"> <li>RoHS conformity</li> </ul>	Yes
reference code	
<ul style="list-style-type: none"> <li>according to IEC 81346-2</li> </ul>	WH
<ul style="list-style-type: none"> <li>according to IEC 81346-2:2019</li> </ul>	WHA
<b>further information / internet links</b>	
internet link	
<ul style="list-style-type: none"> <li>to web page: selection aid TIA Selection Tool</li> </ul>	<a href="http://www.siemens.com/tia-selection-tool">http://www.siemens.com/tia-selection-tool</a>
<ul style="list-style-type: none"> <li>to website: Industrial communication</li> </ul>	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
<ul style="list-style-type: none"> <li>to website: Industry Mall</li> </ul>	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
<ul style="list-style-type: none"> <li>to website: Information and Download Center</li> </ul>	<a href="http://www.siemens.com/industry/infocenter">http://www.siemens.com/industry/infocenter</a>
<ul style="list-style-type: none"> <li>to website: Selection guide for cables and connectors</li> </ul>	<a href="https://sie.ag/2QdlxcP">https://sie.ag/2QdlxcP</a>
<ul style="list-style-type: none"> <li>to website: Image database</li> </ul>	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
<ul style="list-style-type: none"> <li>to website: CAx-Download-Manager</li> </ul>	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
<ul style="list-style-type: none"> <li>to website: Industry Online Support</li> </ul>	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

last modified:

2/3/2023 