


product type designation

product description



Energy cable 4 x 1.5

Power cable (4-core), sold by the meter, unassembled

Energy cable, 4-core power line, stranded wire, 4x 1.5 mm², trailable Delivery unit: max. 1000 m, minimum order quantity 20 m sold by the meter

suitability for use

connection of 24 V power supply

cable designation

LIYY 4X1X1.5 BK

electrical data

operating voltage / RMS value

600 V

conductor cross section / of the power line

1.5 mm²

continuous current / of the power lines

16 A

mechanical data

number of electrical cores

4

outer diameter

- of inner conductor
- of the wire insulation
- of cable sheath

1.6 mm
2.3 mm
7.7 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.3 mm

conductor class

5

material

- of the conductor
- of the wire insulation
- of cable sheath

CU, blank
PVC
PVC

product component / PE connection

No

marking / of cores

Color

color

- of the power line insulation
- of cable sheath

brown / white / blue / black
Black

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible
- with continuous bending

31 mm
62 mm
62 mm

number of bending cycles

2000000

tensile load / maximum

100 N

weight per length

97 kg/km

ambient conditions

ambient temperature

- during operation
- during storage
- during transport
- during installation

-20 ... +90 °C
-30 ... +90 °C
-30 ... +90 °C
-20 ... +90 °C

fire behavior

Flame-resistant acc. to IEC 60332-1-2

class of burning behaviour / according to EN 13501-6

Eca

chemical resistance	
<ul style="list-style-type: none"> to mineral oil 	Oil resistant according to EN 50290-2-22 (VDE 0819), compound type TM55 (7x24h/90 °C)
<ul style="list-style-type: none"> to grease 	Conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free 	No
<ul style="list-style-type: none"> silicon-free 	Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; c(ETL)us 3047254 CM 75°C
UL/ETL style / 600 V Rating	Yes; E502506 AWM STYLE 21216 90°C
certificate of suitability	
<ul style="list-style-type: none"> EAC approval 	Yes
<ul style="list-style-type: none"> RoHS conformity 	Yes
further information / internet links	
internet link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
<ul style="list-style-type: none"> to website: Selection guide for cables and connectors 	https://sie.ag/2QdlxcP
<ul style="list-style-type: none"> to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> to website: CAx-Download-Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> to website: Industry Online Support 	https://support.industry.siemens.com

last modified:

7/7/2022 