

product type designation

product description

Control connecting cable M12-180/M12-180

Flexible plug-in cable (5-wire), preferred length, pre-assembled with one 5-pin M12 male and one female connector (A-coded, IO-Link Port Class B, 180° cable outlet)

Control connecting cable M12-180/M12-180; 5-core; IO-Link port Class B; pre-assembled with M12 plug and M12 socket (A-coded); straight cable outlet; length 1.0 m.



Figure similar

suitability for use

Plug-in cable for connecting IO-Link components and sensing mechanisms to IO modules, degree of protection IP 65/67

wire length

1 m

electrical data

operating voltage / RMS value

300 V

conductor cross section / of the power line

0.4 mm²

continuous current / of the power lines

2.5 A

mechanical data

number of electrical cores

5

type of electrical connection

M12-180

AWG number

24

outer diameter

- of inner conductor
- of the wire insulation
- of cable sheath

0.7 mm
1.2 mm
5.3 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.3 mm

material

- of the conductor
- of cable sheath

CU, blank
PUR

product component / PE connection

No

marking / of cores

Color

color

- of the power line insulation
- of cable sheath

Brown / white / blue / black / gray
Black

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible

21 mm
42 mm

tensile load / maximum

10 N

weight per length

40 kg/km

plug

type of plug interlock

screwed

design of plug-in connection

M12-180

connector coding

M12

connector coding / of the M12 circular connector

A coded

ambient conditions

ambient temperature

- during operation

-15 ... +80 °C

• during storage • during transport • during installation	-25 ... +80 °C -25 ... +80 °C -15 ... +80 °C
fire behavior	Flame-resistant according to IEC 60332-1-2, UL 2556, Sec. 9.3 (FT1), CSA C22.2 No.2556, UL 1581, Sec. 1061 (cable flame)
class of burning behaviour / according to EN 13501-6	Fca
chemical resistance • to mineral oil • to grease • to water	Conditional resistance Conditional resistance Conditional resistance
radiological resistance / to UV radiation	sunlight resistant acc. to UL 2556 sec. 4.2.8.5 (720h)
protection class IP	IP65 / 67
product features, product functions, product components / general	
product feature • halogen-free • silicon-free	Yes Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	Yes; UL Style 20233 (80°C/300V) CSA C22.2 No. 210 I/II A/B FT1
certificate of suitability • EAC approval • RoHS conformity	Yes Yes
further information / internet links	
internet link • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Industry Mall • to website: Information and Download Center • to website: Selection guide for cables and connectors • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter https://sie.ag/2QdlxcP http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified:

5/28/2023 