



Stairwell light timer, 230V 1 NO contact 16A 250V 50Hz, electronic, separate Multi voltage input 8...230V AC DC, 7 selectable functions, setting range 0,5...12 min., for 3- or 4-wire circuit, resettable, max. glow lamp current 50mA, 1WE

| Model | |
|---|----------------------------------|
| product brand name | SETRON |
| product designation | Stairwell lighting timer |
| General technical data | |
| switch-off prewarning | flashing |
| principle of operation of the staircase lighting switch | electronic |
| Voltage | |
| type of voltage of the operating voltage | AC |
| operating voltage at AC minimum | 230 V |
| operating voltage at AC maximum | 230 V |
| staircase lighting timing switch reset function | resettable + continuous light |
| Switching capacity | |
| switching capacity apparent power | |
| <ul style="list-style-type: none"> for fluorescent lamp load with DUO circuit for fluorescent lamp load with parallel compensation for uncompensated fluorescent lamp load | 1 000 VA |
| switching capacity current | |
| <ul style="list-style-type: none"> rated value | 16 A |
| switching capacity active power with incandescent lamp load | 2 000 W |
| Dissipation | |
| power loss [W] for rated value of the current at AC in hot operating state per pole | 1 W |
| Control current | |
| type of voltage | |
| <ul style="list-style-type: none"> of control voltage_1 | AC |
| control voltage | |
| <ul style="list-style-type: none"> _1 initial value _1 full-scale value _2 initial value _2 full-scale value | 230 V 230 V 8 V 230 V |
| control voltage frequency | |
| <ul style="list-style-type: none"> _1 initial value _1 full-scale value _2 initial value _2 full-scale value | 50 Hz 60 Hz 50 Hz 50 Hz |
| Adjustable parameters | |
| adjustable OFF-delay time | |
| <ul style="list-style-type: none"> initial value full-scale value | 0.5 min 12 min |
| number of NC contacts | 0 |

| | | |
|---------------------------------|----------------------------------|--------------|
| number of NO contacts | 1 | |
| number of CO contacts | 0 | |
| Mechanical Design | | |
| height | 90 mm | |
| width | 18 mm | |
| depth | 64 mm | |
| installation depth | 64 mm | |
| number of modular width units | 1 | |
| fastening method | DIN-busbar | |
| General Product Approval | Declaration of Conformity | other |

[Confirmation](#)



[Confirmation](#)

[Miscellaneous](#)

Environment

[Environmental Confirmations](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=7LF6311>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/7LF6311>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=7LF6311

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

4/20/2023 