



Stairwell light timer, 230V, 1 NO contact 16A 250V 50Hz, electronic, setting range 0,5...10 min., for 3- or 4-wire circuit, resettable, max. glow lamp current 25mA, 1WE

Model	
product brand name	SETRON
product designation	Stairwell lighting timer
General technical data	
switch-off prewarning	without
principle of operation of the staircase lighting switch	electronic
Voltage	
type of voltage of the operating voltage	AC
operating voltage at AC minimum	230 V
operating voltage at AC maximum	230 V
staircase lighting timing switch reset function	resettable
Switching capacity	
switching capacity apparent power	
<ul style="list-style-type: none"> <li>for fluorescent lamp load with DUO circuit</li> <li>for fluorescent lamp load with parallel compensation</li> <li>for uncompensated fluorescent lamp load</li> </ul>	1 000 VA
switching capacity current	
<ul style="list-style-type: none"> <li>rated value</li> </ul>	16 A
switching capacity active power with incandescent lamp load	2 000 W
Dissipation	
power loss [W] for rated value of the current at AC in hot operating state per pole	0.8 W
Control current	
type of voltage	
<ul style="list-style-type: none"> <li>of control voltage_1</li> </ul>	AC
control voltage	
<ul style="list-style-type: none"> <li>_1 initial value</li> <li>_1 full-scale value</li> </ul>	230 V
control voltage frequency	
<ul style="list-style-type: none"> <li>_1 initial value</li> <li>_1 full-scale value</li> </ul>	50 Hz
	60 Hz
Adjustable parameters	
adjustable OFF-delay time	
<ul style="list-style-type: none"> <li>initial value</li> <li>full-scale value</li> </ul>	0.5 min
	10 min
number of NC contacts	0
number of NO contacts	1
number of CO contacts	0
Mechanical Design	
height	90 mm

width	18 mm
depth	64 mm
installation depth	64 mm
number of modular width units	1
fastening method	DIN-busbar
<b>General Product Approval</b>	<b>Declaration of Conformity</b>
	<b>other</b>

[Confirmation](#)



[Confirmation](#)

[Miscellaneous](#)

## Environment

[Environmental Confirmations](#)

## Further information

**Siemens has decided to exit the Russian market (see here).**

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

**Siemens is working on the renewal of the current EAC certificates.**

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

**Information on the packaging**

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=7LF6310>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/7LF6310>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=7LF6310](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=7LF6310)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



7LF6310

---

last modified:

4/20/2023 

