



Insta contactor with 2 NO contacts Contact for 230 V AC, 400V 25A Control 230 V AC

Model					
product brand name	SENTRON				
product designation	Insta contactor				
design of the product	2 NO contacts				
type of voltage of the operating voltage	AC				
type of voltage of the operating voltage for actuation	AC				
Supply voltage					
operating voltage rated value					
• minimum	230 V				
• maximum	230 V				
Protection class					
protection class IP	IP20				
Switching capacity					
switching capacity active power with incandescent lamp load	1 000 W				
Dissipation					
power loss [W] for rated value of the current at AC in hot operating state per pole	2 W				
Control current					
control supply voltage					
• rated value	230 V				
• rated value maximum	230 V				
Product details					
product component slide for manual operation	No				
number of NC contacts	0				
number of NO contacts	2				
product extension installable supplementary devices	Yes				
Connections					
installation or assembly note	provision must be made for spacers to ensure heat dissipation				
Mechanical Design					
height	90 mm				
width	18 mm				
depth	71 mm				
installation depth	0 mm				
number of modular width units	1				
net weight	140 g				
General Product Approval		Declaration of Conformity		other	



[Confirmation](#)



EG-Konf.



[Miscellaneous](#)

other

Environment

[Confirmation](#)

[Environmental Confirmations](#)

## Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mifb=5TT5810-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TT5810-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mifb=5TT5810-0](http://www.automation.siemens.com/bilddb/cax_en.aspx?mifb=5TT5810-0)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

2/15/2023 

