Data sheet



SIMATIC HMI TP1900 Comfort INOX Stainless steel front, continuous decorative foil; Degree of protection front IP66K, 19" widescreen TFT display, PROFINET interface, MPI/PROFIBUS DP interface, 24 MB configuration memory, Windows CE 2013; Configurable from WinCC Comfort V14 SP1 with HSP

Figure similar

General information		
Product type designation	TP1900 Comfort INOX	
Display		
Design of display	TFT	
Screen diagonal	18.5 in	
Display width	409.8 mm	
Display height	230.4 mm	
Number of colors	16 777 216	
Resolution (pixels)		
 Horizontal image resolution 	1 366 pixel	
Vertical image resolution	768 pixel	
Backlighting		
 MTBF backlighting (at 25 °C) 	50 000 h	
Backlight dimmable	Yes; 0-100 %	
Control elements		
Keyboard fonts		
 Function keys 		
 Number of function keys 	0	
 Number of function keys with LEDs 	0	
 Keys with LED 	No	
System keys	No	
Numeric keyboard	Yes; Onscreen keyboard	
alphanumeric keyboard	Yes; Onscreen keyboard	
Touch operation		
Design as touch screen	Yes	
Expansions for operator control of the process		
 DP direct LEDs (LEDs as S7 output I/O) 		
— F1Fx	0	
 Direct keys (keys as S7 input I/O) 		
— F1Fx	0	
Direct keys (touch buttons as S7 input I/O)	40	
Installation type/mounting		
Mounting position	vertical	
Mounting in portrait format possible	Yes	
Mounting in landscape format possible	Yes	
maximum permissible angle of inclination without external ventilation	35°	
Supply voltage		
Type of supply voltage	DC	

Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Input current	
Current consumption (rated value)	1.7 A
Starting current inrush I²t	0.5 A ² ·s
Power	
Active power input, typ.	41 W
Processor	
Processor type	X86
Memory	
Flash	Yes
RAM	Yes
Memory available for user data	24 Mbyte
Type of output	
Info LED	No
Power LED	No
Error LED	No
Acoustics	
Buzzer	No
Speaker	Yes
Time of day	165
Clock	Yes
Hardware clock (real-time)	
Software clock Tratenting	Yes
• retentive	Yes; Back-up duration typically 6 weeks
• synchronizable	Yes
Interfaces	
Number of industrial Ethernet interfaces	2; 2 ports (switch) + independent port
Number of RS 485 interfaces	1; RS 422 / 485 combined
Number of RS 422 interfaces	0; together with RS 485
Number of RS 232 interfaces	0
Number of USB interfaces	2; USB 2.0
Number of 20 mA interfaces (TTY)	0
Number of parallel interfaces	0
Number of other interfaces	0
Number of SD card slots	2
With software interfaces	No
Industrial Ethernet	
 Industrial Ethernet status LED 	3
 Number of ports of the integrated switch 	2
Protocols	
PROFINET	Yes
Supports protocol for PROFINET IO	Yes
IRT	Yes
PROFIBUS	Yes
EtherNet/IP	Yes
MPI	Yes
Protocols (Ethernet)	
Trotocolo (Ethornot)	
• TCP/IP	Yes
	Yes Yes
• TCP/IP	
• TCP/IP • DHCP	Yes
TCP/IP DHCP SNMP	Yes Yes
• TCP/IP • DHCP • SNMP • DCP	Yes Yes
TCP/IPDHCPSNMPDCPLLDP	Yes Yes
 TCP/IP DHCP SNMP DCP LLDP WEB characteristics HTTP 	Yes Yes Yes Yes Yes
 TCP/IP DHCP SNMP DCP LLDP WEB characteristics HTTP HTTPS 	Yes Yes Yes Yes Yes Yes
 TCP/IP DHCP SNMP DCP LLDP WEB characteristics HTTP HTTPS HTML 	Yes Yes Yes Yes Yes Yes Yes Yes
 TCP/IP DHCP SNMP DCP LLDP WEB characteristics HTTP HTTPS 	Yes Yes Yes Yes Yes Yes

A 15 - 34	V
• Active X	Yes
JavaScript	Yes
• Java VM	No
Redundancy mode	
Media redundancy	V.
— MRP	Yes
Further protocols	
• CAN	No
MODBUS	Yes
Interrupts/diagnostics/status information	
Diagnoses	
Diagnostic information readable EMC	Yes; S7 controller
Emission of radio interference acc. to EN 55 011	
 Limit class A, for use in industrial areas 	Yes
 Limit class B, for use in residential areas 	No
Degree and class of protection	
IP (at the front)	IP66K
IP (rear)	IP20
NEMA (front)	
Enclosure Type 4 at the front	No
Enclosure Type 4x at the front	Yes; indoor use only
Standards, approvals, certificates	
CE mark	Yes
cULus	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
EAC (formerly Gost-R)	Yes
Use in hazardous areas	
ATEX Zone 2	Yes
ATEX Zone 22	Yes
• IECEx Zone 2	Yes
• IECEx Zone 22	Yes
• cULus Class I Zone 1	No
• cULus Class I Zone 2, Division 2	Yes
• FM Class I Division 2	No
Marine approval	
Germanischer Lloyd (GL)	No; In application process
American Bureau of Shipping (ABS)	No; Available soon
Bureau Veritas (BV)	No; Available soon
Det Norske Veritas (DNV)	No; Available soon
Korean Register of Shipping (KRS)	No; Available soon
Lloyds Register of Shipping (LRS)	No; Available soon
Nippon Kaiji Kyokai (Class NK)	No; Available soon
Polski Rejestr Statkow (PRS)	No; Available soon
Chinese Classification Society (CCS)	No; Available soon
Ambient conditions	
Suited for indoor use	Yes
Suited for outdoor use	No
Ambient temperature during operation	
Operation (vertical installation)	
— For vertical installation, min.	0 °C
— For vertical installation, max.	45 °C
Operation (max. tilt angle)	
— At maximum tilt angle, min.	0°C
At maximum tilt angle, max.	40 °C
Operation (vertical installation, portrait format)	
— For vertical installation, min.	0°C
— For vertical installation, max.	40 °C
Operation (max. tilt angle, portrait format)	
operation (manifeld aligno, portrait format)	

— At maximum tilt angle, min.	0 °C
	35 °C
— At maximum tilt angle, max. Ambient temperature during storage/transportation	00 0
• min.	-20 °C
• max.	-20 °C
Relative humidity	00 0
Operation, max.	70 %; no condensation
Operating systems	
proprietary	No
pre-installed operating system	
Windows CE	Yes; Windows Embedded Compact 2013
configuration / header	
Message indicator	Yes
Alarm system (incl. buffer and acknowledgment)	Yes
Process value display (output)	Yes
Process value default (input) possible	Yes
Recipe management	Yes
Configuration software	
STEP 7 Basic (TIA Portal)	No
 STEP 7 Professional (TIA Portal) 	No
WinCC flexible Compact	No
WinCC flexible Standard	No
WinCC flexible Advanced	No
 WinCC Basic (TIA Portal) 	No
 WinCC Comfort (TIA Portal) 	Yes; V14 SP1 HSP and higher
 WinCC Advanced (TIA Portal) 	Yes; V14 SP1 HSP and higher
WinCC Professional (TIA Portal)	Yes; V14 SP1 HSP and higher
Languages	
Online languages	
Number of online/runtime languages	32
Project languages	
Languages per project Transfer with a Wire Co. (TIA Parts)	32
Functionality under WinCC (TIA Portal)	V
Libraries	Yes
Applications/options	Voo
Web browser Pocket Word	Yes
Pocket Word Pocket Excel	Yes Yes
POCKET EXCEI PDF Viewer	Yes
Media Player	Yes
SIMATIC WinCC Sm@rtServer	Yes
SIMATIC WINCC SHI@RServer SIMATIC WINCC Audit	Yes
Number of Visual Basic Scripts	Yes
Task planner	
time-controlled	Yes
task-controlled	Yes
Help system	
Number of characters per info text	320
Message system	
Number of alarm classes	32
Bit messages	
Number of bit messages	6 000
Analog messages	
— Number of analog messages	200
 S7 alarm number procedure 	Yes
 System messages HMI 	Yes
 System event, more (SIMATIC S7, SINUMERIK, 	Yes
SIMOTION,)	00
Number of characters per message	80
Number of process values per messageAcknowledgment groups	8 Von
A OKROWIOGGMONT GROUNG	Yes

- Managa indicator	Vee
Message indicatorMessage buffer	Yes
Number of entries	1 024
Circulating buffer	Yes
— retentive	Yes
	Yes
— maintenance-free	Tes
Number of recipes	500
Data records per recipe	1 000
Entries per data record	2 000
Size of internal recipe memory	4 Mbyte
Recipe memory expandable	Yes
ariables	165
Number of variables per device	4 096
Number of variables per screen	400
Limit values	Yes
Multiplexing	Yes
	Yes
Structures Arrays	Yes
Arrays nages	169
Number of configurable images	750
Number of configurable images Permanent window/default	Yes
Global image	Yes
Pop-up images	Yes
Slide-in images	Yes
Image selection by PLC	Yes
Image selection by PLC Image number in the PLC	Yes
nage objects	165
Number of objects per image	600
Text fields	Yes
	Yes
I/O fields Craphia I/O fields (graphics list)	Yes
Graphic I/O fields (graphics list) Graphic I/O fields (footblieb)	
Symbolic I/O fields (text list) Data/time fields	Yes
Date/time fields Switches	Yes
• Switches	Yes
Buttons	Yes
Graphic display	Yes
• Icons	Yes
Geometric objects	Yes
omplex image objects	40
Number of complex objects per screen Alarm view	40 Von
Alarm view Trand view	Yes
Trend view	Yes
User view Status/gentral	Yes
Status/control Sm@tClient view	Yes
Sm@rtClient view	Yes
Recipe view f(x) trand view	Yes
• f(x) trend view	Yes
System diagnostics view Modia Player	Yes
Media Player HTML browner	Yes
HTML browser	Yes
PDF display	Yes
IP camera display	Yes
Bar graphs	Yes
• Sliders	Yes
Pointer instruments	Yes
Analog/digital clock	Yes
sts	
Number of text lists per project	500
Number of entries per text list	500
 Number of graphics lists per project 	500

Number of entries per graphics list	500
Archiving Archiving	
Number of archives per device	50
Number of entries per archive	50 000
Message archive	Yes
Process value archive	Yes
Archiving methods	
Sequential archive	Yes
Short-term archive	Yes
Memory location	
— Memory card	Yes
— USB memory	Yes
— Ethernet	Yes
Data storage format	
— CSV	Yes
— TXT	Yes
— RDB	Yes
Security	
 Number of user groups 	50
 Number of user rights 	32
Number of users	50
Password export/import	Yes
SIMATIC Logon	Yes
Logging through printer	V.
• Alarms	Yes
Report (shift log)	Yes
Hardcopy Fleetronic print to file	Yes DDE HTML
Electronic print to file Character sets	Yes; PDF, HTML
Keyboard fonts	
— US English	Yes
Transfer (upload/download)	
MPI/PROFIBUS DP	Yes
• USB	Yes
• Ethernet	Yes
using external storage medium	Yes
Process coupling	
• S7-1200	Yes
• S7-1500	Yes
• S7-200	Yes
• S7-300/400	Yes
• LOGO!	Yes
• WinAC	Yes
• SINUMERIK	Yes; With SINUMERIK option package as from WinCC V15 or higher
• SIMOTION	Yes
 Allen Bradley (EtherNet/IP) 	Yes
Allen Bradley (DF1)	Yes
Mitsubishi (MC TCP/IP)	Yes
Mitsubishi (FX)	Yes
OMRON (FINS TCP)	No
OMRON (LINK/Multilink)	Yes
Modicon (Modbus TCP/IP) Madican (Madica)	Yes
Modicon (Modbus) ODC LIA Client	Yes
OPC UA Server	Yes
OPC UA Server Service tools/configuration aids	Yes
Backup/Restore manually	Yes
Backup/Restore manually Backup/Restore automatically	Yes
Simulation	Yes
Device switchover	Yes
Peripherals/Options	

Printer	Yes	
SIMATIC HMI MM memory card: Multi Media Card	Yes; Up to 128 MB	
SIMATIC HMI SD memory card: Secure Digital memory card	Yes; Up to 2 GB	
SIMATIC HMI CF memory card Compact Flash Card	No	
USB memory	Yes	
SIMATIC IPC USB Flashdrive (USB stick)	Yes; Up to 16 GB	
SIMATIC HMI USB stick	Yes; Up to 8 GB	
Network camera	Yes	
Mechanics/material		
Enclosure material (front)		
Plastic	No	
Aluminum	No	
Stainless steel	Yes	
Dimensions		
Width of the housing front	483 mm	
Height of housing front	337 mm	
Mounting cutout, width	465 mm	
Mounting cutout, height	319 mm	
Overall depth	73 mm	
Weights		
Weight (without packaging)	7.9 kg	

last modified: 3/2/2021 🖸