



SIMATIC MV530 S optical reader resolution: 800 x 600 pixels; Function: 1D/2D code reading; operating range [mm]: 30...250, depending on dot size; image field[mm]: 40x30...185x140; PoE; IP67; delivery: complete reader incl. built-in ring lamp green, pole filter, Optic 5.6 mm (fix- focus, fixed cover) and protective barrel;

suitability for operation

1D codes: Int. 2/5, Code 128, Code 93, Code 39, Code 32, EAN 13, EAN 8, UPC-A, UPC-E, GS1, Pharmacode, Postnet, 2D codes: DMC, dot code, PDF417 (without: Truncated, Micro and Macro), Q R (without: Micro and Macro), verification uncalibrated

interfaces

type of electrical connection	
• of Industrial Ethernet interface	M12, d-coded, PoE
• of the RS 422 interface	M12, 12-pin, male
• of the RS 232 interface	M12, 12-pin, male
• for supply voltage	M12, 12-pin, male
• at the digital inputs/outputs	M12, 12-pin, male
number of digital inputs	1
number of digital outputs	3
digital input version	1 fast trigger input
digital output version	1 fast strobe output, 2 potential-free outputs (NPN- PNP-capable)

optical data

design of image sensor / of the camera	CMOS-Chip, 800 x 600
type of image capture	Global shutter with manual or automatic exposure time
range	30 ... 250 mm
range / note	range determined and preset by the built-in special lens
fastening method / of lens	C-mount lens connection
type of light source	Integrated lighting or external lighting according to accessories list
picture recording frequency / maximum	100 Hz
code reading rate / maximum	80 1/s
type of focusing	Based on mounting

supply voltage, current consumption, power loss

supply voltage	
• at DC / rated value	24 V
• at DC	19.2 ... 28.8 V
consumed current / at DC / at 24 V	
• typical	0.2 A
• maximum	2 A
buffering time / in the event of power failure / minimum	0.01 s

mechanical data

material	Die-cast aluminum
color	petrol blue

ambient conditions

ambient temperature	
• during operation	50 °C
• during storage	-30 ... +70 °C
• during transport	-30 ... +70 °C

relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP67
shock resistance	According to IEC 60068-2
shock acceleration	300 m/s ²
vibrational acceleration	40 m/s ²
design, dimensions and weights	
width	68 mm
height	122 mm
depth	45 mm
net weight	0.55 kg
fastening method	4 x M4 screws
product features, product functions, product components / general	
display version	7 LEDs
protocol / is supported / Media Redundancy Protocol (MRP)	No
product function / of the PROFINET IO device / is supported / H-Sync forwarding	No
protocol / is supported	
• LLDP	Yes
• PROFINET IO protocol	Yes
• TCP/IP	Yes
• SNMP v1	Yes
• SNMP v2	No
• SNMP v3	No
• DCP	Yes
• EtherNet/IP protocol	No
• OPC UA	No
product feature / silicon-free	Yes
standards, specifications, approvals	
certificate of suitability	CE, NuG suitable
MTBF	66 a
accessories	
accessories	mounting brackets, built-in ring lights, external ring lights, E-focus lens, C-mount lenses, protective barrels for lenses
further information / internet links	
internet link	
• to web page: selection aid TIA Selection Tool	https://support.industry.siemens.com/cs/ww/en/view/67384964
• to website: Industrial communication	http://www.siemens.com/codereader
• to website: Industry Mall	https://mall.industry.siemens.com
• to website: Information and Download Center	http://www.siemens.com/industry/infocenter
• to website: Image database	http://automation.siemens.com/bilddb
• to website: CAX-Download-Manager	http://www.siemens.com/cax
• to website: Industry Online Support	https://support.industry.siemens.com

last modified:

7/7/2022 