




BN.	file No.	Length
	2922c484	1800±30mm

MATERIAL LIST:

⑤	OUTER MOLD	PVC color For black	2	
④	INNER MOLD	LD-PE	1	
③	USB 2.0 A TYPE	USB 2.0 Type A Male Solder Type ,The Pin Gold Plating, the shell for Nickel Plating	1	
②	USB C TYPE	USB Type C Male Solder Type,Black PBT Insulation,The Pin Gold Plating, the shell for Nickel Plating	1	
①	CABLE	28AWG BC*1P+23AWG BC*2+AEB , JACKET:PVC/BLACK OD4.5±0.2MM	1	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT'Y	REMARK

		NEW	2023-04-28	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

NOTE:

- Electrical test:
 - (1).100% open short & miss wire test;
 - (2).Insulation resistance:DC 300V 10M ohm min;
 - (3).Contactor resistance:3 ohm max;
- Feature:
 - Current Rate:3A max
 - Voltage:5V DC
 - Data Transfer: 480Mbps
- ROHS 2.0 AND REACH COMPLIANT
- PRINTING:AWM 2725 80°C 30V VW-1 28AWG/1P AND 23AWG/2C I/II A/B 80°C 30V USB2.0 CABLE
- Storage temperature : -20°C~+80°C
Operation temperature: -10°C~+60°C
Operation humidity:10%~85%
Storage humidity:10%~85%
- Packing:1pcs/Paper ring+Label

Renkforce					
CUSTOMER		BN.			
PRODUCT NAME	USB 2.0 A Male to Type C Male Cable			UNIT	MM
DRAWNBY	CHECKBY	APPOBY	DATE		
Hasia	Alvan		2023-04-28		