

VOLTCRAFT

VOLTCRAFT - TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

VC-SPB-20.000

Rugged Solar Power Bank 20,000 mAh with 8 W Solar Panel

CE

Item no: 2891367

The VC-SPB-20.000 is a solar charging power bank with integrated flashlight. It can charge up to 3 devices at the same time.



FEATURES

IP54 protection // Drop protection from max. 70 cm // 4x foldable solar panels // LED light with 3 modes (Steady, Flashing, SOS) // Fast charging (PD max. 20 W)

TECHNICAL DATA

Rechargeable battery	Li-Ion rechargeable battery, 20,000 mAh, 74 Wh
USB-C® input	5 V/DC, 3 A; 9 V/DC, 2 A; 12 V/DC, 1.5 A; max. 18 W (PD)
USB-C® output	5 V/DC, 3 A; 9 V/DC, 2.2 A; 12 V/DC, 1.67 A; max. 20 W (PD)
USB-A output (any port)	4.5 V/DC, 5 A; 5 V/DC, 4.5 A; 9 V/DC, 2 A; 12 V/DC, 1.5 A; max. 22.5 W
USB-A output (port 1 + port 2)	max. 15 W
USB-C® + USB-A (port 1 + port 2) output	5 V/DC, 3 A; max. 15 W
Solar panel	5 V/DC; max. 8 W
LED flashlight	3 modes (solid, SOS, flashing); Power: 1 W
Protection mechanisms	Overcharge protection; Over-discharge protection; Short circuit protection; Over temperature protection
Drop protection	max. height: 70 cm
Ingress protection	IP54
Operating temperature	0 to +45 °C
Storage temperature	0 to +45 °C
Dimensions (L x W x H) (approx.)	171 x 98 x 53 mm
Weight (approx.)	775 g

CONTENTS

Power bank // USB-C® to USB-C® cable // Lanyard // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*2891367_V1_0324_en_ds 1276935051 I1/O1 en