

VOLTCRAFT - TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

VC371 60 A 40 A AC/DC MINI CLAMP METER

CE

Item no: 2893199

The product is a clamp meter and can be used to measure and display various electrical parameters.

CONTENTS

Product // 2 x 1.5 V AAA batteries //
Test leads with removable probe tip covers // Storage bag //
Operating instructions

TECHNICAL DATA

General

Power supply	2x AAA 1.5 V batteries
Measuring categories	CAT III 600 V
Current measurement	max. 40 A (AC/DC)
Display	4000 counts (2 – 3 renewals/sec.)
Clamp opening range	width: max. 5.5 mm, height: max. 13 mm
Automatic shut-off	approx. 15 mins
Display type	EBTN colour
Operating altitude	max. 2000 m (above sea level)
Operating conditions	0 to +28 °C, ≤95 % RH (non-condensing) >+28 to +40 °C, ≤75 % RH (non-condensing) >+40 to +50 °C, ≤45 % RH (non-condensing)
Storage conditions	-10 to +50 °C, ≤80 % RH (non-condensing)



Dimensions (W x H x D)	188 x 51 x 36 mm
Weight	approx. 173 g

Test leads and probes

Rated voltage	CAT III 1000 V
Rated current	10 A
Protection class	II

Specifications

Accuracy

Specified accuracy \pm (% of the reading + display error in counts). //
 Accuracy is maintained for 1 year at +23 °C (\pm 5 °C), \leq 75 % RH (non-condensing). //
 Temperature coefficient: +0.1 x (specified accuracy) / 1 °C. //
 To avoid impaired measurements, do not operate the product in areas with electromagnetic field strengths >1 V/m (\pm 5 %).

Calibration

The recommended calibration interval is 1 year. //
 ⚠ Calibration should only be performed by qualified personnel.

Alternating current (AC)

Range	Resolution	Accuracy*
4.000 A	0.001 A	$\pm(4.0\% +10)$ with a low-pass filter (VFC) $\pm(6.0\% + 20)$
40.00 A	0.01 A	$\pm(4.0\% +9)$ with a low-pass filter (VFC) $\pm(6.0\% + 20)$

*Accuracy: 5 - 100 % of the measuring range
 Overload protection: 600 V 40 A // Frequency range: 50-60 Hz //
 Permitted display with unused measuring input: \leq 5 counts (clamp closed)
 True RMS Crest factor (CF) for non-sinusoidal signals: max. 3.0:
 Crest factor 1.0 – 2.0 : +4 % deviation // Crest factor 2.0 – 2.5 : +5 % deviation //
 Crest factor 2.5 – 3.0 : +7 % deviation

Direct current (DC)

Range	Resolution	Accuracy*
4.000 A	0.001 A	$\pm(3.5\% +9)$
40.00 A	0.01 A	$\pm(3.5\% +5)$

*Accuracy: 5 - 100 % of the measuring range; after successful zero adjustment
 Overload protection: 600 V, 40 A

AC voltage

Range	Resolution	Accuracy*
4.000 V	0.001 V	$\pm(1.2\% +5)$
40.00 V	0.01 V	$\pm(1.5\% +5)$
400.0 V	0.1 V	$\pm(1.5\% +5)$ with a low-pass filter (VFC) $\pm(4.0\% + 10)$
600 V	1 V	$\pm(2.0\% +5)$ with a low-pass filter (VFC) $\pm(4.0\% + 10)$

*Accuracy: 5 - 100 % of the measuring range
 Overload protection: 600 V // Frequency range: 45-400 Hz // Impedance: \geq 10 M Ω //
 Permitted display with unused measuring input: \leq 5 counts (clamp closed)
 True RMS Crest factor (CF) for non-sinusoidal signals: max. 3.0:

Range	Resolution	Accuracy*
Crest factor 1.0 – 2.0 : +4 % deviation // Crest factor 2.0 – 2.5 : +5 % deviation //		
Crest factor 2.5 – 3.0 : +7 % deviation		

DC voltage

Range	Resolution	Accuracy*
400.0 mV	0.1 mV	±(0.8 % +8)
4.000 V	0.001 V	±(1.2 % +5)
40.00 V	0.01 V	±(1.2 % +5)
400.0 V	0.1 V	±(1.2 % +5)
600 V	1 V	±(1.5 % +5)

*Accuracy: 5 - 100 % of the measuring range
 Overload protection: 600 V // Impedance: ≥10 MΩ //
 Permitted display with unused measuring input: ≤5 counts (clamp closed)

Resistance

Range	Resolution	Accuracy*
400.0 Ω	0.1 Ω	±(1.2 % +5)
4.000 kΩ	0.001 kΩ	±(1.0 % +5)
40.00 kΩ	0.01 kΩ	±(1.2 % +5)
400.0 kΩ	0.1 kΩ	±(1.2 % +5)
4.000 MΩ	0.001 MΩ	±(1.2 % +5)
40.00 MΩ	0.01 MΩ	±(2.0 % +5)

*Accuracy: 5 - 100 % of the measuring range, <400 Ω after successful zero adjustment
 Overload protection: 600 V // Measuring voltage: approx. 0.5 V

Capacitance

Range	Resolution	Accuracy*
4.000 nF	0.001 nF	±(4.0 % +10)
40.00 nF	0.01 nF	±(4.0 % +5)
400.0 nF	0.1 nF	±(3.0 % +5)
4.000 μF	0.001 μF	±(3.0 % +5)
40.00 μF	0.01 μF	±(3.0 % +5)
100.0 μF	0.1 μF	±(5.0 % +10)

*Accuracy: 10 - 100 % of the measuring range, ≤1 μF after successful zero adjustment
 Overload protection: 600 V // Measuring voltage: approx. 0.5 V //
 Permitted display with unused measuring input: ≤5 counts (clamp closed)

Diode test

Test voltage	Resolution
Approx. 3.2 V	0.001 V

Acoustic continuity test

Test voltage	Resolution
Approx. 1 V	0.1 Ω

Non-contact (AC) voltage test

Test voltage	Distance
≥100 V/AC	max. 5 mm

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*2893199_V1_1123_en_ds 1110011787 I1/O1 en